

---

Item no.: 282-907  
Product description: 2-conductor ground terminal block

---



Produkt kann von Bild abweichen / product may differ

Packing unit 50 pieces

RoHS compliant

Product group	1 (Rail Mounted Terminal Blocks)
Cross section [mm <sup>2</sup> ]	0.2 - 6 mm <sup>2</sup>
Cross section [AWG]	24 - 10 AWG
Connection method	CAGE CLAMP®CONNECTION
Weight	22.3 g
Color	green-yellow
Wiring type	Front-entry
No. of connection Points	2
No. of potentials	1
Height	32.5 mm
Height	1.28 in
Width	8 mm
Width	0.315 in
Depth	74.5 mm
Depth	2.93 in
Strip length from	12 mm
Strip length to	13 mm
Strip length	0.49 in
Mounting	TS 35





Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [ mm <sup>2</sup> ]
282-907	ABS	05-HG476175/3-PDA			6,0
282-907	BV	07436/Co	800	32	6,0
282-907	CSA	154112-1505033			24-10
282-907	DNV	E-10423	800	41	6,0
282-907	GL	17295-00HH			6
282-907	KEMA	2036290.01			6
282-907	LR	91/20112(E6)	800	32	6,0
282-907	RMR	11130002	800	32	6,0
282-907	UR	E45172			24-10

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected