

LC1F1154FD

TeSys F contactor - 4P (4 NO) - AC-1 - ≤ 440 V
200 A - coil 110 V DC



Main

Range	TeSys
Product name	TeSys F
Product or component type	Contacteur
Device short name	LC1F
Contacteur application	Resistive load
Utilisation category	AC-1
Poles description	4P
Pole contact composition	4 NO
[Ue] rated operational voltage	≤ 1000 V AC 50/60 Hz ≤ 460 V DC
[Ie] rated operational current	200 A (≤ 40 °C) at ≤ 440 V AC AC-1
Control circuit type	DC standard
Control circuit voltage	110 V DC
[Uimp] rated impulse withstand voltage	8 kV
Overvoltage category	III
[Ith] conventional free air thermal current	200 A at ≤ 40 °C
Irms rated making capacity	1150 A AC conforming to IEC 60947-4-1
Rated breaking capacity	920 kA conforming to IEC 60947-4-1
[Icw] rated short-time withstand current	1100 A ≤ 40 °C 10 s 640 A ≤ 40 °C 30 s 520 A ≤ 40 °C 1 min 400 A ≤ 40 °C 3 min 320 A ≤ 40 °C 10 min
Associated fuse rating	125 aM at ≤ 440 V 200 aG at ≤ 440 V
Average impedance	0.37 mOhm at 50 Hz - Ith 200 A
[Ui] rated insulation voltage	1000 V conforming to IEC 60947-4-1 1500 V conforming to VDE 0110 group C
Power dissipation per pole	15 W AC-1
Mounting support	Plate
Standards	EN 60947-1 EN 60947-4-1 IEC 60947-1 IEC 60947-4-1 JEM 1038
Product certifications	BV CCC CSA DNV GL RINA RMRoS UL LROS
Connections - terminals	Control circuit : screw clamp terminals 2 cable(s) 1...2.5 mm ² - cable stiffness: flexible - with cable end Power circuit : connector 1 cable(s) 95 mm ² Control circuit : screw clamp terminals 1 cable(s) 1...4 mm ² - cable stiffness: flexible - without cable end Control circuit : screw clamp terminals 2 cable(s) 1...4 mm ² - cable stiffness: flexible - without cable end Control circuit : screw clamp terminals 1 cable(s)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

	1...4 mm ² - cable stiffness: flexible - with cable end Control circuit : screw clamp terminals 1 cable(s) 1...4 mm ² - cable stiffness: solid - without cable end Control circuit : screw clamp terminals 2 cable(s) 1...4 mm ² - cable stiffness: solid - without cable end Power circuit : lugs-ring terminals 1 cable(s) 95 mm ² Power circuit : bar 2 x (20 x 3 mm)
Tightening torque	Control circuit : 1.2 N.m Power circuit : 10 N.m
Operating time	30...40 ms closing 30...50 ms opening
Mechanical durability	10 Mcycles
Operating rate	2400 cyc/h at <= 55 °C

Complementary

Control circuit voltage limits	0.85...1.1 Uc at 55 °C operational 0.15...0.2 Uc at 55 °C drop-out
Inrush power in W	560 W at 20 °C
Hold-in power consumption in W	4.5 W at 20 °C
Heat dissipation	4.5 W

Environment

IP degree of protection	IP2x front face with shrouds (ordered separately) conforming to IEC 60529 IP2x front face with shrouds (ordered separately) conforming to VDE 0106
Protective treatment	TH
Ambient air temperature for operation	-5...55 °C
Ambient air temperature for storage	-60...80 °C
Permissible ambient air temperature around the device	-40...70 °C
Operating altitude	3000 m without derating in temperature
Mechanical robustness	Vibrations contactor open 2 Gn, 5...300 Hz Shocks contactor closed 15 Gn for 11 ms Vibrations contactor closed 6 Gn, 5...300 Hz Shocks contactor open 9 Gn for 11 ms
Height	162 mm
Width	200.5 mm
Depth	171 mm
Product weight	3.83 kg

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Compliant - since 0852 - Schneider Electric declaration of conformity
Product environmental profile	Available
Product end of life instructions	Available