# FOCUSED ON TOUGH JOBS AND SINGLE USE DURABILITY.






BLACK ABSORBENT-LINED POWDER-FREE NITRILE **EXAMINATION GLOVES** 

Tested and certified for protection against viruses (EN ISO374-5)

WE'VE COMBINED SWEAT MANAGEMENT AND UNPRECEDENTED STRENGTH IN A FULLY-TEXTURED GLOVE THAT DELIVERS THE **ULTIMATE IN COMFORT AND PERFORMANCE.** 

- DriTek<sup>®</sup> Comfort Technology with absorbent lining that wicks away moisture for added extended use
- ANSI/EN Level 3 abrasion resistance for durability and extended wear
- · Fully textured surface for excellent grip
- Optimal thickness for durability and tactile sensitivity •
- Up to 3x longer lasting than standard nitrile gloves
- SHA Dermatogically Approved







#### PACKAGING

- 4-Pairs (8 Gloves) / Pack
- 60 Packs Per Case
- All Packaging Size-Color Coded

	T		
DriTek <sup>®</sup> sweat management technology		•	
Fully textured surface			
ANSI/EN level 3 abrasion resistance			
Ergonomic design		•	
Extended cuff		•	

ITEM NO.	SIZE		PALM \	WIDTH
N664883	М	71⁄2 – 8	3.8"	97mm
N664884	L	81⁄2 – 9	4.3"	109mm
N664885	XL	9½ – 10	4.5"	114mm
N664886	2XL	10½ - 11	4.9"	125mm
N664887	3XL	11½ – 12	5.3"	134mm

## **SafetyMate**





### 💥 MegaMan Black

BLACK ABSORBENT-LINED POWDER-FREE NITRILE EXAMINATION GLOVES

#### **PRODUCT DESCRIPTION**

#### **SPECIFICATIONS**

PRODUCT		MegaMan	
GRADE		Powder-Free Exam	
MATERIAL		Nitrile	
THICKNESS FINGER		10.1mil 0.26mm	
	PALM	8.5mil 0.22mm	
	CUFF	7.0mil 0.18mm	
COLOR		Black	
SURFACE	OUTER	Fully Textured	
	INNER	DriTek®	
LENGTH		11" 280mm	
WEIGHT		12.8g	
FIT TYPE		Ambidextrous	
CUFF TYPE		Beaded	
WATERTIGHT AQL		1.5	
ORIGIN COUNTRY		China	

#### **PHYSICAL PROPERTIES** PRE-AGING POST-AGING

TENSILE STRENGTH:	17 MPa	16 MPa
ELONGATION:	560%	520%

#### **INTEGRATED TECHNOLOGIES**

DRITEK Comfort Technology: Advanced flock lining is a powder-free, soft cotton-like nitrile glove lining that wicks away moisture for added comfort in extended use.

100% Air Inspected





\* Specifications based on size Large glove

#### **STANDARDS & CERTIFICATIONS**

EN 420.2003 REACH EU 1907/2006 EU 2016/425 ANSI/ISEA 105-2016 CAT III COMPLEX DESIGN TGA LISTED (ARTG# 334926) contact

FDA 21 CFR 177.2600 Component materials comply with FDA regulations for food

Riley C MECDE



Please visit swsafety.com/symbols for information on standards used on this document

#### ORDERING

ITEM NO.	SIZE		PALM	WIDTH	PACKAGING
N660881	XS 5	51⁄2 – 6	3.0"	76mm	50 gloves per box 10 boxes per case
N660882	S 6	5½ – 7	3.4"	87mm	50 gloves per box 10 boxes per case
N660883	M 7	71⁄2 – 8	3.8"	97mm	50 gloves per box 10 boxes per case
N660884	L 8	31⁄2 – 9	4.3"	109mm	50 gloves per box 10 boxes per case
N660885	XL 9	91⁄2 – 10	4.5"	114mm	50 gloves per box 10 boxes per case
N660886	2XL 1	01⁄2 – 11	4.9"	125mm	50 gloves per box 10 boxes per case
N660887	3XL 1'	1½ – 12	5.3"	134mm	50 gloves per box 10 boxes per case

#### APPLICATIONS

Assembly

\$

Chemical Handling

Fabrication

Janitorial Maintenance

**Light Machining Operations** 

Maintenance

Waste Management

Keep out of sunlight. Store in a cool, dry place Keep away from sources of ozone or ignition





#### FINALLY. BIODEGRADABILITY WITHOUT PERFORMANCE LOSS.

Ecotek is a nitrile treatment that accelerates the break-down in landfills without performance loss. Ecotek gloves biodegrade in landfill, 92.6% in 2 1/2 years tested according to ASTM D5526-12. SW is changing the future of disposable gloves with Ecotek, an innovative solution that contributes to a cleaner environment for a better tomorrow.

