

Mixer XGT® 1 200 W, 0 – 500 / 0 – 920 min⁻¹, 240 mm

UT001G

Model UT001G is a cordless mixer powered by 40Vmax XGT® Li-Ion battery.

The main features and benefits are: Brushless motor provides output power similar or superior to corded models in the same class. Double D-handle design reduces user fatigue to increase work efficiency. Screw in type shaft holder.



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Brushless Motor	✓
No load speed	0 - 500 / 920 min ⁻¹
Spindle Thread	M12 / M14
Blade diameter (beater)	240 mm
Vibration Level (3 axes)	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor)	1,5 m/s ²
Sound Power Level (L _{WA})	92 dB(A)
Sound Pressure Level (L _{pA})	84 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Product Dimensions (L x W x H):	373 x 458 x 235 mm
Tool weight with battery	5,7 - 7,0 kg

User benefits

- Soft start for smooth start-ups
- Ergonomic rubberised D-handle design for better fit and added comfort
- Battery cover minimizes the chance that spattered material might adhere to battery
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makita.uk.com



Related products

Other

User manual

Parts drawing