

VVD0

switch-disconnector VVD - 3 poles - 690 V 25 A
- non padlockable black handle



Main

Commercial Status	Commercialised
Range of product	TeSys VARIO
Device short name	Main switch disconnector
Product or component type	Rotary switch disconnector
Performance level	High performance
Poles description	3P
Network type	AC DC
Rotary handle mounting style	Direct
Handle colour	Black
Handle front plate colour	Black
[Ith] conventional free air thermal current	25 A
Suitability for isolation	Yes

Complementary

Kit composition	Black handle V0 switch body
Rotary handle padlocking	Without
Mounting support	Symmetrical rail for body Door for rotary handle
[Ue] rated operational voltage	690 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	8 kV
[Ithe] conventional enclosed thermal current	20 A

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

0.8 A at 250 V L/R = 1 ms DC-5 2
0.8 A at 250 V L/R = 1 ms DC-4 2
0.8 A at 250 V L/R = 1 ms DC-3 2
0.8 A at 250 V L/R = 1 ms DC-2 2
0.8 A at 250 V L/R = 1 ms DC-1 1
0.5 A at 250 V L/R = 1 ms DC-5 1
0.5 A at 250 V L/R = 1 ms DC-4 1
0.5 A at 250 V L/R = 1 ms DC-3 1
0.5 A at 250 V L/R = 1 ms DC-2 1
0.5 A at 220 V L/R = 1 ms DC-5 1
0.5 A at 220 V L/R = 1 ms DC-4 1
0.5 A at 220 V L/R = 1 ms DC-3 1
0.5 A at 220 V L/R = 1 ms DC-2 1
2.5 A at 220 V L/R = 1 ms DC-1 1
2.5 A at 110 V L/R = 1 ms DC-5 1
2.5 A at 110 V L/R = 1 ms DC-4 1
2.5 A at 110 V L/R = 1 ms DC-3 1
2.5 A at 110 V L/R = 1 ms DC-2 1
19.9 A at 240 V AC-23A
19.7 A at 230 V AC-23A
17.5 A at 690 V AC-23A
16.7 A at 500 V AC-23A
14.5 A at 400 V AC-23A
1.6 A at 250 V L/R = 1 ms DC-5 3
1.6 A at 250 V L/R = 1 ms DC-4 3
1.6 A at 250 V L/R = 1 ms DC-3 3
1.6 A at 250 V L/R = 1 ms DC-2 3
1.5 A at 220 V L/R = 1 ms DC-5 2
1.5 A at 220 V L/R = 1 ms DC-4 2
1.5 A at 220 V L/R = 1 ms DC-3 2
1.5 A at 220 V L/R = 1 ms DC-2 2
9 A at 110 V L/R = 1 ms DC-1 1
6 A at 250 V L/R = 1 ms DC-1 2
5 A at 110 V L/R = 1 ms DC-5 2
5 A at 110 V L/R = 1 ms DC-4 2
5 A at 110 V L/R = 1 ms DC-3 2
5 A at 110 V L/R = 1 ms DC-2 2
3 A at 220 V L/R = 1 ms DC-5 3
3 A at 220 V L/R = 1 ms DC-4 3
3 A at 220 V L/R = 1 ms DC-3 3
3 A at 220 V L/R = 1 ms DC-2 3
25 A at 60 V L/R = 1 ms DC-5 3
25 A at 60 V L/R = 1 ms DC-5 2
25 A at 60 V L/R = 1 ms DC-4 3
25 A at 60 V L/R = 1 ms DC-4 2
25 A at 60 V L/R = 1 ms DC-3 3
25 A at 60 V L/R = 1 ms DC-3 2
25 A at 60 V L/R = 1 ms DC-2 3
25 A at 60 V L/R = 1 ms DC-2 2
25 A at 60 V L/R = 1 ms DC-1 3
25 A at 60 V L/R = 1 ms DC-1 2
25 A at 60 V L/R = 1 ms DC-1 1
25 A at 48 V L/R = 1 ms DC-5 3
25 A at 48 V L/R = 1 ms DC-5 2
25 A at 48 V L/R = 1 ms DC-5 1
25 A at 48 V L/R = 1 ms DC-4 3
25 A at 48 V L/R = 1 ms DC-4 2
25 A at 48 V L/R = 1 ms DC-4 1
25 A at 48 V L/R = 1 ms DC-3 3
25 A at 48 V L/R = 1 ms DC-3 2
25 A at 48 V L/R = 1 ms DC-3 1
25 A at 48 V L/R = 1 ms DC-2 3
25 A at 48 V L/R = 1 ms DC-2 2
25 A at 48 V L/R = 1 ms DC-2 1
25 A at 48 V L/R = 1 ms DC-1 3
25 A at 48 V L/R = 1 ms DC-1 2
25 A at 48 V L/R = 1 ms DC-1 1
25 A at 24 V L/R = 1 ms DC-5 3
25 A at 24 V L/R = 1 ms DC-5 2
25 A at 24 V L/R = 1 ms DC-5 1
25 A at 24 V L/R = 1 ms DC-4 3
25 A at 24 V L/R = 1 ms DC-4 2
25 A at 24 V L/R = 1 ms DC-4 1
25 A at 24 V L/R = 1 ms DC-3 3
25 A at 24 V L/R = 1 ms DC-3 2
25 A at 24 V L/R = 1 ms DC-3 1
25 A at 24 V L/R = 1 ms DC-2 3
25 A at 24 V L/R = 1 ms DC-2 2
25 A at 24 V L/R = 1 ms DC-2 1
25 A at 24 V L/R = 1 ms DC-1 3
25 A at 24 V L/R = 1 ms DC-1 2
25 A at 24 V L/R = 1 ms DC-1 1
25 A at 230...690 V AC-22A
25 A at 230...690 V AC-21A
25 A at 110 V L/R = 1 ms DC-5 3

Rated operational power in W	7.5 kW at 500 V AC-3 7.5 kW at 415 V AC-23A 7.5 kW at 400 V AC-23A 5.5 kW at 400...415 V AC-3 5.5 kW at 240 V AC-23A 5.5 kW at 230 V AC-23A 4 kW at 230...240 V AC-3 15 kW at 690 V AC-23A 11 kW at 690 V AC-3 11 kW at 500 V AC-23A
Intermittent duty class	30
Making capacity	250 A at 400 V (AC-23A) 250 A at 400 V (AC-22A) 250 A at 400 V (AC-21A)
[Icm] rated short-circuit making capacity	1 kA at 400 V at Ipeak
[Icw] rated short-time withstand current	300 kA at 400 V during 1 s
Rated conditional short-circuit current	10 kA at 400 V - associated fuse 25 A gG 10 kA at 400 V - associated fuse 25 A aM
Breaking capacity	200 kA at 400 V AC-23A 200 kA at 400 V AC-22A 200 kA at 400 V AC-21A
Mechanical durability	100000 cycles
Electrical durability	30000 cycles on DC-1...5 100000 cycles on AC-21
Connections - terminals	Power circuit : screw terminals cable 6 mm ² - cable stiffness: flexible - with cable end Power circuit : screw terminals cable 10 mm ² - cable stiffness: solid -
Tightening torque	Power circuit : 2.1 N.m - on screw terminals
Colour	Black front face
Provision for padlocking	Non padlockable
Marking	0 - 1
Handle front plate dimension	45 x 45 mm
Height	74 mm
Width	45 mm
Depth	106 mm
Product weight	0.25 kg

Environment

Standards	IEC 60947-3
Product certifications	CSA GL UL
Protective treatment	TC
IP degree of protection	IP65 IP20 with protection shrouds conforming to IEC 60529
Shock resistance	30 gn conforming to IEC 60068-2-27
Vibration resistance	1 gn conforming to IEC 60068-2-6
Ambient air temperature for operation	-20...50 °C
Fire resistance	960 °C conforming to IEC 60695-2-1