

2.4 / 5 GHz Whip Antenna



APAMBJ-135

Request Samples



Check Inventory



Ø9.5 x 56 mm

RoHS/RoHS II Compliant

MSL Level = 1

Description

This versatile 2.4/5 GHz monopole whip antenna delivers robust dual-band performance for modern wireless protocols including Wi-Fi®, Bluetooth®, Zigbee®, Thread, and Matter. Featuring a peak gain of 4.0 / 5.2 dBi @ 2.4 / 5 GHz and customizable straight connectors, it enables flexible integration across diverse IoT applications. The antenna supports smart home systems, asset tracking, smart metering, and intelligent lighting installations. As a RoHS-compliant, MSL Level 1 component, it ensures reliable connectivity and manufacturing compatibility for deployments requiring consistent dual-band coverage and adaptable mechanical configurations in both residential and commercial environments.



Features

- 2.4 / 5 GHz Monopole Whip Antenna
- Peak Gain 4.0 / 5.2 dBi @ 2.4 / 5 GHz
- Connector Design for Straight
- Fully Customizable Connectors
- [RoHS Compliant | MSL Level 1](#)

Applications

- Bluetooth® / ZigBee® / Thread / Matter / Wi-Fi
- Smart Home & Smart Building
- Asset Tracking & Telematics
- Smart Metering
- Intelligent Lighting

Ordering Information

Part Number	Description	Connector Option
APAMBJ-135	2.4 / 5 GHz Whip Antenna with SMA (M)	SMA (M)
APAMBJ-135A	2.4 / 5 GHz Whip Antenna with RP-SMA (M)	RP-SMA(M)

Note: Other options not listed may be available upon request via [Abracon online support](#)



12117 Bee Caves Rd, Bldg-3, Suite 200 Bee
Cave, TX 78738
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 12-18-25

ABRACON IS
ISO9001-2015
CERTIFIED

2.4 / 5 GHz Whip Antenna



APAMBJ-135

Request Samples



Check Inventory



Ø9.5 x 56 mm

RoHS/RoHS II Compliant

MSL Level = 1

Electrical Specification

Parameter	Specification		Unit
Operating Frequency	2.4	5	GHz
VSWR (Typ.)	1.5		:1
Peak Gain	4.0	5.2	dBi
Impedance	50		Ω
Polarization	Linear		
Radiation Pattern (Azimuth)	Omni-directional		
Input Power (Ambient 25°C)	20		W

Please note: All measurement data is based on the standard configuration (conducted in free space unless otherwise specified).

Mechanical Specification

Parameter	Specification
Dimensions	Ø9.5 x 56 mm
Material	UV-Resistant ABS
Recommended Torque for Mounting	0.565 N·m
Color	Black
Antenna Type	Whip (Monopole)
RF Connector ⁽¹⁾	SMA(M)
Additional Resources	Download STEP File, Package Drawing, 3D PDF

(1): Fully Customizable Connectors

Environmental Specification

Parameter	Specification
Operating Temperature	-40°C to +85°C
Storage Temperature	-40°C to +85°C
RoHS Complaint	Yes



12117 Bee Caves Rd, Bldg-3, Suite 200 Bee
Cave, TX 78738
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 12-18-25

ABRACON IS
ISO9001-2015
CERTIFIED

2.4 / 5 GHz Whip Antenna



APAMBJ-135

Request Samples



Check Inventory




Ø9.5 x 56 mm

RoHS/RoHS II Compliant

MSL Level = 1

Product Dimensions



Unit : mm



12117 Bee Caves Rd, Bldg-3, Suite 200 Bee
Cave, TX 78738
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 12-18-25

ABRACON IS
ISO9001-2015
CERTIFIED

2.4 / 5 GHz Whip Antenna



APAMBJ-135

Request Samples



Check Inventory





Ø9.5 x 56 mm

RoHS/RoHS II Compliant

MSL Level = 1

Reflection Characteristics – Return Loss & VSWR



2.4 / 5 GHz Whip Antenna



APAMBJ-135

Request Samples



Check Inventory





Ø9.5 x 56 mm

RoHS/RoHS II Compliant

MSL Level = 1

Radiation Characteristics – Total Efficiency (%) & Peak Gain



2.4 / 5 GHz Whip Antenna



APAMBJ-135

Request Samples



Check Inventory




Ø9.5 x 56 mm


RoHS/RoHS II Compliant

MSL Level = 1

Radiation Characteristics –3D Radiation Pattern



2450 and 5500 MHz Radiation pattern



Radiation pattern reference

Note: Mounted on Ground Plane of 70x35 mm
Measured in Certified CTIA 3D Anechoic Chamber

2.4 / 5 GHz Whip Antenna



APAMBJ-135

Request Samples



Check Inventory



Ø9.5 x 56 mm

RoHS/RoHS II Compliant

MSL Level = 1

Packaging

Package Type	Quantity	Dimensions
Plastic bag	1 pcs/ Plastic bag	100 x 150 mm
Outer Box	1000 pcs/box	470 x 310 x 210 mm

ATTENTION: Abracon LLC's products are Commercial-Off-The-Shelf ('COTS'), which are designed, intended, and validated for use in commercial, industrial, and automotive applications. The customer is responsible for testing and verifying the performance of an Abracon solution to meet their system-level requirements.



12117 Bee Caves Rd, Bldg-3, Suite 200 Bee
Cave, TX 78738
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 12-18-25

ABRACON IS
ISO9001-2015
CERTIFIED