



# M12 to RJ-45 Industrial Ethernet Cable, 2m (6.5 ft.)

# TI-CD02 (v1.0R)

- Compatible with the TI-XPG50 industrial M12 switch
- 1 x M12 8-pin A-code cable interface
- 1 x RJ-45 cable interface
- IP67 weather rated
- 2m (6.5 ft.) cable length

TRENDnet's M12 to RJ-45 Industrial Ethernet Cable, 2m (6.5 ft.), model TI-CD02, is designed to connect a PoE device to the TRENDnet industrial M12 railway switch. The M12 cable features one M12 interface, and one RJ-45 interface for a single device connection. This rugged IP67 rated M12 cable is specially designed for moving bus, train, and other rolling stock applications.



# **NETWORKING SOLUTION**





# **FEATURES**



## **Cable Interfaces**

Designed to connect an RJ-45 PoE device to the 8-pin M12 interface on the industrial railway switch



## **Cable Length**

2m (6.5 ft.) cable length



## **IP67 Rated Cable**

Rugged IP67 weather rated cable

# **SPECIFICATIONS**

#### Interface

- 1 x M12 8-pin A-code male interface
- 1 x RJ-45 network interface
- IP67 rated

#### **Features**

- Max. contact resistance: 20Ω
- Min. insulation resistance: DC 200V 10ms  $10M\Omega$
- IP67 rating ensures protection from liquid moisture and fine particulates
- · PUR jacket resists oil and other contaminants

### **Operating Temperature**

• -25° - 80° C (-13° - 176° F)

#### **Operating Humidity**

• Max. 90 % non-condensing

### Length

- 2m (6.5 ft.)
- Weight
- 112g (4 oz.)

#### Warranty

• 1 year

#### **Package Contents**

• TI-CD02

All references to speed are for comparison purposes only. Product specifications, size, and shape are subject to change without notice, and actual product appearance may differ from that depicted herein.