

Datasheet

RS Pro 5.08mm Pitch Straight PCB Terminal Block with Screw Termination, Through Hole, 2 Way

RS Stock No: **790-1203**



Product Details

RS Pro 5.08 mm pitch straight PCB terminal block features screw termination and through hole mounting type. It is a professional range of wire-to-board 2-part terminal block plugs with 5.08 mm pitch with screw cage clamp termination method. It is used to mating headers.

Features and Benefits

- A professional range of wire-to-board 2-part terminal block plugs with 5.08 mm pitch with screw cage clamp termination method
- For mating headers see typical stock numbers 790-0950 for straight and 790-0994 for right angle variants
- Nylon 66 construction

**Specifications:**

Body Orientation	Straight
Colour	Green
Current Rating	16 A
Depth	15.3 mm
Gender	Female
Length	10.16 mm
Material	Nylon 66
Mounting Type	Through Hole
Number of Contacts	2
Number of Rows	1
Pitch	5.08 mm
Termination Method	Screw
Type	PCB Terminal Block
Voltage Rating	300 V
Width	13.3 mm
Insulation Resistance	>2000 mΩ
American Wire Gauge	12 to 26 AWG
Insulation Withstand Voltage	2000 V ac
Operating Temperature Range	-40 to +105°C
Flammability Rating	UL 94 V-0