


KEMET Part Number: PEH200SB3470MU2
(A351GD471M250A)

PEH200, Aluminum Electrolytic, 470 uF, 20%, 250 VDC, -40/+85°C



General Information

Supplier:	KEMET
Series:	PEH200
Dielectric:	Aluminum Electrolytic
Description:	Screw Terminal, Aluminum Electrolytic
RoHS:	Yes
AEC-Q200:	No
Notes:	Dimensions D And L Include Slewing. MS (MxS) = M8x12
Shelf Life:	156 Weeks

Dimensions

D	36.6mm +/-1mm
L	59.5mm +/-1mm
T	4.4mm NOM
S	13mm +/-0.5mm
F	8mm +/-0.5mm
DT	8mm NOM
LT	66.9mm +/-1mm

Packaging Specifications

Weight:	85 g
Slewing:	Yes
Packaging:	Bulk, Bag
Packaging Quantity:	42

Specifications

Capacitance:	470 uF
Capacitance Tolerance:	20%
Voltage DC:	250 VDC
Temperature Range:	-40/+85°C
Rated Temperature:	85°C
Life:	10000 Hrs (Rated Voltage And Ripple Current At 85C)
Resistance:	240 mOhms (100Hz 20C), 120 mOhms (100kHz 20C)
Ripple Current:	2.7 Amps (100Hz 85C), 15.9 Amps (10kHz 50C), 10.6 Amps (10kHz 40C)
Leakage Current:	4352.5 uA (5min 20°C)
Inductance:	12 nH (ESL)