

Technical data



21317VMC3

Spherical roller bearings



Spherical roller bearing, one-piece machined cage

VISUAL (S)



PRODUCT DEFINITION

Brand	SNR
d - Internal diameter	85 mm
D - External diameter	180 mm
B - Bearing/Inner ring width	41 mm
D1 - Inner diameter outer ring	153,1 mm
rs - Min fillet radius	3 mm
Number of lubrication holes	0
b - Groove width	0 mm
k - Hole diameter	0 mm
Radial clearance class	C3
Mass	5,23 kg

PRODUCT PERFORMANCE

C - Dynamic load	341000000 mN
C0 - Static load	344000000 mN
Cu - Fatigue limit load	38400000 mN
e - Coefficient	0.23
Y0 - Static axial load coefficient	2.93
Y1 - Lower axial load coefficient	2.99
Y2 - Upper axial load coefficient	4.46
N ref - Reference thermal speed	21600 °/s
N lim - Mechanical Limit Speed	27600 °/s
Tmin - Min operating temperature	233,15 °K
Tmax - Max operating temperature	473,15 °K



BEARING FREQUENCIES

BPFO - Over rolling frequency on outer ring (60 rpm)	6.705 Hz
BPFI - Over rolling frequency on inner (60 rpm)	9.295 Hz
BSF - Over rolling frequency on rolling element (60 rpm)	5.949 Hz
BRF - Rotational frequency - rolling element (60 rpm)	2.975 Hz
FTF - Rotational frequency - cage (60 rpm)	0.419 Hz

ABUTMENT

da max - Max shoulder diameter IR	0 mm
da min - Min shoulder diameter IR	99 mm
Da max - Max shoulder diameter OR	166 mm
ra max - Max shaft & housing fillet radius	2,5 mm



INDUSTRY CALCUL FACTORS

Equivalent dynamic radial load

$$P = X.F_r + Y.F_a$$

$F_a / F_r \leq e$		$F_a / F_r > e$	
X	Y	X	Y
1	Y1	0.67	Y2

Equivalent static radial load

$$P_0 = X_0.F_r + Y_0.F_a$$

X_0	Y_0
1	Y0

The values for e, Y1, Y2 and Y0 are shown in the above table .

