

Product datasheet

Specifications



SCREW TERMINAL, FEED THROUGH, 2 POINTS, 16MM², GREY

Local distributor code:
397144873

NSYTRV162

EAN Code: 3606480532122

Main

| | |
|------------------------------------|----------------------|
| Range | Lineryg |
| Product name | Lineryg TR |
| Product or component type | Terminal block |
| Device short name | TRV |
| Accessory / separate part category | Connection accessory |
| Terminal block type | Passthrough |
| Terminal block level | 1 |
| Mounting mode | Clip-on |
| Nominal cross section | 16 mm ² |
| Length | 55.5 mm |
| Colour | Grey |
| Quantity per set | Set of 50 |

Complementary

| | |
|--------------------------------|--|
| Width | 12.2 mm |
| Height | 55 mm |
| Connections - terminals | 1 x screw terminal: upstream (M5) 1 x screw terminal: downstream (M5) |
| number of connections | 2 |
| Connection position | Sideways |
| Number of measurement input | 2 |
| Cable cross section | 0.2...10 mm ² , flexible cable with cable end 0.2...16 mm ² , solid cable with cable end 1.5...25 mm ² , solid cable without cable end 1.5...25 mm ² , flexible cable without cable end |
| Tightening torque | 2.5...3 N.m |
| Wire stripping length | 14 mm |
| Tool type | Connection: screwdriver Disconnection: screwdriver |
| [Ue] rated operational voltage | 1000 V conforming to EN/IEC 60947-7-1 600 V CSA 600 V UL |
| [In] rated current | 76 A conforming to EN/IEC 60947-7-1 85 A UL 85 A CSA |

| | |
|------------------------------|--|
| Material | Polyamide 6/6: insulating case Copper alloy: connector and screw Copper alloy: commoning link Chromium-nickel steel: spring |
| Dielectric loss | 0.01 at 1 MHz conforming to IEC 60250 0.01 at 1 MHz conforming to VDE 0303-T4 |
| Dielectric constant | 3.7 at 1 MHz |
| Resistivity | 10000 M Ω .m conforming to IEC 60093 10000 M Ω .m conforming to VDE 0303-T30 |
| Surface resistance | 1000 G Ω conforming to IEC 60093 1000 G Ω conforming to VDE 0303-T30 |
| Creep resistance | 500 CTI (> 400 kB) conforming to IEC 60093 500 CTI (> 400 kB) conforming to VDE 0303-T30 |
| Flame retardance | V0, thickness 0.8 mm conforming to UL 94 |
| Net weight | 30 g |
| Range compatibility | PrismaSeT G PrismaSeT P PrismaSet HD PrismaSeT Pack 250 PanelSeT Mureva PrismaSeT XS TeSys |
| Product compatibility | Spacial enclosures |

Environment

| | |
|--|---|
| Product certifications | DNV VDE GL UL CSA |
| Dielectric strength | 1000 V conforming to IEC 60243-1 |
| Ambient air temperature for operation | -40...130 °C conforming to IEC 60216-1 -40...130 °C conforming to VDE 0304-T21 |

Packing Units

| | |
|-------------------------------------|-----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 1.200 cm |
| Package 1 Width | 5.500 cm |
| Package 1 Length | 5.500 cm |
| Package 1 Weight | 29.000 g |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 50 |
| Package 2 Height | 9.500 cm |
| Package 2 Width | 11.500 cm |
| Package 2 Length | 36.100 cm |
| Package 2 Weight | 1.538 kg |
| Unit Type of Package 3 | S06 |
| Number of Units in Package 3 | 2400 |

| | |
|------------------|-----------|
| Package 3 Height | 75.000 cm |
| Package 3 Width | 60.000 cm |
| Package 3 Length | 80.000 cm |
| Package 3 Weight | 87.496 kg |

Logistical informations

Country of origin TR

Contractual warranty

Warranty (in months) 18



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Total lifecycle Carbon footprint 14

Environmental Disclosure [Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard Yes

Packaging without single use plastic Yes

[EU RoHS Directive](#) Compliant

REACH Regulation [REACH Declaration](#)

Halogen-free status Halogen free plastic parts product

PVC free Yes

Silicone-free Yes

Use Again

Repack and remanufacture

End of life manual availability No need of specific recycling operations

Take-back No

WEEE Label  The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins