




Terminals & Splices > Spade Terminals



Spade Terminal Type: **Spade Flange Tongue Terminal**

Wire Size: **2050 – 5180 CMA**

Stud Size: **#10**

Features

Product Type Features

Stud Size	#10
Sealable	No
Wire Insulation Support Retention Type	Insulation Support

Electrical Characteristics

Voltage Rating	300 V
----------------	-------

Body Features

Product Weight	.945 g[.0333 oz]
----------------	------------------

Contact Features

Spade Terminal Type	Spade Flange Tongue Terminal
Barrel Type	Closed
Terminal Orientation	Flanged
Terminal Plating Material	Tin

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Wire Size	2050 – 5180 CMA
-----------	-----------------



Stud Diameter	4.82 mm[.19 in]
Tongue Thickness	.79 mm[.031 in]
Product Length	19.56 mm[.77 in]
Compatible Insulation Diameter (Max)	4.32 mm[.17 in]
Compatible Insulation Diameter Range	2.92 – 4.31 mm[.115 – .17 in]

Usage Conditions

Insulation Option	Partially Insulated
-------------------	---------------------

Operation/Application

Compatible With Wire Base Material	Copper
Compatible With Wire Plating Material	Tin

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	50
Packaging Method	Box

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part





numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | PIDG

 Compression Connectors(17)	 Crimp Wire Pins, Tabs & Ferrules(41)	 Knife Disconnects(11)	 Quick Disconnects(38)
 Ring Terminals(588)	 Spade Terminals(228)	 Special Purpose Terminals(1)	 Splices(41)

Customers Also Bought

 TE Part #2-520182-2 ULTRAFast 187 ASSY REC 22-18 TPBR LP	 TE Part #ANT-5GW-IPW2-NP Antenna Whip 5G WB Cell IP67 N Plug	 TE Part #ANT-5GW-SPNF1 Antenna 5G WB Cell Dome IP67 N Jack	 TE Part #8-1879134-5 RN 0603 73K2 0.1% 10PPM 1K RL
 TE Part #5-2176328-9 CRGP 1206 680K 1%	 TE Part #ANT-5GW-SPS1-1 Antenna 5G LTE IP67 Puck RG174 1M SMA	 TE Part #CSD-NM-914-NM N Type to N Type 914 mm RG58	 TE Part #1658615-4 09 POS HDF PLUG, AP, LEAD FREE



Documents

Product Drawings

SMP 0-0320863-0

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1377174-3_C1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1377174-3_C1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1377174-3_C1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.