



Brand of NTN Group

Technical data

MUC206-19FD

Insert bearings



Stainless steel insert, spherical outer diameter with locking pin, fixing by socket set screw, seal with slinger, food grease

VISUAL (S)



PRODUCT DEFINITION

Brand	SNR
B - Width of Inner Ring	38,1 mm
C - Width of Outer Ring	19 mm
C1 - Distance center of OR to center of lubrication zone	5,105 mm
d - Shaft diameter	30,163 mm
D - Outer diameter of OR	62 mm
G - Set screw size	1/4-28UNF
m - Distance to set screw	5 mm



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
 S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
 SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

PRODUCT DEFINITION

r - Radius Inner Ring	1.5
S - Distance front side/bearing centre	15,9 mm
f0 - Factor	13.7
SW - Wrench size	3,175 mm

PRODUCT PERFORMANCE

C - Dynamic load rating	16700000 mN
C0 - Static load rating	9000000 mN
Operating temperature min.	253,15 °K
Operating temperature max.	373,15 °K

OTHER FEATURES

Mass	0,308 kg
Recommended tightening torque for set screw	3.9 N-m

BEARING FREQUENCIES

BPFO - Over rolling frequency on outer ring (60 rpm)	3.57822580645161 Hz
BPMF - Over rolling frequency on inner (60 rpm)	5.42177419354839 Hz
BSF - Over rolling frequency on rolling element (60 rpm)	4.67705105410211 Hz
BRF - Rotational frequency - rolling element (60 rpm)	2.33852552705106 Hz
FTF - Rotational frequency - cage (60 rpm)	0.39758064516129 Hz

