



Wire & Cable > Wire & Cable Accessories > Cable Tie Mounts & Accessories



Wire & Cable Accessory Type: **Cable Tie Mount**

Wire & Cable Mounting Type: **Screw**

Product Width: **22 mm [.866 in]**

Primary Product Material: **Nylon**

Packaging Method: **Box**

Features

Product Type Features

Product Type	Accessory
Wire & Cable Accessory Type	Cable Tie Mount

Body Features

Primary Product Material	Nylon
--------------------------	-------

Mechanical Attachment

Wire & Cable Mounting Type	Screw
----------------------------	-------

Dimensions

Product Width	22 mm[.866 in]
---------------	----------------

Packaging Features

Packaging Method	Box
------------------	-----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant




China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2023 (233) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # 1478769-2
ANTI-VIB NYLON GLD 16MM BLK




TE Part # 1478769-3
ANTI-VIB NYLON GLD 20MM BLK



TE Part # 1478769-4
ANTI-VIB NYLON GLD 20MM BLK



TE Part # 1478769-5
ANTI-VIB NYLON GLD 25MM BLK



TE Part # 1478769-6
ANTI-VIB NYLON GLD 32MM BLK

Customers Also Bought





TE Part #7-1879233-3
SMD Power Resistor: 7 Watt, 200-2M Ohm



TE Part #2-1623730-6
BCHE SBCHE4 6R8 5%



TE Part #1478769-2
ANTI-VIB NYLON GLD 16MM BLK



TE Part #4-1625890-3
2W SM M/OX 5% 33R



TE Part #6-2176414-2
7W STD M/OX 5% 6K8



TE Part #2016677-3
RF CA,UMCC GEN2-GEN4,0.81,L50, BLACK



TE Part #1337809-3
50 OHM COAX SMA STR PLUG STIR



TE Part #1478769-3
ANTI-VIB NYLON GLD 20MM BLK



TE Part #1478769-5
ANTI-VIB NYLON GLD 25MM BLK

Documents

Product Drawings

ANTI-VIB NYLON GLD 12MM BLK

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1478769-1_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1478769-1_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1478769-1_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.