
**PWTR30-2RS-XL**

Galet de roulement

Yoke type track rollers PWTR...-2RS-XL, double row cylindrical roller bearings with particularly thick-walled outer ring, with a central rib, full complement cylindrical roller set and an inner ring, the outer ring is guided axially by the central rib and rolling elements, protected lip seal on both sides, X-life design

X-life

Information technique



Votre alternative produit actuelle

joint	2RS	Joint frottant des deux côtés
profilé bague extérieure	IOP	Optimized INA-profile
dispositif de lubrification	IR	Via inner ring

dimensions principale & données de performance

d	30 mm	Alésage
D	62 mm	Diamètre extérieur
B	29 mm	Largeur, bague intérieure
C _{r w}	35.000 N	Charge dyn. de base, radiale
C _{0r w}	44.500 N	Charge stat. de base, radiale
C _{ur w}	6.000 N	Limite à la fatigue, radiale
n _{D G}	2.200 1/min	Vitesse pour une lubrification à la graisse
F _{0r per}	44.500 N	Charge radiale statique admissible
F _{r per}	28.500 N	Charge radial dynamique admissible sur bague extérieure
≈m	0,452 kg	Poids



Dimensions

C	28 mm	Largeur, bague extérieure
d 2	38 mm	Diamètre d'arrêt rondelle de butée
r min	1 mm	Dimension minimum de chanfrein
r 1 min	0,5 mm	Dimension minimum de chanfrein

Caractéristiques

-  Effort radial
-  Effort axial uni directionnel
-  Effort axial dans les 2 directions
-  L_h Lubrification à vie, sans entretien
-  Lubrification à la graisse
-  Etanche des 2 côtés