

Eaton 185610

Catalog Number: 185610

Eaton Moeller® series C22 Pushbutton, classic, flat, maintained, 1 N/O, white, cable (black) with non-terminated end, 4 pole, 1 m

General specifications



Product Name	Catalog Number
Eaton Moeller® series C22 Pushbutton	185610
EAN	Product Length/Depth
4015081811045	1060 mm
Product Height	Product Width
30 mm	30 mm
Product Weight	Certifications
0.048 kg	VDE 0660
	CSA
	IEC/EN 60947-5-1
	UL
	CE
	CSA Class No.: 321103
	CSA File No.: 165628
	UL 508
	CSA-C22.2 No. 14-18 and No. 94.2-15
	CE marking
	UL Category Control No.: NKCR
	UL File No.: E29184

Product specifications

Type

Pushbutton actuator

Actuator color

White

Actuator function

Maintained

Switching function latching

Electric connection type

Cable

Fitted with:

Front ring

Operating frequency

3600 Operations/h

Pollution degree

3

Climatic proofing

Damp heat, constant, to IEC 60068-2-78

Damp heat, cyclic, to IEC 60068-2-30

Connection to SmartWire-DT

No

Rated impulse withstand voltage (Uimp)

800 V AC

Bezel color

Titanium

Cable material

PUR

Actuating force

5 N

Actuator diameter

29.7 mm

Ambient operating temperature - max

70 °C

Ambient operating temperature - min

-30 °C

Lamp voltage - max

0 V

Resources

Catalogs

[eaton-pushbuttons-signal-towers-sensors-assortment-overview-catalog-ca047003en-en-us.pdf](#)

Declarations of conformity

[DA-DC-00004157.pdf](#)

[DA-DC-00004135.pdf](#)

Drawings

[eaton-operating-c22-pushbutton-dimensions-004.eps](#)

[eaton-operating-button-symbol-013.eps](#)

[eaton-operating-devices-3d-drawing-170.eps](#)

[eaton-operating-c22-pushbutton-3d-drawing.eps](#)

eCAD model

[DA-CE-ETN.C22-DR-W-K10-P62](#)

Installation instructions

[IL047016ZU](#)

Installation videos

[Eaton's RMQ compact solution pilot devices](#)

mCAD model

[DA-CS-c22_d_open_cable](#)

[DA-CD-c22_d_open_cable](#)

Sales notes

[eaton-rmq-mci-multi-color-light-indicator-flyer-fl047005en-en-us.pdf](#)

System overview

[Pilot devices - selection aid](#)

Wiring diagrams

[eaton-operating-c22-pushbutton-wiring-diagram-002.eps](#)

Number of command positions

1

Number of contacts (change-over contacts)

0

Number of contacts (normally closed contacts)

0

Number of contacts (normally open contacts)

1

Bezel material

Plastic

Design

Flat

Classical

Mounting position

As required

Rated conditional short-circuit current (I_q)

1 kA

Connection type

Cable (black) with non-terminated end, 4 pole

Cable length

1 m

Overvoltage category

III

Control circuit reliability

1 failure per 17,000,000 switching operations (statistically determined, at 17 V DC/7 mA: N/O contact

Degree of protection

NEMA 12

IP67/IP69K

Inscription

Blank

Front element type

Flat

Lens type

Round

Shock resistance

30 g, Mechanical, Shock duration 11 ms

Short-circuit protection rating

Max. 4 A gG/gL, Fuse, Contacts

Opening diameter

22.5 mm

Opening height

0 mm

Rated insulation voltage (Ui)

250 V

Rated operational current (Ie) at AC-15, 24 V

4 A

Rated operational current (Ie) at DC-13, 24 V

3 A

Width opening

0 mm

Product category

RMQ compact solution

Ambient storage temperature - max

80 °C

Ambient storage temperature - min

30 °C

Tightening torque

2 Nm, Threaded ring



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia