




---

 PRODUCT-DETAILS

# AF205-30-00-33

## AF205-30-00-33 Contactor




---

**General Information**

Extended Product Type	AF205-30-00-33
Product ID	1SFL527002R3300
EAN	7320500477021
Catalog Description	AF205-30-00-33 Contactor

Long Description	<p>The AF205-30-00-33 is a 3 pole - 1000 V IEC or 600 V UL contactor with Main Circuit Bars, controlling motors up to 110 kW / 400 V AC (AC-3) or 150 hp / 480 V UL and switching power circuits up to 350 A (AC-1) or 300 A UL general use. Thanks to the AF technology, the contactor has a wide control voltage range (100-250 V 50/60 Hz and DC), managing large control voltage variations, reducing panel energy consumptions and ensuring distinct operations in unstable networks. Furthermore, surge protection is built-in, offering a compact solution. AF contactors have a block type design, can be easily extended with add-on auxiliary contact blocks and an additional wide range of accessories. Includes Mounting kit, containing all necessary screws, washers and sockets for connecting the terminals, and screws for mounting the device.</p>
------------------	---

---

**Ordering**

Minimum Order Quantity	1 piece
Customs Tariff Number	85364900

### Popular Downloads

EPLAN Data	9AAC174542_EPLAN
Data Sheet, Technical Information	1SBC100214C0202
Data Sheet, Technical Information (Part 2)	1SAC200017M0002
Instructions and Manuals	1SFC100008M0201
CAD Dimensional Drawing	2CDC001079B0201

### Dimensions

Product Net Width	105 mm
Product Net Depth / Length	169.5 mm
Product Net Height	196 mm
Product Net Weight	2.4 kg

### Technical

Number of Main Contacts NO	3
Number of Main Contacts NC	0
Number of Auxiliary Contacts NO	0
Number of Auxiliary Contacts NC	0
Number of Poles	3P
Rated Operational Voltage	Main Circuit 1000 V
Rated Frequency (f)	Main Circuit 50 Hz
Conventional Free-air Thermal Current (I <sub>th</sub> )	acc. to IEC 60947-4-1, Open Contactors $\Theta = 40\text{ °C}$ 350 A
Rated Operational Current AC-1 (I <sub>e</sub> )	(1000 V) 40 °C 275 A (1000 V) 60 °C 250 A (1000 V) 70 °C 200 A (690 V) 40 °C 350 A (690 V) 70 °C 240 A
Rated Operational Current AC-3 (I <sub>e</sub> )	(415 V) 55 °C 205 A (440 V) 55 °C 205 A (500 V) 55 °C 186 A (690 V) 55 °C 165 A (1000 V) 55 °C 100 A (380 / 400 V) 55 °C 205 A (220 / 230 / 240 V) 55 °C 205 A
Rated Operational Power AC-3 (P <sub>e</sub> )	(415 V) 110 kW (440 V) 132 kW (500 V) 132 kW (690 V) 160 kW (1000 V) 132 kW (380 / 400 V) 110 kW (220 / 230 / 240 V) 55 kW
Rated Breaking Capacity AC-3	8 x I <sub>e</sub> AC-3
Rated Making Capacity AC-3	10 x I <sub>e</sub> AC-3
Short-Circuit Protective	gG Type Fuses 400 A

Devices

Rated Short-time Withstand Current Low Voltage ( $I_{cw}$ )	at 40 °C Ambient Temp, in Free Air, from a Cold State 10 s 1640 A at 40 °C Ambient Temp, in Free Air, from a Cold State 15 min 350 A at 40 °C Ambient Temp, in Free Air, from a Cold State 1 min 670 A at 40 °C Ambient Temp, in Free Air, from a Cold State 1 s 2050 A at 40 °C Ambient Temp, in Free Air, from a Cold State 30 s 947 A
Rated Insulation Voltage ( $U_i$ )	acc. to IEC 60947-4-1 and VDE 0110 (Gr. C) 1000 V acc. to UL/CSA 1000 V
Rated Impulse Withstand Voltage ( $U_{imp}$ )	8 kV
Maximum Electrical Switching Frequency	(AC-1) 300 cycles per hour (AC-2 / AC-4) 150 cycles per hour (AC-3) 300 cycles per hour
Mechanical Durability	5 million
Maximum Mechanical Switching Frequency	300 cycles per hour
Coil Operating Limits	(acc. to IEC 60947-4-1) $U_c$ (at $\theta \leq 70$ °C)
Rated Control Circuit Voltage ( $U_c$ )	50 Hz 100 ... 250 V 60 Hz 100 ... 250 V DC Operation 100 ... 250 V
Coil Consumption	Holding at Max. Rated Control Circuit Voltage 50 Hz 7 V-A Holding at Max. Rated Control Circuit Voltage 60 Hz 7 V-A Pull-in at Max. Rated Control Circuit Voltage 50 Hz 220 V-A Pull-in at Max. Rated Control Circuit Voltage 60 Hz 220 V-A Pull-in at Max. Rated Control Circuit Voltage DC 190 W
Power Loss	at Rated Operating Conditions per Pole 8 W
Operate Time	Between Coil De-energization and NO Contact Opening 37 ... 47 ms Between Coil Energization and NO Contact Closing 25 ... 55 ms
Degree of Protection	acc. to IEC 60529, IEC 60947-1, EN 60529 Auxiliary Terminals IP40
Terminal Type	Main Circuit: Bars
Product Name	Block Contactor

**Technical UL/CSA**

Maximum Operating Voltage UL/CSA	Main Circuit 1000 V
General Use Rating UL/CSA	(1000 V AC) 275 A
Horsepower Rating UL/CSA	(200 ... 208 V AC) Three Phase 30 Hp (200 V AC) Three Phase 60 hp (208 V AC) Three Phase 60 hp (220 ... 240 V AC) Three Phase 30 Hp (220 ... 240 V AC) Three Phase 75 hp (440 ... 480 V AC) Three Phase 75 Hp (440 ... 480 V AC) Three Phase 150 hp (550 ... 600 V AC) Three Phase 100 Hp (550 ... 600 V AC) Three Phase 200 hp

**Environmental**

Ambient Air Temperature	Close to Contactor Fitted with Thermal O/L Relay (0.85 ... 1.1 $U_c$ ) -25 ... 55 °C Close to Contactor without Thermal O/L Relay (0.85 ... 1.1 $U_c$ ) -40 ... 70 °C Close to Contactor for Storage -40 ... 70 °C
Maximum Operating Altitude Permissible	Without Derating 3000 m

**Material Compliance**

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	2CMT2021-006202
RoHS Declaration	2CMT2021-006277
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
Toxic Substances Control Act - TSCA	2CMT2023-006525
WEEE B2C / B2B	Business To Business
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

## ABB EcoSolutions

End Of Life Disassembling Instructions	1SFC100112M0001
Environmental Product Declaration - EPD	1SFC100095D0201

## Certificates and Declarations

A2L Certificate – UL	9AKK108468A6695
ABS Certificate	14-LD1092198-PDA
BV Certificate	BV_36353_A0BV
CB Certificate	SE-82315
CCS Certificate	GB14T00030
CQC Certificate	CQC2014010304676685 CQC2014010304724672
Declaration of Conformity - CCC	2020980304001306 2020980304001071
Declaration of Conformity - CE	2CMT2015-005439
Declaration of Conformity - UKCA	2CMT2020-006118
DNV Certificate	DNV_E-14043
EAC Certificate	9AKK107046A8618
GL Certificate	GL_95072-14HH
KC Certificate	9AKK107046A9912
LR Certificate	LR_14_70011(E1)
PRS Certificate	TE_2092_880423_16
RINA Certificate	ELE060313XG_002
RMRS Certificate	9AKK107045A6978
UL Certificate	20121023-E36588
UL Listing Card	UL_E36588

## Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	160 mm
Package Level 1 Depth / Length	258 mm
Package Level 1 Height	235 mm
Package Level 1 Gross Weight	3 kg
Package Level 1 EAN	7320500477021

---

**External Classifications and Standards**

---

Object Classification Code		Q
ETIM 7	EC000066 - Power contactor, AC switching	
ETIM 8	EC000066 - Power contactor, AC switching	
ETIM 9	EC000066 - Power contactor, AC switching	
eClass		V11.0 : 27371003
UNSPSC		39121529
IDEA Granular Category Code (IGCC)		4758 >> Iec Contactors
E-Number (Finland)		3707504

---

---

**Categories**

---

Low Voltage Products and Systems → Control Products → Contactors → Block Contactors → AF Contactors → AF205

