




Connectors > Automotive Connectors > Automotive Connector Accessories > Other Automotive Connector Accessories



Primary Product Color: **Gold**
Primary Product Material: **Copper Alloy**
Automotive Connector Accessory Type: **Clip**
Operating Temperature Range: **-30 – 80 °C [-22 – 176 °F]**

Features

Product Type Features

Automotive Connector Accessory Type	Clip
-------------------------------------	------

Body Features

Primary Product Color	Gold
Primary Product Material	Copper Alloy

Usage Conditions

Operating Temperature Range	-30 – 80 °C[-22 – 176 °F]
-----------------------------	---------------------------

Industry Standards

UL Flammability Rating	UL 94HB
------------------------	---------

Packaging Features

Packaging Method	Bag
Packaging Quantity	2000

Other

Serviceable	Yes
-------------	-----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold







EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1612121-5 SQUIB 2POS PLUG HSG	 TE Part # 1612121-3 SQUIB PLUG HSG	 TE Part # 1612121-1 SQUIB 2POS PLUG HSG	 TE Part # 1376688-1 11DIA SQUIB SLIM PLUG HSG YELL
 TE Part # 1473139-1 SQUIB 11DIA MK-2 PLUG HSG	 TE Part # 1612120-1 11DIA SQUIB SLIM MK-2 PLUG HSG	 TE Part # 1612120-3 11DIA SQUIB SLIM MK-2 PLUG HSG	 TE Part # 1827120-1 SQUIB LOCKING BUTTON





TE Part # 1376688-3

11DIA SQUIB SLIM PLUG HSG ORNG



TE Part # 1612121-4

SQUIB 2POS PLUG HSG

Also in the Series

AMP Auto Squib Products



Automotive Connector Caps & Covers (2)




Automotive Housings(12)




Automotive Terminals(1)



Connector Contacts(1)



Other Automotive Connector Accessories(19)



PCB Headers & Receptacles(1)



Power Contacts(1)

Customers Also Bought



TE Part #5-1703884-1

2POS,SHORT CIRC SPR,HOUSING, ASSY



TE Part #1-1703884-1

2POS,SHORT CIRC SPR,HOUSING, ASSY



TE Part #1-1823640-1

SHORT CIRC PLUG,AK2,ASSY



TE Part #1473369-4

SQUIB 11DIA SCR ASSY 8.8MM TYP



TE Part #1-1703885-1

2POS,SHORT CIRC SPR,HOUSING



TE Part #2-1703884-1

2POS,SHORT CIRC SPR,HOUSING, ASSY




TE Part #1-1473369-4

SQUIB 11DIA SCR ASSY 8.8MM TYPE



TE Part #1473369-1

SQUIB 11DIA SCR ASSY 8.8MM TYP



Documents

Product Drawings
SQUIB 11DIA SCR ASSY 9.3MM TYP
Japanese

CAD Files
Customer View Model
ENG_CVM_CVM_1376766-3_A.2d_dxf.zip
English
3D PDF
3D
Customer View Model
ENG_CVM_CVM_1376766-3_A.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_1376766-3_A.3d_stp.zip
English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications
SQUIB 11DIA SHORT CIRCUIT RING
Japanese
SQUIB 11DIA SHORT CIRCUIT RING
Japanese
Product Specification
Japanese
Product Specification
Japanese

Instruction Sheets
11DIA SQUIB SCR ASSY
English
Instruction Sheet (non U.S.)
English