

Backpack Vacuum Cleaner XGT®

VC009G

40Vmax • 180 mbar • 2,0 L

XGT® Battery powered HEPA Backpack Vacuum Cleaner.

VC009G has Increased suction power and lower noise with Improved operation switch which allows to check battery remaining capacity and operation mode. Comfortable backpack harness for reduced heat built-up. With 3 modes : (Normal/High/ Powerful).



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Air volume	1,9 m³/min
Max. sealed suction	180 mbar
Suction power	45 / 85 / 165 W
AWS ready	✓
Continuous Use XGT® 40V Max / 4.0 Ah	50 / 26 / 11 min
Continuous use XGT® 40Vmax / 5.0 Ah	55 / 30 / 14 min
Dust Bag Capacity	2,0 L
Sound Pressure Level (L _{pA})	72 dB(A)
Product net weight	3,4 kg
Noise Uncertainty (K Factor)	2,5 dB(A)
Tool weight with battery	4,1 - 5,3 kg
Product Dimensions (L x W x H):	233 x 150 x 375

User benefits

- Auto-start Wireless System (AWS) connects to power tool with Bluetooth
- HEPA Filter is used to capture very fine particles effectively
- 3 modes for suction power with mode memory function
- Brushless maintenance-free and long-life motor
- Battery protection circuit protects against overloading, over-discharging and over-heating

Link to product - www.makita.uk.com



Related products

Other

User manual

Parts drawing