

KHB0250SE5

Plug-in tap off unit, Canalis KH, with switch
disconnecter for DIN fuse size 1, 250A, 3L
+PEN, white RAL9001



Main

Range of product	Canalis
Range compatibility	Canalis KT busbar trunking Canalis KH
Product or component type	Tap-off unit
Busbar trunking compatibility	Canalis KT busbar trunking with KH type plug-in Canalis KHF and KGF busbar trunkingplug-in
[Ie] rated operational current	250 A at 35 °C
Protection type	Switch-disconnector fuse: DIN fuse, size 1
Provided equipment	fuse
Mounting mode	Plug-in with auto-clamping system
Tap-off unit polarity	3L+PEN
Colour	White (RAL 9001)

Complementary

Device application	High power distribution
[Ue] rated operational voltage	500 V
[Ui] rated insulation voltage	500 V
Network frequency	50/60 Hz
Control type	Rotary handle
Electrical connection	Cable clamp terminal - ISO32 150 mm ² (x1) - for L/N Cable clamp terminal - ISO32 70 mm ² (x1) - for PE
Door/cover opening side	Front
Tap-off unit disconnection mode	By drawing out
Standards	IEC 61439-1 IEC 61439-6 IEC 61641
Width	664 mm
Depth	490 mm
Height	403 mm
Net weight	35 kg

Environment

Earthing system	TN-C
IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK08 conforming to IEC 62262

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins