

# AeraMax® SV

H13 HEPA filter captures up to 99.95% of particles as small as 0.1 microns, including allergens, such as pollen, dust, pet dander, and smoke.

## SPECIFICATIONS

Weight (kg)	14.5
Air Delivery (m³/hour)	959
Decibel Rating (dB)	38.3, 45.9, 55.8, 69.5
Power Requirements	220-240v, 50/60 Hz, 0.7A
Power Consumption (W)	5, 9, 21, 85
Air intake / Outlet	Sides / Top
Control Panel	Yes with Change Filter Light Indicator
Sensors	AeraSmart PM2.5 smart sensors which monitor the air quality and automatically adjust the fan speed to keep air purified, moving, and safe
Housing Materials	ABS Plastic
Operating Temperature / Humidity	10-40°C/ 50% - 90% (non-condensing at ambient)
Area coverage (m²)	130 at 3 ACH and 80 at 5 ACH
Filter Type	Pre-filter + Combo Carbon and H13 HEPA
Smoke / Dust / Pollen CADR (m³/hour)	910, 959, 947
Warranty	3-Year Limited
Certifications	Energy Star Certified, AHAM Certified



Item # 9799601  
Dimensions: 793 x 370 x 370mm

## AERAMAX SV REPLACEMENT FILTERS

*Two sets of filters required*


Filter Type	H13 HEPA and Carbon Filter with Pre-Filter
Estimated Filter Life	2 Years
Pack Size	2 sets per pack
Item Number	9787902



# AeraMax SV

## Recyclability:

Percentage of this product and packaging that can be easily separated for recycling



## Energy Usage:

Fan Speed	1	2	3	4	Automatic Mode (AVG 1-3)
Annual kWh	43.80	78.84	183.96	744.60	102.20

The average annual running cost based on 24/7 running time is **£28.62**, based on an energy price calculated at £0.28 per kWh, which is the average electricity price across the UK as of July 2022\*. This is less than half the cost of running a fridge-freezer with an energy rating of A.\*

\*<https://www.confused.com/gas-electricity/guides/appliances-how-much-do-yours-cost-to-run>

## Aftercare:

### Servicing:

Based on the standard filter configuration, the machine will need a replacement filter every 24 months.

### Cleaning:

Wipe over with a damp microfibre cloth. Do not use any cleaning solutions.

### Handling & Storage:

Read and follow all instructions and warnings before use. This product is intended for indoor use only.

### Support:

This unit comes with a 3-year warranty. For product related questions, or further information, our dedicated Customer Service team can be reached at our freephone number 00800 1810 1810.