



Part Number: 8762NH

Audio, Control, and Instrumentation Cable Overall Beldfoil® Shield

[Request Sample](#)

Product Description

20 AWG stranded (7x28) TC conductors, polyethylene insulation, twisted pair, overall Beldfoil® shield (100% coverage), 20 AWG stranded TC drain wire, LSZH jacket.

Technical Specifications

Product Overview

Environmental Space:	Indoor - Euroclass B2ca
Suitable Applications:	Instrumentation and computer cable; For data transmission applications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
20	7x28	TC - Tinned Copper	1

Conductor Count:	2
Conductor Size:	20 AWG

Insulation

Material	Nominal Diameter	Diameter +/- Tolerance	Nominal Wall Thickness
Polyethylene	1.78 mm	0.05 mm	0.016 in

Color Chart

Number	Color
Pair 1	Black & Clear

Outer Shield Material

Type	Material	Material Trade Name	Coverage [%]	Thickness of Foil	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Aluminum/Polyester	Z-fold®	100 %	9 / 12 µm	TC - Tinned Copper	AWG20/7	7x28 mm

Outer Jacket Material

Material	Color	Nominal Diameter	Nominal Wall Thickness
LSZH / FRNC (UV stabilised)	Chrome (RAL 7037)	5.4 mm	0.9 mm

Construction and Dimensions

Stranding

Twists
6 twist/ft

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR
31.2 Ohm/km

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
88.6 pF/m	160.8 pF/m

Inductance

Nominal Inductance	Nominal Pair Inductance
0.18 μ H/ft	0.591 μ H/m

Impedance

Nominal Characteristic Impedance
56 Ohm

Delay

Nominal Velocity of Propagation (VP) [%]
66 %

Current

Element	Max. Recommended Current [A]
Conductor	3.9 A

Voltage

UL Voltage Rating	Voltage Rating [V]
300 V RMS	300 V

Temperature Range

Installation Temp Range:	-15°C To +80°C
UL Temp Rating:	75°C
Storage Temp Range:	-45°C To +80°C
Operating Temp Range:	-30°C To +75°C
Operating Temp Range (Flexible Install):	-15°C To +80°C
Operating Temp Range (Fixed Install):	-45°C To +80°C

Mechanical Characteristics

Oil Resistance:	IEC 60811-404
Bulk Cable Weight:	21 lbs/1000ft
Max Recommended Pulling Tension:	210 N
Min Bend Radius During Installation:	54 mm
Min Bend Radius/Minor Axis:	2 in

Standards

NEC/(UL) Specification:	CMG
CEC/C(UL) Specification:	CMG
CPR Euroclass:	B2ca-s1,d1,a1
CENELEC Compliance:	EN 50290-2-27

Applicable Environmental and Other Programs

EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-01-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
Suitability - Non-Halogenated:	Yes

Flammability, LS0H, Toxicity Testing

C(UL) Flammability:	FT4
UL Flammability:	UL1685 FT4 Loading
ISO/IEC Flammability:	IEC 60332-3-24
Amount of Halogen acc. to IEC 60754-1 & EN50267-1:	Zero

UL voltage rating:	300 V RMS
--------------------	-----------

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color
8762NH.001000	Chrome
8762NH.00152	Chrome
8762NH.00305	Chrome
8762NH.00500	Chrome

History

Revision Number:	6
------------------	---

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.