




Connectors > Contacts > Connector Contacts



Contact Type: **Socket**

Contact Mating Area Plating Material: **Gold (Au)**

Wire Contact Termination Area Plating Material: **Tin**

Operating Voltage: **250 VAC**

Compatible With Wire & Cable Type: **Discrete Wire**

Features

Product Type Features

Applied Pressure	Intermediate
------------------	--------------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Electrical Characteristics

Termination Resistance	12 mΩ
Dielectric Withstanding Voltage (Max)	750 V
Insulation Resistance	5000 MΩ
Operating Voltage	250 VAC

Contact Features

Mating Square Post Dimension	.64 mm[.025 in]
Wire Contact Termination Area Plating Material Finish	Matte
Contact Type	Socket
Contact Mating Area Plating Material	Gold (Au)
Wire Contact Termination Area Plating Material	Tin
Contact Base Material	Copper Tin Phosphor Bronze
Contact Current Rating (Max)	3 A

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------



Product Terminates To

Wire & Cable

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Wire Size	236.823 – 789.41 CMA
-----------	----------------------

Usage Conditions

Operating Temperature Range	-65 – 105 °C[-85 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

Compatible With Approved Standards Products	CSA LR7189, UL E28476
---	-----------------------

Packaging Features

Packaging Method	Loose Piece
Packaging Quantity	1000

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous



materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 843996-3 TOOL, EXTRACTION RESET	TE Part # 91517-1 CCII FEMALE MOD IV REC 24-22 ASSY	TE Part # 58641-2 PROCrimp DIE MOD IV	TE Part # 58641-1 PRO-CRIMP TL & DIE MOD IV


Also in the Series | AMPMODU IV/V

Backplane Connector Housings(1)	Connector Caps & Covers(11)	Connector Contacts(271)	Connector Hardware(10)
Insertion & Extraction Tools(4)	PCB Headers & Receptacles(517)	Power Contacts(207)	


Customers Also Bought

TE Part #5-1879665-2 H8 42K2 0.1% 15PPM	TE Part #1-87456-1 16 MODIV HSG COMP DR .100CL	TE Part #3-640621-2 02P MTA100 CONN ASSY F/T NATL	TE Part #3-2176382-3 RQ 0805 287K 0.1% 10PPM 5K RL





TE Part #5749721-7
68 50SR VERT RCPT ASSY




TE Part #D03269-000
B-155-07-35-22-5



TE Part #6-87756-8
MOD IV RECP LP



TE Part #1-87456-7
22 MODIV HSG COMP DR .100CL



TE Part #87456-5
10 MODIV HSG COMP DR .100CL



TE Part #T4131012121-000
M12,REAR MOUNT,FEMALE,A,12P,
SOLDER WIRE

Documents

Product Drawings

MOD IV RECP LP LF

English

CAD Files

Customer View Model

ENG_CVM_5-103171-5_J.3d_igs.zip

English

Customer View Model

ENG_CVM_5-103171-5_J.3d_stp.zip

English

Customer View Model

ENG_CVM_5-103171-5_J.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMPMODU_INTERCONNECTION_SYSTEM_SECTION5_CONT

English

Product Specifications

Application Specification

English