

Diamond machinist's file hand 125 mm D126 (medium) for hard materials



Diamond machinist's file hand 125 mm D126 (medium) for hard materials

Item number: [15401126](#)

EAN: [4007220255131](#)

Diamond files and sheets are used for tasks where conventional files fail due to the hardness of the material being worked on.

Diamond files and sheets are also used for processing hardened steel. The working temperatures are so low that no chemical wear occurs. This allows the higher hardness of the diamond grain to be exploited for a longer tool life.

Diamond machinist's files are used in many industries, such as the manufacturing of large tools.

They are supplied with ergonomic file handles.

Technical information

Grit size	D 126
Height	4.2 mm
Length, coating	110 mm
Length, total	125 mm
Shape	Hand
Width	11.2 mm

Recommendations for use

- ✔ Apply only slight pressure to the file, especially in workpiece edge areas.
 - ✔ Loaded diamond files can be cleaned in kerosene or anti-static plastic cleaner with a file brush. Alternatively, ultrasonic cleaning is also possible. Often it will suffice to knock the file against a hard object.
 - ✔ Avoid using grease!
-

Ordering notes

- ✔ Customer-specific tool solutions are available on request.

Contents

- ✔ Diamond machinist's files are supplied with ergonomic file handles.

Materials that can be worked

- ✔ Abrasive materials
- ✔ Case-hardened steels
- ✔ Ferrite (magnetic material)
- ✔ Glass
- ✔ Graphite and synthetic carbon
- ✔ Nickel or titanium-based superalloys
- ✔ Steel materials with a hardness > 54 HRC
- ✔ Technical ceramics
- ✔ Tool steels
- ✔ Tungsten carbide

Applications

- ✔ Deburring
- ✔ Finishing
- ✔ Leveling
- ✔ Removing oxide layers
- ✔ Surface work
- ✔ Working on edges
- ✔ Working on edges (chamfering, rounding)

Drive types

- ✔ Manual application
-

**PFERD
TOOLS**



August Rüggeberg GmbH & Co. KG

Hauptstraße 13

51709 Marienheide

+49 2264 9-0

+49 2264 9-400

info@pferd.com