



## SAFETY DATA SHEET

### EVO-STIK EPOXY RAPID RESIN

According to Regulation (EC) No 1907/2006

#### SECTION 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

##### **1.1. Product identifier**

Product name                    EVO-STIK EPOXY RAPID RESIN  
 Product No.                    808522, 808539, 808539A, S808539, 808591

##### **1.2. Relevant identified uses of the substance or mixture and uses advised against**

Identified uses                    Adhesive.

##### **1.3. Details of the supplier of the safety data sheet**

Supplier                        BOSTIK LIMITED  
                                   COMMON ROAD  
                                   STAFFORD  
                                   STAFFORDSHIRE  
                                   ST16 3EH  
                                   +44 1785 272625  
                                   sds.uk@bostik.com

##### **1.4. Emergency telephone number**

+44 1785 272650 (24 Hours)

#### SECTION 2: HAZARDS IDENTIFICATION

##### **2.1. Classification of the substance or mixture**

Classification (EC 1272/2008)

Physical and Chemical Hazards	Not classified.
Human health	Skin Irrit. 2 - H315; Eye Irrit. 2 - H319; Skin Sens. 1 - H317
Environment	Aquatic Chronic 2 - H411

Classification (1999/45/EEC)

Xi;R36/38. R43. N;R51/53.

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

##### **2.2. Label elements**

Contains                        BISPHENOL A-EPICHLORHYDRIN EPOXY RESIN (NUMBER AV MW<700)  
                                   REACTION PRODUCT: BISPHENOL F-(EPICHLOROHYDRIN); EPOXY RESIN

Label In Accordance With (EC) No. 1272/2008



Signal Word                    Warning

Hazard Statements

H315	Causes skin irritation.
H317	May cause an allergic skin reaction.
H319	Causes serious eye irritation.
H411	Toxic to aquatic life with long lasting effects.

Precautionary Statements

P102	Keep out of reach of children.
P103	Read label before use.

# EVO-STIK EPOXY RAPID RESIN

P273	Avoid release to the environment.
P280	Wear protective gloves/protective clothing/eye protection/face protection.
P261	Avoid breathing vapour/spray.
P337+313	If eye irritation persists: Get medical advice/attention.
P403+235	Store in a well-ventilated place. Keep cool.
P501	Dispose of contents/container in accordance with local regulations.
Supplementary Precautionary Statements	
P333+313	If skin irritation or rash occurs: Get medical advice/attention.
P362	Take off contaminated clothing and wash before reuse.
P363	Wash contaminated clothing before reuse.
P321	Specific treatment (see medical advice on this label).
P403+233	Store in a well-ventilated place. Keep container tightly closed.
Supplemental label information	
EUH205	Contains epoxy constituents. May produce an allergic reaction.

## 2.3. Other hazards

### SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS

#### 3.2. Mixtures

BISPHENOL A-EPICHLORHYDRIN EPOXY RESIN (NUMBER AV MW<700)		60-100%
CAS-No.: 25068-38-6	EC No.: 500-033-5	Registration Number: 05-2114287500-52
Classification (EC 1272/2008) Skin Irrit. 2 - H315 Eye Irrit. 2 - H319 Skin Sens. 1 - H317 Aquatic Chronic 2 - H411	Classification (67/548/EEC) Xi;R36/38. N;R51/53. R43.	
gamma-GLYCIDEOXYPROPYLTRIMETHOXYSILANE		1-5%
CAS-No.: 2530-83-8	EC No.: 219-784-2	
Classification (EC 1272/2008) Eye Dam. 1 - H318	Classification (67/548/EEC) Xi;R41.	
REACTION PRODUCT: BISPHENOL F-(EPICHLOROHYDRIN); EPOXY RESIN		5-10%
CAS-No.: 28064-14-4	EC No.:	
Classification (EC 1272/2008) Skin Irrit. 2 - H315 Eye Irrit. 2 - H319 Skin Sens. 1 - H317 Aquatic Chronic 2 - H411	Classification (67/548/EEC) Xi;R36/38. N;R51/53. R43.	

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

### SECTION 4: FIRST AID MEASURES

#### 4.1. Description of first aid measures

##### Inhalation

Remove victim immediately from source of exposure. Move the exposed person to fresh air at once. Get medical attention if any discomfort continues.

##### Ingestion

DO NOT induce vomiting. Get medical attention immediately.

# EVO-STIK EPOXY RAPID RESIN

## Skin contact

Promptly flush contaminated skin with water. Promptly remove clothing if soaked through and flush the skin with water. Get medical attention if irritation persists after washing.

## Eye contact

Rinse the eye with water immediately. Continue to rinse for at least 15 minutes and get medical attention.

## **4.2. Most important symptoms and effects, both acute and delayed**

## **4.3. Indication of any immediate medical attention and special treatment needed**

## **SECTION 5: FIREFIGHTING MEASURES**

### **5.1. Extinguishing media**

Extinguishing media

Use fire-extinguishing media appropriate for surrounding materials.

### **5.2. Special hazards arising from the substance or mixture**

Specific hazards

Fire or high temperatures create: Toxic gases/vapours/fumes of: Carbon dioxide (CO<sub>2</sub>). Carbon monoxide (CO).

### **5.3. Advice for firefighters**

Special Fire Fighting Procedures

Keep run-off water out of sewers and water sources. Dike for water control. If risk of water pollution occurs, notify appropriate authorities.

## **SECTION 6: ACCIDENTAL RELEASE MEASURES**

### **6.1. Personal precautions, protective equipment and emergency procedures**

Avoid skin and eye contact. Ensure adequate ventilation.

### **6.2. Environmental precautions**

Prevent entry into drains and water courses.

### **6.3. Methods and material for containment and cleaning up**

Absorb in vermiculite, dry sand or earth and place into containers.

### **6.4. Reference to other sections**

Wear protective clothing as described in Section 8 of this safety data sheet.

## **SECTION 7: HANDLING AND STORAGE**

### **7.1. Precautions for safe handling**

Avoid spilling, skin and eye contact. Persons susceptible to allergic reactions should not handle this product. Ventilate well, avoid breathing vapours. Use approved respirator if air contamination is above accepted level.

### **7.2. Conditions for safe storage, including any incompatibilities**

Store in tightly closed original container in a dry, cool and well-ventilated place. Keep in original container.

Storage Class

Chemical storage.

### **7.3. Specific end use(s)**

The identified uses for this product are detailed in Section 1.2.

## **SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION**

### **8.1. Control parameters**

Ingredient Comments

WEL = Workplace Exposure Limits

### **8.2. Exposure controls**

# EVO-STIK EPOXY RAPID RESIN

Protective equipment



## Engineering measures

Provide adequate general and local exhaust ventilation.

## Respiratory equipment

No specific recommendation made, but respiratory protection must be used if the general level exceeds the recommended occupational exposure limit.

## Hand protection

Protective gloves should be used if there is a risk of direct contact or splash. Use protective gloves made of: Nitrile.

## Eye protection

Wear splash-proof eye goggles to prevent any possibility of eye contact.

## Other Protection

Wear appropriate clothing to prevent any possibility of liquid contact and repeated or prolonged vapour contact. Provide eyewash station.

## Hygiene measures

DO NOT SMOKE IN WORK AREA! Wash hands at the end of each work shift and before eating, smoking and using the toilet. Wash promptly if skin becomes wet or contaminated. Promptly remove any clothing that becomes contaminated. When using do not eat, drink or smoke.

## SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

### 9.1. Information on basic physical and chemical properties

Appearance	Colourless-pale yellow liquid.
Odour	Slight odour.
Initial boiling point and boiling range (°C)	> 200°C
Relative density	1.15
Flash point (°C)	> 150

### 9.2. Other information

## SECTION 10: STABILITY AND REACTIVITY

### 10.1. Reactivity

### 10.2. Chemical stability

Stable under normal temperature conditions.

### 10.3. Possibility of hazardous reactions

### 10.4. Conditions to avoid

Avoid contact with strong oxidisers. Avoid contact with acids and alkalis.

### 10.5. Incompatible materials

### 10.6. Hazardous decomposition products

Fire or high temperatures create: Carbon monoxide (CO). Carbon dioxide (CO<sub>2</sub>).

## SECTION 11: TOXICOLOGICAL INFORMATION

### 11.1. Information on toxicological effects

#### Inhalation

Vapour may irritate respiratory system or lungs.

# EVO-STIK EPOXY RAPID RESIN

## Ingestion

May cause discomfort if swallowed.

## Skin contact

Liquid may irritate skin. May cause sensitisation by skin contact.

## Eye contact

Irritating to eyes.

## Medical Considerations

Skin disorders and allergies.

## SECTION 12: ECOLOGICAL INFORMATION

### Ecotoxicity

Dangerous for the environment: May cause long-term adverse effects in the aquatic environment.

#### 12.1. Toxicity

#### 12.2. Persistence and degradability

##### Degradability

No data available.

#### 12.3. Bioaccumulative potential

##### Bioaccumulative potential

No data available on bioaccumulation.

#### 12.4. Mobility in soil

##### Mobility:

Semi-mobile.

#### 12.5. Results of PBT and vPvB assessment

#### 12.6. Other adverse effects

Not available.

## SECTION 13: DISPOSAL CONSIDERATIONS

### General information

This material is classified as special waste as defined by Special Waste Regulations 1996 and must be disposed of by an authorised contractor

#### 13.1. Waste treatment methods

Dispose of waste and residues in accordance with local authority requirements.

## SECTION 14: TRANSPORT INFORMATION

#### 14.1. UN number

UN No. (ADR/RID/ADN)	3082
UN No. (IMDG)	3082
UN No. (ICAO)	3082

#### 14.2. UN proper shipping name

Proper Shipping Name	ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (BISPHENOL A-EPICHLOROHYDRIN EPOXY RESIN (NUMBER AV MW<700), BISPHENOL F EPOXY RESIN)
----------------------	---

#### 14.3. Transport hazard class(es)

ADR/RID/ADN Class	9
ADR/RID/ADN Class	Class 9: Miscellaneous dangerous substances and articles.

# EVO-STIK EPOXY RAPID RESIN

ADR Label No.	9
IMDG Class	9
ICAO Class/Division	9
Transport Labels	



## 14.4. Packing group

ADR/RID/ADN Packing group	III
IMDG Packing group	III
ICAO Packing group	III

## 14.5. Environmental hazards

Environmentally Hazardous Substance/Marine Pollutant



## 14.6. Special precautions for user

EMS	F-A, S-F
Emergency Action Code	•3Z
Hazard No. (ADR)	90
Tunnel Restriction Code	(E)

## 14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

### SECTION 15: REGULATORY INFORMATION

#### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Statutory Instruments

The Chemicals (Hazard Information and Packaging for Supply) Regulations 2009 (S.I 2009 No. 716). Control of Substances Hazardous to Health.

Approved Code Of Practice

Safety Data Sheets for Substances and Preparations. Classification and Labelling of Substances and Preparations Dangerous for Supply.

Guidance Notes

Workplace Exposure Limits EH40. CHIP for everyone HSG(108).

EU Legislation

Dangerous Substance Directive 67/548/EEC. Dangerous Preparations Directive 1999/45/EC. Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006 with amendments.

#### 15.2. Chemical Safety Assessment

### SECTION 16: OTHER INFORMATION

General information

This product should be used as directed by Bostik Ltd. For further information consult the product data sheet or contact Technical Services.

## EVO-STIK EPOXY RAPID RESIN

## Information Sources

This safety data sheet was compiled using current safety information supplied by distributor of raw materials.

## Revision Comments

NOTE: Lines within the margin indicate significant changes from the previous revision. This safety data sheet supersedes all previous issues and users are cautioned to ensure that it is current. Destroy all previous data sheets and if in doubt contact Bostik Limited.

Issued By \_\_\_\_\_ Approved EC \_\_\_\_\_

Revision Date January 2015

Revision 2

Date September 2011

## Risk Phrases In Full

R36/38 Irritating to eyes and skin.

R41 Risk of serious damage to eyes.

R43 May cause sensitisation by skin contact

R51/53 Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment

## Hazard Statements In Full

H315 Causes skin irritation

H317 May cause an allergic skin reaction.

H318 Causes serious eye damage.

H319 Causes serious eye irritation.

H411 Toxic to aquatic life with long lasting effects



## SAFETY DATA SHEET

### EVO-STIK EPOXY RAPID HARDENER

According to Regulation (EC) No 1907/2006

#### SECTION 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

##### **1.1. Product identifier**

Product name                            EVO-STIK EPOXY RAPID HARDENER  
 Product No.                            808522, 808539, 808539A, S808539, 808591

##### **1.2. Relevant identified uses of the substance or mixture and uses advised against**

Identified uses                            Powdered Cement / Grout

##### **1.3. Details of the supplier of the safety data sheet**

Supplier                                    BOSTIK LIMITED  
     COMMON ROAD  
     STAFFORD  
     STAFFORDSHIRE  
     ST16 3EH  
     +44 1785 272625  
     sds.uk@bostik.com

##### **1.4. Emergency telephone number**

+44 1785 272650 (24 Hours)

#### SECTION 2: HAZARDS IDENTIFICATION

##### **2.1. Classification of the substance or mixture**

Classification (EC 1272/2008)

Physical and Chemical Hazards	Not classified.
Human health	
Environment	Not classified.

Classification (1999/45/EEC)                    Xi;R41, R43.

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

##### **2.2. Label elements**

Contains                                    AMINES, POLYETHYLENEPOLY-, TRIETHYLENETETRAMINE FRACTION

Label In Accordance With (EC) No. 1272/2008



Signal Word

Danger

Hazard Statements

H315	Causes skin irritation.
H317	May cause an allergic skin reaction.
H318	Causes serious eye damage.

Precautionary Statements

P102	Keep out of reach of children.
P103	Read label before use.
P280	Wear protective gloves/protective clothing/eye protection/face protection.
P261	Avoid breathing vapour/spray.

# EVO-STIK EPOXY RAPID HARDENER

P305+351+338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P333+313	If skin irritation or rash occurs: Get medical advice/attention.
P337+313	If eye irritation persists: Get medical advice/attention.
P501	Dispose of contents/container in accordance with local regulations.
Supplementary Precautionary Statements	
P302+352	IF ON SKIN: Wash with plenty of soap and water.
P310	Immediately call a POISON CENTER or doctor/physician.
P402+404	Store in a dry place. Store in a closed container.
P403+233	Store in a well-ventilated place. Keep container tightly closed.

## 2.3. Other hazards

### SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS

#### 3.2. Mixtures

AMINES, POLYETHYLENEPOLY-, TRIETHYLENETETRAMINE FRACTION	1-5%
CAS-No.: 90640-67-8	EC No.: 292-588-2
Classification (EC 1272/2008)	Classification (67/548/EEC)
Acute Tox. 4 - H302	Xn;R21/22.
Acute Tox. 4 - H312	R43,R52/53.
Skin Sens. 1 - H317	
Aquatic Chronic 3 - H412	
POLYAMIDE RESIN	60-100%
CAS-No.:	EC No.:
Classification (EC 1272/2008)	Classification (67/548/EEC)
Not classified.	Xi;R41.

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

### SECTION 4: FIRST AID MEASURES

#### 4.1. Description of first aid measures

##### Inhalation

Remove victim immediately from source of exposure. Move the exposed person to fresh air at once. Get medical attention if any discomfort continues.

##### Ingestion

DO NOT induce vomiting. Get medical attention immediately.

##### Skin contact

Wash off promptly and flush contaminated skin with water. Promptly remove clothing if soaked through and flush skin with water. Get medical attention if irritation persists after washing.

##### Eye contact

Rinse the eye with water immediately. Continue to rinse for at least 15 minutes and get medical attention.

#### 4.2. Most important symptoms and effects, both acute and delayed

#### 4.3. Indication of any immediate medical attention and special treatment needed

### SECTION 5: FIREFIGHTING MEASURES

#### 5.1. Extinguishing media

##### Extinguishing media

Use fire-extinguishing media appropriate for surrounding materials.

# EVO-STIK EPOXY RAPID HARDENER

## 5.2. Special hazards arising from the substance or mixture

### Specific hazards

Fire creates: Toxic gases/vapours/fumes of: Carbon monoxide (CO). Carbon dioxide (CO2).

## 5.3. Advice for firefighters

### Protective equipment for fire-fighters

Use protective equipment appropriate for surrounding materials.

## **SECTION 6: ACCIDENTAL RELEASE MEASURES**

### 6.1. Personal precautions, protective equipment and emergency procedures

Avoid contact with skin and eyes. Provide adequate ventilation. Avoid inhalation of dust. Use protective gloves, goggles and suitable protective clothing.

### 6.2. Environmental precautions

Do not allow to enter drains, sewers or watercourses.

### 6.3. Methods and material for containment and cleaning up

Collect spillage in containers, seal securely and deliver for disposal according to local regulations.

### 6.4. Reference to other sections

For personal protection, see section 8.

## **SECTION 7: HANDLING AND STORAGE**

### 7.1. Precautions for safe handling

Provide good ventilation. Avoid inhalation of dust and contact with skin and eyes.

### 7.2. Conditions for safe storage, including any incompatibilities

Store in tightly closed original container in a dry, cool and well-ventilated place. Keep in original container.

Storage Class

Chemical storage.

### 7.3. Specific end use(s)

Usage Description

\*IMPORTANT\* Use within time period as indicated on packaging.

## **SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION**

### 8.1. Control parameters

Ingredient Comments

WEL = Workplace Exposure Limits

### 8.2. Exposure controls

Protective equipment



Engineering measures

Provide adequate general and local exhaust ventilation.

Respiratory equipment

In case of inadequate ventilation use suitable respirator.

Hand protection

Protective gloves must be used if there is a risk of direct contact or splash. Use protective gloves made of: Nitrile.

Eye protection

Wear dust resistant safety goggles where there is danger of eye contact.

# EVO-STIK EPOXY RAPID HARDENER

## Other Protection

Provide eyewash station. Wear appropriate clothing to prevent repeated or prolonged skin contact.

## Hygiene measures

DO NOT SMOKE IN WORK AREA! Wash hands at the end of each work shift and before eating, smoking and using the toilet. Promptly remove any clothing that becomes contaminated. Wash promptly with soap & water if skin becomes contaminated. When using do not eat, drink or smoke.

## SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

### 9.1. Information on basic physical and chemical properties

Appearance	Liquid
Colour	Amber.
Odour	Ammonia.
Initial boiling point and boiling range (°C)	> 260°C
Relative density	0.96
Flash point (°C)	> 200°C

### 9.2. Other information

## SECTION 10: STABILITY AND REACTIVITY

### 10.1. Reactivity

No data available

### 10.2. Chemical stability

Stable under normal temperature conditions.

### 10.3. Possibility of hazardous reactions

Not available.

Hazardous Polymerisation

Unknown.

### 10.4. Conditions to avoid

Avoid contact with strong oxidisers.

### 10.5. Incompatible materials

Materials To Avoid

Bases, alkalis (inorganic). Acids, oxidising.

### 10.6. Hazardous decomposition products

Fire or high temperatures create: Carbon monoxide (CO). Carbon dioxide (CO<sub>2</sub>).

## SECTION 11: TOXICOLOGICAL INFORMATION

### 11.1. Information on toxicological effects

#### Inhalation

Irritating to respiratory system.

#### Ingestion

May cause discomfort if swallowed. May cause stomach pain or vomiting.

#### Skin contact

Irritating to skin. May cause sensitisation by skin contact.

#### Eye contact

Risk of serious damage to eyes. Contact with concentrated chemical may very rapidly cause severe eye damage, possibly loss of sight.

# EVO-STIK EPOXY RAPID HARDENER

Medical Considerations  
Skin disorders and allergies.

## SECTION 12: ECOLOGICAL INFORMATION

### Ecotoxicity

The product components are not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment.

#### 12.1. Toxicity

No data available

#### 12.2. Persistence and degradability

##### Degradability

There are no data on the degradability of this product.

#### 12.3. Bioaccumulative potential

##### Bioaccumulative potential

No data available on bioaccumulation.

#### 12.4. Mobility in soil

##### Mobility:

Not relevant, due to the form of the product.

#### 12.5. Results of PBT and vPvB assessment

No data available

#### 12.6. Other adverse effects

Not available.

## SECTION 13: DISPOSAL CONSIDERATIONS

### 13.1. Waste treatment methods

Dispose of waste and residues in accordance with local authority requirements.

## SECTION 14: TRANSPORT INFORMATION

General	The product is not covered by international regulation on the transport of dangerous goods (IMDG, IATA, ADR/RID).
---------	---

#### 14.1. UN number

Not applicable.

#### 14.2. UN proper shipping name

Not applicable.

#### 14.3. Transport hazard class(es)

##### Transport Labels

No transport warning sign required.

#### 14.4. Packing group

Not applicable.

#### 14.5. Environmental hazards

Environmentally Hazardous Substance/Marine Pollutant

No.

#### 14.6. Special precautions for user

