


NO	DESCRIPTION	DATE
△1	ADD VSWR	02.21.13'



1.0 ELECTRICAL

- 1.1 FREQUENCY RANGE: DC-1 GHz
- 1.2 NOMINAL IMPEDANCE: 75 OHM
- 1.3 DC RESISTANCE: 75 OHMS \pm 5%
- 1.4 POWER RATING: 0.5W
- 1.5 VSWR: 1.3 MAX. @500 MHz △1

2.0 MATERIALS

- 2.1 BODIES: BRASS PER JIS-C3604
ZINC
- 2.2 CENTER CONTACT: BRASS PER JIS-C3604
- 2.3 INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710

3.0 FINISHES AND OTHERS

- 3.1 SEE BELOW TABLE FOR DETAILS.

4.0 ENVIRONMENTAL

- 4.1 OPERATING TEMPERATURE RANGE: -20° C TO +70° C

10	CHASSIS	BRASS	1	NICKEL 100 μ " MIN.
9	RESISTOR	1/2W-75 Ω	1	NONE
8	BODY	BRASS	1	NICKEL 100 μ " MIN.
7	WASHER	BRASS	1	NICKEL
6	SPRING WASHER	SK-5	1	NICKEL
5	WASHER	BRASS	1	NICKEL
4	GASKET	RUBBER	1	RED
3	CENTER CONTACT	BRASS	1	GOLD
2	INSULATION	TEFLON	1	NONE
1	SHELL	ZINC	1	NICKEL
NO	DESCRIPTION	MATERIAL	Q'TY	FINISH

APPROVED

by _____

DATE: _____



DESCRIPTION		BNC STRAIGHT PLUG TERMINATOR							
製圖	DRAWN	TOLERANCE		品名	13-52-3 T.G.Z	日期	DATE	版次	REV.
	Yoko	.X	± 0.2	TITLE	\ROHS COMPLIANT (75 Ω)				
檢圖	CHECK	.XX	± 0.1	單位	mm(in)	DWG.NO.	13-0254		
	Arc	.XXX	± 0.05	SCALE					
認定	APPROVAL	ANGLE	$\pm 5^\circ$	比例	4:1				
	Angela								