




OPEN ENDED SPANNERS

6 "Strong and accurate"

- ✔ Carefully forged and professionally machined:
- ✔ Powerful jaws: ground precisely to exact nominal size for optimum contact areas
- ✔ High bending strength - does not fracture or splinter when overloaded, thus minimising the risk of injury
- ✔ Overloading indicated by deformation
- ✔ Secure grip thanks to slim profile shaft
- ✔ Non-glare matt chrome-plated finish
- ✔ Top-grade industrial quality for the hardest of continuous use

Spanner sizes:

- ✔ Metric dimensions: 4x4.5 - 55x60 mm
- ✔ Imperial dimensions: 1/4x5/16" - 2.1/4x2.7/16"
- ✔ Whitworth dimensions: 1/8x3/16W - 7/8x1"




mm	"AF	Whitw.
4 x 4.5	1/4" x 5/16"	1/8" x 3/16"
55 x 60	2 1/4" x 2 7/16"	7/8" x 1"

6

DOUBLE OPEN ENDED SPANNER

- ✔ Acc. to DIN 3110, ISO 3318, ISO 1085, ISO 10102
- ✔ Slim pattern, oval shaft
- ✔ GEDORE vanadium steel 31CrV3, heads finely polished, chrome-plated
- ✔ * not standardised

mm



Code	No.	*	(*)	mm	L	a	b ₁	b ₂	↕	⊞	£
6063400	6 4x4,5	*		4 x 4,5	100	3.4	13.0	14.0	14	10	
6063590	6 4x5	*		4 x 5	100	3.4	13.0	14.0	13	10	
6063670	6 5x5,5	*		5 x 5,5	100	3.4	14.5	16.0	16	10	
6063750	6 5,5x7	*		5,5 x 7	122	3.5	16.0	17.5	23	10	
6063830	6 6x7	*		6 x 7	122	3.5	16.5	17.5	22	10	
6063910	6 6x8	*		6 x 8	122	3.5	16.5	20.0	25	10	
6064050	6 7x8	*		7 x 8	140	3.8	17.5	20.0	34	10	
6064130	6 7x9	*		7 x 9	140	3.8	17.5	22.0	35	10	
6064210	6 8x9	*		8 x 9	140	3.8	20.0	22.0	35	10	
6064480	6 8x10	*		8 x 10	140	4.0	20.0	23.5	36	10	
6064560	6 9x10	*		9 x 10	157	4.5	22.0	23.5	46	10	
6064640	6 9x11	*		9 x 11	157	4.5	22.0	26.5	50	10	
6064720	6 10x11	*		10 x 11	157	4.5	23.5	26.5	50	10	
6064800	6 10x12	*		10 x 12	157	4.5	23.5	28.0	51	10	
6064990	6 10x13	*		10 x 13	172	5.0	23.5	30.5	65	10	
6065020	6 10x14	*		10 x 14	172	5.0	23.5	32.0	67	10	
6065100	6 11x13	*		11 x 13	172	5.0	26.5	30.5	68	10	
6065290	6 11x14	*		11 x 14	172	5.0	26.5	32.0	72	10	
6065370	6 12x13	*		12 x 13	172	5.0	28.0	30.5	69	10	
6065450	6 12x14	*		12 x 14	172	5.0	28.0	32.0	76	10	
6065530	6 13x14	*		13 x 14	178	5.0	30.5	32.0	81	10	
6065610	6 13x15	*		13 x 15	188	5.5	30.5	34.5	98	10	
6068980	6 13x16	*		13 x 16	190	5.5	30.5	35.5	98	10	
6065880	6 14x15	*		14 x 15	188	5.5	32.0	34.5	95	10	
6065960	6 13x17	*		13 x 17	205	6.0	30.5	38.5	122	10	
6066180	6 14x17	*		14 x 17	205	6.0	32.0	38.5	119	10	
6066260	6 16x17	*		16 x 17	205	6.0	35.5	38.5	128	10	
6066340	6 16x18	*		16 x 18	205	6.0	35.5	40.5	129	10	

Code	No.	*	(*)	mm	L	a	b ₁	b ₂	↕	⊞	£
6066420	6 17x19	*		17 x 19	222	6.5	38.5	43.0	168	10	
6066500	6 18x19	*		18 x 19	222	6.5	40.5	43.0	174	10	
6069360	6 18x21	*		18 x 21	236	7.0	40.5	46.0	196	10	
6066690	6 17x22	*		17 x 22	236	7.0	38.5	48.5	205	10	
6066770	6 19x22	*		19 x 22	236	7.0	43.0	48.5	219	10	
6066850	6 20x22	*		20 x 22	236	7.0	44.5	48.5	213	10	
6066930	6 19x24	*		19 x 24	250	7.5	43.0	53.5	256	10	
6067070	6 21x23	*		21 x 23	247	7.5	46.0	50.0	245	10	
6069440	6 21x24	*		21 x 24	250	7.5	46.0	53.5	268	10	
6067150	6 22x24	*		22 x 24	250	7.5	48.5	53.5	260	10	
6067230	6 22x27	*		22 x 27	266	8.0	48.5	60.0	336	10	
6067310	6 24x26	*		24 x 26	266	8.0	53.5	56.5	321	10	
6067580	6 24x27	*		24 x 27	266	8.0	53.5	60.0	337	10	
6067660	6 24x30	*		24 x 30	280	8.5	53.5	63.5	390	10	
6067740	6 25x28	*		25 x 28	280	8.5	55.0	60.0	378	10	
6067820	6 27x29	*		27 x 29	302	9.0	60.0	63.5	456	10	
6067900	6 27x30	*		27 x 30	302	9.0	60.0	63.5	466	10	
6068040	6 27x32	*		27 x 32	302	9.0	60.0	68.0	487	10	
6068120	6 30x32	*		30 x 32	302	9.0	63.5	68.0	504	10	
6069520	6 30x34	*		30 x 34	302	9.0	63.5	72.0	503	10	
6068200	6 30x36	*		30 x 36	328	9.4	63.5	76.0	677	1	
6068390	6 32x36	*		32 x 36	328	9.4	68.0	76.0	594	1	
6069600	6 34x36	*		34 x 36	328	9.4	71.0	75.0	624	1	
6068470	6 36x41	*		36 x 41	360	10.0	76.0	84.5	770	1	
6068550	6 38x42	*		38 x 42	360	10.0	77.0	86.0	784	1	
6068630	6 41x46	*		41 x 46	400	10.7	86.5	95.5	1104	1	
6068710	6 46x50	*		46 x 50	450	11.6	95.5	102.0	1445	1	
2312107	6 55x60	*	(*)	55 x 60	560	18.0	113.0	123.0	3160	1	