Technical Data Sheet





Page 1

GDPHHigh Powered Airduster

GDPH is a non-flammable, high powered airduster, designed for the safe removal of dust and airborne contamination from very delicate or inaccessible areas of electrical and electronic equipment. It may also assist in drying operations after cleaning to remove rinse water, for example. GDPH contains a non-flammable, fluorinated propellant that combines the low GWP (global warming potential) of hydrocarbons with the ultra-low MIR (maximum incremental reactivity) and POCP (photochemical ozone creation potential) of hydrofluorocarbons.

- High power, inert, pure compressed gas for dust removal; ideal for maintenance engineers
- Powerful initial blast with minimal drop in pressure; heavy duty actuator and extension tube
- Ideal for the removal of dust and dirt from delicate and inaccessible areas
- Non-flammable, environmentally friendly propellant; Low GWP, MIR and POCP values

Typical Properties

Colour	Colourless
Flash Point (°C)	None
Boiling Point (°C)	-19
GWP (vs. CO ₂ , 100yr ITH)	6
Photochemical Reactivity (MIRg O ₃ /gVOC)	0.09
Photochemical Ozone Creation Potential (POCP)	6.4

<u>Description</u>	<u>Packaging</u>	Order Code	Shelf Life
GDPH Airduster	400ml Aerosol	GDPH400	48 months

Directions for Use

GDPH should be used in a vertical position or at an angle of not greater than 60° to the vertical otherwise a freezing effect will result.

Caution: Do not use GDPH for prolonged blasts as the surface of the can will form frost.

Revision 1: Jan 2014

Copyright Electrolube 2013

All information is given in good faith but without warranty. Properties are given as a guide only and should not be taken as a specification.

Electrolube cannot be held responsible for the performance of its products within any application determined by the customer, who must satisfy themselves as to the suitability of the product.

Ashby Park, Coalfield Way, Ashby de la Zouch, Leicestershire LE65 1JR T +44 (0)1530 419 600 F +44 (0)1530 416 640 BS EN ISO 9001:2008 Certificate No. FM 32082