

PRODUCT-DETAILS

DS202C C16 A30

DS202C C16 A30 Residual Current Circuit Breaker with Overcurrent Protection



General Information

Extended Product Type	DS202C C16 A30
Product ID	2CSR252140R1164
EAN	8012542122654
Catalog Description	DS202C C16 A30 Residual Current Circuit Breaker with Overcurrent Protection
Long Description	The DS202C series RCBO is a 2P in two-modules device for the protection of end user single-phase circuits against overload and short-circuit currents. Protection against the effects of sinusoidal alternating and direct pulsating earth fault currents. Protection against indirect contacts and additional protection against direct contacts (with sensitivity = 30 mA).

Technical

Standards	IEC 61009-1 IEC 61009-2-1 EN 61009-1 EN 61009-2-1
Tripping Characteristic	C
Type of Residual Current	A type
Rated Voltage (U_r)	230-240 V AC
Rated Operational Voltage	230 / 240 V AC
Rated Insulation Voltage (U_i)	500 V
Rated Impulse Withstand Voltage (U_{imp})	4 kV

Input Voltage Type	AC
Rated Current (I_n)	16 A
Rated Residual Current	30 mA
Rated Short-Circuit Capacity (I_{cn})	6 kA
Rated Ultimate Short-Circuit Breaking Capacity (I_{cu})	10 kA
Rated Conditional Short-Circuit Current (I_{nc})	10 kA
Rated Service Short-Circuit Breaking Capacity, in % of I_{cu} (I_{cs})	6 kA
Leakage Current Type	A
Frequency (f)	50/60 Hz
Rated Frequency (f)	50/60 Hz
Power Loss	3.4 W
Power Supply Connection	Arbitrary
Energy Limiting Class	3
Electrical Endurance	10000 cycle 20000 cycle
Number of Poles	2
Number of Protected Poles	2
Operating Characteristic	Instantaneous
Overvoltage Category	III
Position of Neutral Terminals	Right Left
Earthing Switch Type	Undelayed
Release Type	C
Options Provided	None
Accessories Available	Yes
Connecting Capacity	Busbar 10 mm ² Rigid 25 ... 25 mm ² Flexible 25 ... 25 mm ²
Rated Cross-Section	4 - Multi-Wired 1...25 mm ² 1 - Solid-Core 25...25 mm ²

Environmental

Ambient Temperature	-25...55 °C
Ambient Air Temperature	Operation -25...55 °C
Degree of Protection	IP2X
Pollution Degree	2
RoHS Status	Following EU Directive 2011/65/EU
Environmental Information	9AKK107680A8583

Technical UL/CSA

Short-Circuit Current Rating (SCCR)	0.03 A
-------------------------------------	--------

Dimensions

Width in Number of Modular Spacings	2
-------------------------------------	---

Product Net Width	0.035 m
Product Net Height	0.085 m
Product Net Depth / Length	0.069 m
Product Net Weight	0.225 kg
Built-In Depth (t ₂)	69 mm

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	106 mm
Package Level 1 Height	40 mm
Package Level 1 Depth / Length	80 mm
Package Level 1 Gross Weight	0.239 kg
Package Level 1 EAN	8012542122654
Package Level 2 Units	box 5 piece
Package Level 2 Width	0.200 m
Package Level 2 Height	0.106 m
Package Level 2 Depth / Length	0.080 m
Package Level 2 Gross Weight	1.125 kg
Package Level 2 EAN	8012542122661

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85363010
E-Number (Finland)	3259957
Replacement Product ID (NEW)	2CSR752140R1164
Country of Origin	Italy (IT)

Certificates and Declarations (Document Number)

Declaration of Conformity - CE	9AKK106713A5589
Environmental Information	9AKK107680A8583
Instructions and Manuals	9AKK106354A0766
RoHS Information	2CSC422002K2701

Popular Downloads

Data Sheet, Technical Information	9AKK107991A8329
Instructions and Manuals	9AKK106354A0766

Classifications

ETIM 7	EC000905 - Earth leakage circuit breaker
ETIM 8	EC000905 - Earth leakage circuit breaker
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

WEEE B2C / B2B	Business To Consumer
CN8	85363030
Object Classification Code	F

Accessories

Identifier	Description	Type	Quantity	Unit Of Measure
2CDS200912R0001	S2C-H6R Auxiliary Contact	S2C-H6R	1	piece
2CDS200922R0001	S2C-S/H6R Signal / Auxiliary Contact	S2C-S/H6R	1	piece
2CDS200946R0001	S2C-H6-11R Auxiliary Contact	S2C-H6-11R	1	piece
2CDS200946R0002	S2C-H6-20R Auxiliary Contact	S2C-H6-20R	1	piece
2CDS200946R0003	S2C-H6-02R Auxiliary Contact	S2C-H6-02R	1	piece
2CSR201997R0013	DS2C-CM Motor operating device	DS2C-CM	1	piece
2CSS200910R0005	S2C-OVP1 Overvoltage release	S2C-OVP1	1	piece
2CSS200911R0002	S2C-UA 24 AC Undervoltage release	S2C-UA 24 AC	1	piece
2CSS200911R0003	S2C-UA 48 AC Undervoltage release	S2C-UA 48 AC	1	piece
2CSS200911R0004	S2C-UA 110 AC Undervoltage release	S2C-UA 110 AC	1	piece
2CSS200911R0005	S2C-UA 230 AC Undervoltage release	S2C-UA 230 AC	1	piece
2CSS200933R0011	F2C-A1 Shunt trip	F2C-A1	1	piece
2CSS200933R0012	F2C-A2 Shunt trip	F2C-A2	1	piece
2CSS200993R0005	S2C-OVP2 Overvoltage release	S2C-OVP2	1	piece
2CSS200999R0001	S2C-EST Plug-in base	S2C-EST	1	piece

Categories

Low Voltage Products and Systems → Modular DIN Rail Products → Residual Current Devices RCDs → Residual Current Circuit Breakers with Overcurrent Protection RCBO

