

REGULOG TABLES

CHARACTERISTICS OF METAL STRUCTURE

The electrically height-adjustable REGULOG table is supported by two sheet steel bases, each with a thickness of 40/10th and a tube size of 25 x 25mm, equipped with two height-setting jacks. These bases provide support for the two electrically controlled telescopic lift columns used by the operator for precise height adjustment. A sheet steel crossmember, with a thickness of 12/10th, positioned between the two columns, ensures excellent frame rigidity. Additionally, a C-shaped sheet steel with a thickness of 25/10th, connecting the two columns at the top, serves as a housing for the control box and all connection cables. The height adjustment range is from 700 to 1100mm, excluding the worktop thickness.

The frame is finished with a fine-textured structured epoxy powder paint, oven-polymerised at 180°C. The height adjustment columns are coated with smooth epoxy paint.

Dimensions: Widths: 750 (exclusively with a depth of 750mm), 1000, 1200, 1500, 1800, 2000, and 2400mm. Depths: 750 and 1000mm.

Remote-control: Remote control benefits from combination of a modern design and intuitive, convenient use. Up and down keys have been designed so that they can be recognised by touch without having to look at them when in use, thanks to the chrome-finished and embossed symbols.

This remote-control is foreseen with a 1700mm long cable with RJ45 plug.

ASSOCIATION OF FRAME AND WORKTOP

The REGULOG frame is designed to accommodate 28mm and 19mm melamine worktops, as well as 24mm plywood worktops, as detailed in the workbench worktop description pages. The worktop is fastened to the frame with VBA TB 5x20 wood screws.

EQUIPMENT (See range on pages 126 to 155)

The following equipment is available for the upper section: superstructure uprights, perforated panels, magnetic whiteboard, holder for 10 A4 sleeves, shelves, grab container support rails, monitor supports, electrical power strips.


Equipment available for the lower part includes: retractable keyboard stand, 1 drawer unit, rubbish bag stand.

Upon request, tables can be equipped with 4 castors with a diameter of 100mm, 2 of which are braked, to replace floor level adjustment cylinders.

LABELS

Worktops are PEFC certified.

The evenly distributed admissible load for the REGULOG is 140kg (dynamic load).



In compliance with standard XPD 65762

Colour chart: