




Connectors > Rectangular Connectors > Standard Rectangular Connectors



Connector Product Type: **Housing**

Connector & Housing Type: **Plug, Receptacle**

Termination Method to Wire & Cable: **Crimp**

Connector System: **Wire-to-Wire**

Contact Retention Within Housing: **Without**

Features

Product Type Features

Compatible With Discrete Wire Type	Stranded
Connector Product Type	Housing
Connector & Housing Type	Plug, Receptacle
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	1
Number of Rows	1

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Body Features

Primary Product Color	White
-----------------------	-------



Contact Features

Contact Type	Blade
Contact Retention Within Housing	Without

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Panel Mount Feature	Without
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	Polycarbonate
------------------	---------------

Dimensions

Connector Width	17.15 mm[.675 in]
Wire Size	6 AWG
Connector Height	17.15 mm[.675 in]
Connector Length	48 mm[1.89 in]

Usage Conditions

Operating Temperature Range	-20 – 105 °C[-4 – 221 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards


Compatible With Agency/Standards Products	UL
UL Rating	Recognized
Compatible With Approved Standards Products	UL E28476
Glow Wire Rating	Standard Part - Not Glow Wire
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	300
Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>





EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 1445716-3
KIT 6AWG WHITE


Also in the Series | AMP Power Series - 75



Rectangular Connector Housings(9)




Rectangular Power Connectors(16)




Standard Rectangular Connectors(16)




Customers Also Bought




TE Part #2-320559-4
SPLICE BUTT PIDG 22-16; TAPE




TE Part #4-794678-2
12P MICRO MNL ASSY,R/A,THRU,LF




TE Part #1600903-1
2NDARY RCPT PWR VERT BLKHED MT




TE Part #1600914-5
HARDWARE KIT PANEL MT MULTIBEA




TE Part #1600902-1
INSERT MBXL 2 SIGNAL LOCK 4POS




TE Part #8-35247-2
TERMINAL,SOLIS R 8 1/4




TE Part #1-1600961-7
CONT 12-16 AWG PWR, MFBL PLATE



TE Part #5102159-2
A/L UNIV HDR 14P RA



TE Part #5531216-5
CONTACT MINI TANDEM SPRING L



TE Part #5557730-1
MJ,TE,8P/8C,SHLD,PINL STOPS&G

Documents

Product Drawings
75A HSG SUBASY WHITE

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1445715-3_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1445715-3_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1445715-3_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



Datasheets & Catalog Pages

POWER_CONNECTORS_CATALOG_SEC02_CABLE_MOUNTED

English

2_PIECE_POWER_CONNECTORS_qrg_4-1773458-1

English

Product Specifications

Application Specification

English

Agency Approvals

Agency Approval Document

English