

Product information Mechanical risks

uvex phynomic ESD//60058



Description

The uvex phynomic ESD is a light safety glove for work in antistatic areas. The conductive polyamide/carbon liner and the conductive aqua-polymer impregnation enables excellent dexterity. The coating is extremely flexible and provides a very high level of breathability.

Characteristics

- anti-static safety gloves
- Meets the requirements of EN 16350: 2014 (Conditions: contact resistance $< 10^8$ Ohm, ambient temperature $23^{\circ}\text{C} \pm 1^{\circ}\text{C}$, air humidity $25\% \pm 5\%$)
- excellent dexterity
- Excellent dry grip
- Very high level of breathability

Applications

- ESD areas
- precision assembly work
- For work in antistatic areas
- precision work



pure standard



EN 388



2121

MADE IN GERMANY 



Manufacturer

UVEX SAFETY Gloves GmbH & Co. KG
Elso-Klöver-Str. 6
21337 Lüneburg
Postfach 24 47 · 21314 Lüneburg
GERMANY
Tel.: +49 4131 9502-0
Fax: +49 4131 84338
Email: gloves@uvex.de
Website: uvex-safety.de

Product name	uvex phynomic ESD
EN	388 (2 1 2 1)
Sizes	5, 6, 7, 8, 9, 10, 11, 12
Construction	conductive aqua polymer impregnation on palm and fingertips, knitted cuff
Basic glove	polyamide/ elastane /carbon
Coating	conductive aqua-polymer impregnation
Colour	grey/grey
Resistance	for dry areas of application
Product code	60058