

60mm Tower ROG Pole Buzzer Flash

Local distributor code:

403035672 XVC6B35S

EAN Code: 3606480032660

Main

Range of product	Harmony XVC6	
Product or component type	Complete pre-wired monolithic tower light	
Beacon or indicator bank unit type	3 illuminated units	
Sound signalling	Buzzer	
Mounting diameter	60 mm	
Component name	XVC	
Light source	LED steady or flashing red LED steady or flashing orange LED steady or flashing green	
[Us] rated supply voltage	24 V	
Supply circuit type	AC/DC	
Noise level	7085 dB (continuous or intermittent tone) at 1 m	

Complementary

Material	Polycarbonate: illuminated unit ABS (acrylonitrile butadiene-styrene): base unit PBT + ABS (UL94HB): top cover STK (chromium-plated): support tube	
Product mounting	On support tube, 22 mm	
Cable cross section	0.33 mm²	
AWG gauge	AWG 22	
Cable length	550 mm	
Marking	CE	
[Uimp] rated impulse withstand voltage	0.8 kV	
Current consumption	115 mA	
Fundamental frequency	2.23 kHz	
Flashing frequency	1 Hz	
Net weight	0.98 kg	
Height	563.1 mm	

Environment

Product certifications	IEC 61000-6-4	
	IEC 61000-6-2	
Standards	IEC 61000-6-3	

Protective treatment	тс	
Ambient air temperature for storage	-3570 °C	
Ambient air temperature for operation	-1050 °C	
Electrical shock protection class	S Class I conforming to IEC 61140	
IP degree of protection	IP23 vertical surface installation conforming to IEC 60529	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.000 cm
Package 1 Width	74.900 cm
Package 1 Length	9.000 cm
Package 1 Weight	900.000 g
Unit Type of Package 2	P06
Number of Units in Package 2	30
Package 2 Height	75.000 cm
Package 2 Width	60.000 cm
Package 2 Length	80.000 cm
Package 2 Weight	35.000 kg

Logistical informations

Country of origin ID

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint		
Total lifecycle Carbon footprint	30	

Use Better

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)

Use Again

12 Aug 2025


○ Repack and remanufacture		
Take-back	No	

Dimensions Drawings

Pre-assembled and Pre-wired Tower Light with Support Tube Mounting

Dimensions

Below drawing shows the maximum configuration of the product. Select the number of stages according to the product characteristics in order to get **b1** dimension.




No. of illuminated units	b1 With buzzer (mm)	b1 With buzzer (in.)
1 stage	483.1	19.02
2 stages	523.1	20.59
3 stages	563.1	22.17
4 stages	603.1	23.74
5 stages	643.1	25.32

Mounting and Clearance

Pre-assembled and Pre-wired Tower Light

Support Tube Mounting



Technical Illustration

Dimensions




Image of product / Alternate images

Alternative











