



TCT WRECKER 300mm x 6 Tpi - 1 pc

MULTI MATERIAL : HEAVY DUTY WRECKER™ CARBIDE TEETH DEMOLITION BLADES

- The multi material WRECKER™ with carbide teeth cuts all from thick metal, cast iron, nail embedded wood, hardened screws and fastners.
- Up to 50x longer life than standard Bi -metal blades. Carbide teeth deliver long life and extreme durability in the toughest applications.
- Up to 25% more cuts per charge vs. standard Bi-Metal blades. Optimised for use with cordless tools.
- FANG TIP™: For faster plunge cutting and reaching into restricted areas.
- Thick 1.27mm robust blade body for precise straight cuts.
- 25 mm blade height for improved stability and minimum vibration.
- Best for multi material demolition -cwood with nails or hardened fastners and thick metal



Article Number	48475243
Blade length (mm)	300
Materials suited for	Thick metal > 4 mm Medium metal 1.5 - 4 mm Cast Iron Non ferrous metal (Cu/Al) Wood with nails & screws
Max. cutting capacity cast iron pipes [mm]	ø 10 - 250
Max. cutting capacity metal pipe	ø 10 - 250
Max. cutting capacity non ferrous metals [mm]	6 - 14
Max. cutting capacity steel (mm)	6 - 14