







# 9007C52B2

## **LIMIT SWITCH 600V 10AMP C +OPTIONS**





## Download your 9007C52B2 datasheet



#### Characteristics | Documents & Downloads

Main ————————————————————————————————————	Н	lie	d	le	е	è	
---	---	-----	---	----	---	---	--

9007 Range of product Series name Heavy duty Product or component type Limit switch **Product specific application** Compact box Device short name 9007C **Body type** Plug-in Head type Rotary head Material Metal Fixing mode By the body

Movement of operating head Rotary

Type of operator Zinc spring return without operating lever (-) 9007C lever

Switch actuation From left and right CW and CCW

Type of approach 1 or 2 programmable direction lateral approach **Electrical connection** (AWG 22...AWG 12) screw-clamp terminals, 1...2 1 entry for 1/2" - 14 NPT conforming to ANSI B1.20.1 Cable entry

Number of poles Contacts type and

composition

NC-NO

**Contacts operation** Snap action Positive opening Without Sale per indivisible quantity

#### Complementary

Hide

**Body material** Zinc **Head material** Zinc Function available

Switch function SPDT-DB **Contact form** Form Z Contacts material Silver contacts (1-2)NC **Terminals description ISO** 

(3-4)NO

Maximum actuation speed 90 ft/min with 45° cam angle, levers only 130 ft/min with 30° cam angle, levers only

10° Tripping angle Maximum displacement 90°

angle

Repeat accuracy +/- 0.002 in linear travel of cam

1.2 A at 600 V AC, A600 conforming to NEMA [le] rated operational current 1.5 A at 480 V AC, A600 conforming to NEMA

3 A at 240 V AC, A600 conforming to NEMA

6 A at 120 V AC, A600 conforming to NEMA 0.1 A at 600 V DC, Q600 conforming to NEMA 0.27 A at 250 V AC, Q600 conforming to NEMA 0.55 A at 125 V DC, Q600 conforming to NEMA

[Ithe] conventional enclosed

[Ui] rated insulation voltage

thermal current

600 V degree of pollution 3 conforming to UL 508 for contact

block

600 V degree of pollution 3 conforming to CSA C22.2 No 14 for

contact block

[Uimp] rated impulse withstand voltage

2.5 kV AC for 1 min conforming to CE 2.2 kV AC for 1 min conforming to UL 2.64 kV AC for 1 s conforming to CSA

Short circuit protection 10 A by CC fuse, protection type: non-time delay

**Electrical durability** 1000000 cycles

Local signalling Without

Mechanical durability 10000000 cycles

Width 1.55 in Height 3.14 in Depth 2.5 in **Product weight** 1.25 lb(US)

#### **Environment**

Hide

Shock resistance 60 gn (duration = 9 ms) conforming to IEC 60068-2-27 Vibration resistance 25 gn (f = 10...150 Hz) conforming to IEC 60068-2-6

**NEMA** degree of protection NEMA 1 conforming to Nema type 250

NEMA 2 conforming to Nema type 250 NEMA 4 conforming to Nema type 250 NEMA 6 conforming to Nema type 250 NEMA 6P conforming to Nema type 250 NEMA 12 conforming to Nema type 250 NEMA 13 conforming to Nema type 250

IP degree of protection IP67 conforming to IEC 60529

Class of protection against

electric shock

Class 0 conforming to IEC 61140

Ambient air temperature for

operation

-20...185 °F for standard environment

Ambient air temperature for

storage

-20...185 °F

**Environmental characteristic** Standard environment Protective treatment Epoxy powder coat

#### Offer Sustainability

- Hide

Sustainable offer status Green Premium product

RoHS (date code: YYWW) Compliant - since 1150 - Schneider Electric declaration of

**REACh** Reference not containing SVHC above the threshold

**Product environmental** 

profile

Available download Product environmental

Product end of life instructions

Need no specific recycling operations

### Contractual warranty

☐ Hide

Period 18 months