




Power Double Lock

TE Internal #: 1-368589-4
Housing, Receptacle, Crimp, Wire-to-Panel / Wire-to-Wire, UL 94V-0, 4 Position, Power Double Lock, Rectangular Wire & Cable Connectors & Housings

[View on TE.com >](#)

Connectors > Rectangular Connectors > Standard Rectangular Connectors



Connector Product Type: **Housing**
Connector & Housing Type: **Receptacle**
Termination Method to Wire & Cable: **Crimp**
Connector System: **Wire-to-Panel, Wire-to-Wire**
Contact Retention Within Housing: **Without**

Features

Product Type Features

Compatible With Discrete Wire Type	Stranded
Connector Product Type	Housing
Connector & Housing Type	Receptacle
Connector System	Wire-to-Panel, Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Signal Positions	0
Number of Power Positions	0
Number of Positions	4
Number of Rows	2

Electrical Characteristics

Operating Voltage	300 VAC
-------------------	---------

Body Features



Primary Product Color	Yellow
-----------------------	--------

Contact Features

Contact Layout	Matrix
Contact Type	Tab
Contact Retention Within Housing	Without

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Panel Mount Feature	With
Panel Mount Feature Type	Latches
Connector Mounting Type	Panel Mount

Housing Features

Housing Material	PA 66
Centerline (Pitch)	3.96 mm[.156 in]

Dimensions

Row-to-Row Spacing	4.6 mm[.181 in]
Panel Thickness (Recommended)	.8 – 2 mm[.031 – .078 in]

Usage Conditions

Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

Compatible With Agency/Standards Products	CNR, USR
Compatible With Approved Standards Products	CSA/C22.2 No. 182.3-M1987, UL 1977
Glow Wire Rating	GWT 750°C (Without Flame)
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	150
Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 177908-4
POWER DBL LOCK CAP HSG P/M 4P



TE Part # 368575-4
PDL 4P PLUG 3.96 D/R(GWT) YEL

Also in the Series | Power Double Lock



Connector Contacts(24)



Connector Hardware(14)



Insertion & Extraction Tools(2)




PCB Headers & Receptacles(43)



Power Contacts(24)



Rectangular Power Connectors(283)



Wire-to-Board Headers & Receptacles (43)

Customers Also Bought



TE Part #CAT-P87024-P729A
Glow Wire Power Double Lock Plug




TE Part #1-2232890-5
5P MONOPLUG 2.5 SELECTIVELY LOADED



TE Part #1969453-1
POSITIVE LOCK 250 HOUSING RECEPTACLE



TE Part #2-2178029-2
2P ST-TIMER HSG BLACK, V0




TE Part #177915-1
AMP POWER DBL LOCK REC (L)



TE Part #1-2352002-7
7P MONOPLUG 2.5 SELECTIVELY LOADED



TE Part #1-1625885-4
1W SM M/OX 5% 10R



TE Part #1-2178029-2
2P ST-TIMER RED, V0



TE Part #CP4925-000
ES2000-NO.3-B8-0-60MM-SH

Documents



Product Drawings

PDL 4P CAP 3.96 D/R P/M(GWT) Y

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-368589-4_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-368589-4_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-368589-4_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English