



TECHNICAL CHARACTERISTICS

MATERIAL

INSULATOR: PA 66
 FLAMABILITY RATING: UL94-V0
 COLOR: GREEN
 METAL HOUSING: BRASS (CuZn)
 TERMINAL SCREW: STEEL ZINC PLATING "-" SLOT TYPE
 WIRE GUARD: PhBz TIN PLATED

ENVIRONMENTAL

OPERATING TEMPERATURE: -40 UP TO 105°C
 COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL

	cULus	VDE
CURRENT RATING:	10A	10.5A
WORKING VOLTAGE:	300VAC	300VAC
WITHSTANDING VOLTAGE:	1.6KV	2.5KV
CONTACT RESISTANCE:	20 mOhm MAX	

STANDARD

CERTIFIED E315414 / MODEL NUMBER 361
 CERTIFIED 40023195 / MODEL NUMBER 361

MECHANICAL

SOLID WIRE:	26-16 AWG / 0.13-1.5MM ²
STRANDED WIRE:	26-16 AWG / 0.13-1.5MM ²
TORQUE:	3.0Lb.In / 0.34Nm

WIRE STRIPE LENGTH: 6-7MM

SCREW: M2
 PITCH: 3.81MM

PACKAGING: BOX

SERIE 361

RoHS Compliant

G				PROJECTION: 	GENERAL TOLERANCE .X = +/- 0.2 .XX = +/- 0.15		
F							
E							
D	08-FEV-11	DIMENSSIONS	GG				
C	12-OCT-09	STANDARD	JP				
B	29-OCT-08	CHARACTERISTICS	JP	APPROVAL: RJ	UNIT: MM	DESCRIPTION: SERIE 361 - 3.81MM VERTICAL CABLE ENTRY PLUG 1.5MM² WIRES WR-TBL	SIZE A4
A	31-OCT-07	PDF	EC		SCALE:		
REV	DATE	FILE	BY		SHEET: 1/1		
					DRAW: MARVIN		