



M12 FUEL™

M12 FDSS-422X

M12 FUEL™ SUB COMPACT SPOT SANDER

Compact detail sander with a penta shaped pad allows uncompromised corner accessibility

Four speed modes allows the correct speed to be set for different types of material

Low vibration at only 4.3 m/s²

Sponge interface pad included optimises the tool for profiles and contours which increases the precision and removal of material

Hook and loop pad allows the user to change quickly between different grit types

LED lights up your work area for better visibility

The DNA of our FUEL™ platform redefines the balance of cordless technologies. MILWAUKEE®'s POWERSTATE™ brushless motor, REDLITHIUM™ battery pack and REDLINK PLUS™ electronic intelligence delivering outstanding power, run time and durability

Flexible battery system: works with all MILWAUKEE® M12™ batteries



REDLITHIUM™



No load speed (rpm)	0 - 8,000/ 0 - 10,000/ 0 - 12,000/ 0 - 14,000
Oscillation diameter (mm)	1.5
Sanding pad size (mm)	88.8 x 63.5
Weight with battery pack (EPTA) (kg)	0.8 (M12 B2)
Kit included	1 x M12 B4, 1 x M12 B2 Battery packs, C12 C Charger, HD Box
Article number	4933479681