

Endress+Hauser Capacitance level switch FTI26-AA4UWDGPA

Capacitive point level switch for powder and fine-grained solids for the food industry.



Picture for reference only. Product appearance may vary based on configuration

The Nivector FTI26 is a point level switch for powdered or granular solids in the food and other industries. The capacitance device offers high sensitivity and build-up performance. Thanks to the compact design, installation is possible even when access is restricted. The optional IO-Link capability allows easy parameter setting.

- Easy installation even in tight conditions or where access is restricted thanks to the compact design
- Fulfillment of all relevant hygienic requirements (3-A, EHEDG, FDA, EG1935/2004)
- No individual adjustment to each medium necessary
- Industry 4.0 ready with IO-Link communication

Configuration of FTI26-AA4UWDGPA:

| | | |
|------------------------|-----|---|
| Approval: | AA | Non-hazardous area |
| Power; Output: | 4 | 12-30VDC; 3-wire PNP |
| Electrical Connection: | U | Valve plug ISO4400 M16, IP65 NEMA Type 4X Encl. |
| Process Connection: | WDG | Thread ISO228 G1, plastic |
| >>Accessory Enclosed: | PA | Protector G1-1/2, PBT-GF |

Alternative part number: FTI26-1380/0