


NP-Series - Valve Regulated Lead Acid Battery

NP10-6

SPECIFICATIONS		
Nominal voltage	6	V
20-hr rate Capacity to 1.75VPC at 20°C	10.00	Ah
10-hr rate Capacity to 1.75VPC at 20°C	9.20	Ah
DIMENSIONS		
Length	151 (±1)	mm
Width	50 (±1)	mm
Height		mm
(height over terminals)	97.5 (±2)	mm
Mass (typical)	1.93	kg
TERMINAL TYPE		
FASTON (Quickfit / release)	4.75	mm
Female threaded terminal		
Torque		Nm
OPERATING TEMPERATURE RANGE		
Storage	-20°C to +60°C	
Charge	-15°C to +50°C	
Discharge	-20°C to +60°C	
STORAGE		
Capacity loss per month at 20°C (approx)	3	%
CASE MATERIAL		
Standard Option	ABS (UL94:HB)	
Flame retardant option (FR)	ABS (UL94:V0)	
CHARGE VOLTAGE		
Float charge voltage at 20°C	6.825 (±1%)	V
	2.275 (±1%)	V/cell
Float Charge voltage temperature correction factor (for variations from the standard 20°C)	-3	mV/cell/°C
Cyclic (or Boost) charge at 20°C	7.26 (±3%)	V
	2.42 (±3%)	V/cell
Cyclic Charge voltage temperature correction factor (for variations from the standard 20°C)	-4	mV/cell/°C
CHARGE CURRENT		
Float charge current limit	No limit	A
Cyclic (or Boost) charge current limit	2.50	A
MAXIMUM DISCHARGE CURRENT		
1 second	300	A
1 minute	48	A
SHORT-CIRCUIT CURRENT & INTERNAL RESISTANCE (according to EN IEC 60896-21)		
Internal resistance	N/A	mΩ
Short-Circuit current	N/A	A
IMPEDANCE		
Measured at 1 kHz	25	mΩ
PERFORMANCE & CHARACTERISTICS		
Refer to the technical manual	NP	
DESIGN LIFE		
EUROBAT Classification: Standard Commercial	3 to 5	years
Yuasa design life @ 20°C	up to 5	years
SAFETY		
Installation		
Can be installed and operated in any orientation except permanently inverted		
Handles		
Batteries must not be suspended by their handles (where fitted)		
Vent valves		
Each cell is fitted with a low pressure release valve to allow gasses to escape and then reseal.		
Gas Release		
VRLA Batteries release hydrogen gas which can form explosive mixtures in air. Do not place inside a sealed container		
Recycling		
YUASA's VRLA batteries must be recycled at the end of life in accordance with local and national laws and regulations		



3RD PARTY CERTIFICATIONS

ISO 9001 - Quality Management Systems
 ISO 14001 - Environmental Management Systems
 EN 18001 - OHSAS Management Systems
 UNDERWRITERS LABORATORIES Inc.
 VdS (Germany) - VdS No: G189170

IEC61056

STANDARDS

IEC61056



Issue No.: V.2 / Issue Date: March 2011

ALL DATA IS SUBJECT TO CHANGE WITHOUT NOTICE

YUASA BATTERY SALES
 UK LTD



www.yuasaeurope.com

NP

CELL PACK
 SOLUTIONS

Telephone: +44 (0)191 496 9999
 Email: batteries@cellpacksolutions.co.uk
 Website: www.cellpacksolutions.co.uk