

Material Safety Data Sheet

According to 91/155 EC

Printing date 24.04.2003

CP1041 v1.0 RS 492-7145

Reviewed on 24.04.2003

1 Identification of substance:

- **Product details:**
- **Trade name:** *SP HANDIPACK RESIN*
- **Application of the substance / the preparation** *Epoxy resin*
- **Manufacturer/Supplier:**
SP SYSTEMS LTD
ST. CROSS BUSINESS PARK
NEWPORT I.O.W.
PO30 5WU
UNITED KINGDOM
- **Informing department:** *Product safety department.*

Supplied by:
RS Components Ltd,
Birchington Road, Corby, Northants, NN17 9RS.
Tel: (01536) 402888

TEL.: +44 (0) 1983 828000




FAX: +44 (0) 1983 828100

OUT OF HOURS EMERGENCY.: +44 (0) 2392 241208

2 Composition/Data on components:

- **Chemical characterization**
- **Description:** *Mixture of the substances listed below with harmless additions.*

- **Dangerous components:**

CAS: 25068-38-6 NLP: 500-033-5	bisphenol A-(epichlorhydrin); epoxy resin(number average molecular weight<700)  Xi,  N; R 36/38-43-51/53	50-100%
CAS: 98-00-0 EINECS: 202-626-1	furfuryl alcohol  Xn; R 20/21/22	10-25%

3 Hazards identification

- **Hazard designation:**



Xn Harmful
N Dangerous for the environment

- **Information pertaining to particular dangers for man and environment**

R 20/21/22 Harmful by inhalation, in contact with skin and if swallowed.

R 36/38 Irritating to eyes and skin.

R 43 May cause sensitisation by skin contact.

R 51/53 Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

Contains epoxy constituents. See information supplied by the manufacturer.

- **Classification system**

The classification is in line with current EC lists. It is expanded, however, by information from technical literature and by information furnished by supplier companies.

4 First aid measures

- **General information**

Symptoms of poisoning may even occur after several hours; therefore medical observation for at least 48 hours after the accident.

- **After inhalation**

Supply fresh air and call for doctor for safety reasons.

In case of unconsciousness bring patient into stable side position for transport.

- **After skin contact** Instantly wash with water and soap and rinse thoroughly.

- **After eye contact**

Rinse opened eye for several minutes under running water. If symptoms persist, consult doctor.

(Contd. on page 2)

Material Safety Data Sheet

According to 91/155 EC

Printing date 24.04.2003

CP1041 v1.0 RS 492-7145

Reviewed on 24.04.2003

Trade name: SP HANDIPACK RESIN

(Contd. of page 1)

- **After swallowing** Instantly call for doctor.

5 Fire fighting measures

- **Suitable extinguishing agents**
Water haze
Foam
Fire-extinguishing powder
Carbon dioxide
- **For safety reasons unsuitable extinguishing agents** Water with a full water jet.
- **Special hazards caused by the material, its products of combustion or resulting gases:**
Formation of toxic gases is possible during heating or in case of fire.
- **Protective equipment:**
Put on breathing apparatus.
Wear full protective suit.

6 Accidental release measures

- **Person-related safety precautions:** Not required.
- **Measures for environmental protection:**
Prevent material from reaching sewage system, holes and cellars.
Inform respective authorities in case product reaches water or sewage system.
Do not allow to enter drainage system, surface or ground water.
- **Measures for cleaning/collecting:**
Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).
Dispose of contaminated material as waste according to item 13.
Ensure adequate ventilation.

7 Handling and storage

- **Handling**
- **Information for safe handling:** Ensure good ventilation/exhaustion at the workplace.
- **Information about protection against explosions and fires:** No special measures required.
- **Storage**
- **Requirements to be met by storerooms and containers:** No special requirements.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:** Keep container tightly sealed.

8 Exposure controls and personal protection

- **Additional information about design of technical systems:** No further data; see item 7.

- **Components with limit values that require monitoring at the workplace:**

98-00-0 furfuryl alcohol (10-25%)

OEL	Short-term value: 60 mg/m ³ , 15 ml/m ³
	Long-term value: 20 mg/m ³ , 5 ml/m ³

- **Additional information:** The lists that were valid during the compilation were used as basis.
- **Personal protective equipment**
- **General protective and hygienic measures**
Keep away from foodstuffs, beverages and food.
Take off immediately all contaminated clothing
Wash hands during breaks and at the end of the work.
Avoid contact with the eyes and skin.
- **Breathing equipment:**
In case of brief exposure or low pollution use breathing filter apparatus. In case of intensive or longer exposure use breathing apparatus that is independent of circulating air.

(Contd. on page 3)

Material Safety Data Sheet

According to 91/155 EC

Printing date 24.04.2003

CP1041 v1.0 RS 492-7145

Reviewed on 24.04.2003

Trade name: SP HANDIPACK RESIN

(Contd. of page 2)

Protection of hands:



Protective gloves.

Material of gloves

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.

Penetration time of glove material

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

Eye protection:



Tightly sealed safety glasses.

9 Physical and chemical properties:

General Information

Form: Fluid
Colour: Light brown
Odour: Characteristic

Change in condition

Melting point/Melting range: Not determined
Boiling point/Boiling range: 171°C

Flash point: 75°C

Ignition temperature: 390.0°C

Self-inflammability: Product is not selfigniting.

Danger of explosion: Product is not explosive.

Vapour pressure at 20°C: 0.5 hPa

Density at 20°C 1.147 g/cm³

Solubility in / Miscibility with

Water: Not miscible or difficult to mix

Viscosity:

dynamic at 20°C: 900 mPas

Solvent content:

Organic solvents: 0.1 %
Water: 0.0 %

Solids content: 0.0 %

10 Stability and reactivity

Thermal decomposition / conditions to be avoided:

No decomposition if used according to specifications.

Dangerous reactions

No dangerous reactions known

Dangerous products of decomposition:

No dangerous decomposition products known

GB

(Contd. on page 4)

Material Safety Data Sheet

According to 91/155 EC

Printing date 24.04.2003

CP1041 v1.0 RS 492-7145

Reviewed on 24.04.2003

Trade name: SP HANDIPACK RESIN

(Contd. of page 3)

11 Toxicological information

- **Acute toxicity:**

- **LD/LC50 values that are relevant for classification:**

98-00-0 furfuryl alcohol

Oral	LD50	275 mg/kg (rat)
Dermal	LD50	657 mg/kg (rab)
Inhalative	LC50/4 h	233 mg/l (rat)

- **Primary irritant effect:**

- **on the skin:** Irritant to skin and mucous membranes.

- **on the eye:** Irritant effect.

- **Sensitization:** Sensitization possible by skin contact.

- **Additional toxicological information:**

The product shows the following dangers according to the calculation method of the General EC Classification Guidelines for Preparations as issued in the latest version:

Harmful

Irritant

12 Ecological information:

- **General notes:**

Water hazard class 2 (German Regulation) (Self-assessment): hazardous for water.

Do not allow product to reach ground water, water bodies or sewage system.

13 Disposal considerations

- **Product:**

- **Recommendation**

Must not be disposed of together with household garbage. Do not allow product to reach sewage system.

- **Uncleaned packagings:**

- **Recommendation:**

Disposal must be made according to official regulations.

Packagings that cannot be cleaned are to be disposed of in the same manner as the product.

14 Transport information

- **Land transport ADR/RID (cross-border)**



- **ADR/RID-GGVSE Class:** 9 Miscellaneous dangerous substances and articles.

- **Kemler Number:** 90

- **UN-Number:** 3082

- **Packaging group:** III

- **Label** 9

- **Designation of goods:** 3082 ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (bisphenol A-(epichlorhydrin); epoxy resin(number average molecular weight<700))

(Contd. on page 5)

GB

Material Safety Data Sheet

According to 91/155 EC

Printing date 24.04.2003

CP1041 v1.0 RS 492-7145

Reviewed on 24.04.2003

Trade name: SP HANDIPACK RESIN

(Contd. of page 4)

Maritime transport IMDG:



- **IMDG Class:** 9
- **UN Number:** 3082
- **Label** 9
- **Packaging group:** III
- **Marine pollutant:** No
- **Correct technical name:** ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (bisphenol A-(epichlorhydrin); epoxyresin(number average molecular weight<700))

Air transport ICAO-TI and IATA-DGR:



- **ICAO/IATA Class:** 9
- **UN/ID Number:** 3082
- **Label** 9
- **Packaging group:** III
- **Correct technical name:** ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (bisphenol A-(epichlorhydrin); epoxyresin(number average molecular weight<700))

15 Regulatory information

Designation according to EC guidelines:

The product has been classified and labelled in accordance with EC Directives / Ordinance on Hazardous Materials (GefStoffV)

Code letter and hazard designation of product:

Xn Harmful

N Dangerous for the environment

Hazard-determining components of labelling:

bisphenol A-(epichlorhydrin); epoxy resin(number average molecular weight<700)
furfuryl alcohol

Risk phrases:

20/21/22 Harmful by inhalation, in contact with skin and if swallowed.

36/38 Irritating to eyes and skin.

43 May cause sensitisation by skin contact.

51/53 Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

Safety phrases:

2 Keep out of the reach of children.

13 Keep away from food, drink and animal feedingstuffs.

36/37/39 Wear suitable protective clothing, gloves and eye/face protection.

46 If swallowed, seek medical advice immediately and show this container or label.

Special designation of certain preparations:

Contains epoxy constituents. See information supplied by the manufacturer.

National regulations

Technical instructions (air):

Class	Share in %
II	13.8

- **Water hazard class:** Water hazard class 2 (Self-assessment): hazardous for water.

GB

(Contd. on page 6)

Material Safety Data Sheet

According to 91/155 EC

Printing date 24.04.2003

CP1041 v1.0 RS 492-7145

Reviewed on 24.04.2003

Trade name: SP HANDIPACK RESIN

(Contd. of page 5)

16 Other information:

These data are based on our present knowledge. However, they shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

· **Relevant R-phrases**

20/21/22 Harmful by inhalation, in contact with skin and if swallowed.

36/38 Irritating to eyes and skin.

43 May cause sensitisation by skin contact.

51/53 Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

· **Department issuing data specification sheet:** Environment protection department.

· **Contact:**

HARALD BEHMER

NICK PARTINGTON

· *** Data compared to the previous version altered.**

GB

Material Safety Data Sheet

According to 91/155 EC

Printing date 24.04.2003

CP1041 v1.0 RS 492-7145

Reviewed on 24.04.2003

1 Identification of substance:

- **Product details:**
- **Trade name:** *SP Handipack Hardener*
- **Application of the substance / the preparation** *Epoxy curing agent*
- **Manufacturer/Supplier:**
SP SYSTEMS LTD
ST. CROSS BUSINESS PARK
NEWPORT I.O.W.
PO30 5WU
UNITED KINGDOM
- **Informing department:** *Product safety department.*

Supplied by:
RS Components Ltd,
Birchington Road, Corby, Northants, NN17 9RS.
Tel: (01536) 402888

TEL.: +44 (0) 1983 828000







FAX : +44 (0) 1983 828100

OUT OF HOURS EMERGENCY.: +44 (0) 2392 241208

2 Composition/Data on components:

- **Chemical characterization**
- **Description:** *Mixture of the substances listed below with harmless additions.*

Dangerous components:

CAS: 68391-18-4	Mannich Base	 C; R 34-43	25-50%
CAS: 100-51-6 EINECS: 202-859-9	benzyl alcohol	 Xn; R 20/22	10-25%
CAS: 25620-58-0 EINECS: 247-134-8	trimethylhexane-1,6-diamine	 C; R 22-34-43	10-25%
CAS: 1477-55-0 EINECS: 216-032-5	m-phenylenebis(methylamine)	 C; R 22-34	2.5-10%
CAS: 140-31-8 EINECS: 205-411-0	2-piperazin-1-ylethylamine	 C; R 21/22-34-43-52/53	2.5-10%
CAS: 108-95-2 EINECS: 203-632-7	phenol, pure	 T; R 24/25-34	2.5-10%

3 Hazards identification

- **Hazard designation:**



C Corrosive

- **Information pertaining to particular dangers for man and environment**

R 21/22 Harmful in contact with skin and if swallowed.

R 34 Causes burns.

R 43 May cause sensitisation by skin contact.

- **Classification system**

The classification is in line with current EC lists. It is expanded, however, by information from technical literature and by information furnished by supplier companies.

4 First aid measures

- **General information**

Instantly remove any clothing soiled by the product.

Symptoms of poisoning may even occur after several hours; therefore medical observation for at least 48 hours after the accident.

- **After inhalation**

Supply fresh air and call for doctor for safety reasons.

In case of unconsciousness bring patient into stable side position for transport.

- **After skin contact** Instantly wash with water and soap and rinse thoroughly.

(Contd. on page 8)

Material Safety Data Sheet

According to 91/155 EC

Printing date 24.04.2003

CP1041 v1.0 RS 492-7145

Reviewed on 24.04.2003

Trade name: SP Handipack Hardener

(Contd. of page 7)

- **After eye contact** Rinse opened eye for several minutes under running water. Then consult doctor.
- **After swallowing**
Instantly call for doctor.
Drink copious amounts of water and provide fresh air. Instantly call for doctor.

5 Fire fighting measures

- **Suitable extinguishing agents**
Water haze
Foam
Fire-extinguishing powder
Carbon dioxide
- **For safety reasons unsuitable extinguishing agents** Water with a full water jet.
- **Special hazards caused by the material, its products of combustion or resulting gases:**
Formation of toxic gases is possible during heating or in case of fire.
- **Protective equipment:**
Put on breathing apparatus.
Wear full protective suit.

6 Accidental release measures

- **Person-related safety precautions:**
Wear protective equipment. Keep unprotected persons away.
Wear protective clothing.
- **Measures for environmental protection:**
Prevent material from reaching sewage system, holes and cellars.
Do not allow to enter drainage system, surface or ground water.
- **Measures for cleaning/collecting:**
Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).
Dispose of contaminated material as waste according to item 13.
Ensure adequate ventilation.

7 Handling and storage

- **Handling**
- **Information for safe handling:**
Store in cool, dry place in tightly closed containers.
Keep away from heat and direct sunlight.
- **Information about protection against explosions and fires:** No special measures required.
- **Storage**
- **Requirements to be met by storerooms and containers:** No special requirements.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:** Keep container tightly sealed.

8 Exposure controls and personal protection

- **Additional information about design of technical systems:** No further data; see item 7.
 - **Components with limit values that require monitoring at the workplace:**
- | | |
|---------------------------------|--|
| 108-95-2 phenol, pure (2.5-10%) | |
| OEL | Short-term value: 38 mg/m ³ , 10 ml/m ³
Long-term value: 19 mg/m ³ , 5 ml/m ³ |
- **Additional information:** The lists that were valid during the compilation were used as basis.

- **Personal protective equipment**
- **General protective and hygienic measures**
Keep away from foodstuffs, beverages and food.

(Contd. on page 9)

Material Safety Data Sheet

According to 91/155 EC

Printing date 24.04.2003

CP1041 v1.0 RS 492-7145

Reviewed on 24.04.2003

Trade name: SP Handipack Hardener

(Contd. of page 8)

Take off immediately all contaminated clothing
Wash hands during breaks and at the end of the work.
Avoid contact with the eyes and skin.

- **Breathing equipment:** Use breathing protection in case of insufficient ventilation.
- **Protection of hands:**



Protective gloves.

- **Material of gloves**

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.

- **Penetration time of glove material**

The exact break trough time has to be found out by the manufacturer of the protective gloves and has to be observed.

- **Eye protection:**



Tightly sealed safety glasses.

- **Body protection:** Protective work clothing.

9 Physical and chemical properties:

· General Information

Form: Fluid
Colour: Pale
Odour: Characteristic

· Change in condition

Melting point/Melting range: Not determined
Boiling point/Boiling range: 205°C

· **Flash point:** 118°C

· **Ignition temperature:** 435.0°C

· **Self-inflammability:** Product is not selfigniting.

· **Danger of explosion:** Product is not explosive.

· **Vapour pressure at 20°C:** 0.1 hPa

· **Density at 20°C** 1.057 g/cm³

· Solubility in / Miscibility with

Water: Not miscible or difficult to mix

· **pH-value at 20°C:** 11.0

· Viscosity:

dynamic at 20°C: 2500 mPas

· Solvent content:

Organic solvents: 0.0 %

Water: 0.0 %

· **Solids content:** 0.0 %

GB

(Contd. on page 10)

Material Safety Data Sheet

According to 91/155 EC

Printing date 24.04.2003

CP1041 v1.0 RS 492-7145

Reviewed on 24.04.2003

Trade name: SP Handipack Hardener

(Contd. of page 9)

10 Stability and reactivity

- **Thermal decomposition / conditions to be avoided:**
No decomposition if used according to specifications.
- **Dangerous reactions** No dangerous reactions known
- **Dangerous products of decomposition:** No dangerous decomposition products known

11 Toxicological information

- **Acute toxicity:**

- **LD/LC50 values that are relevant for classification:**

108-95-2 phenol, pure

Oral	LD50	300 mg/kg (mus)
Dermal	LD50	670 mg/kg (rat)
Inhalative	LC50/4 h	316 mg/l (rat)

- **Primary irritant effect:**

- **on the skin:** Caustic effect on skin and mucous membranes.

- **on the eye:** Strong caustic effect.

- **Sensitization:** Sensitization possible by skin contact.

- **Additional toxicological information:**

The product shows the following dangers according to the calculation method of the General EC Classification Guidelines for Preparations as issued in the latest version:

Harmful

Corrosive

Irritant

Swallowing will lead to a strong caustic effect on mouth and throat and to the danger of perforation of esophagus and stomach.

12 Ecological information:

- **General notes:**

Water hazard class 1 (German Regulation) (Self-assessment): slightly hazardous for water.

Do not allow product to reach ground water, water bodies or sewage system.

13 Disposal considerations

- **Product:**

- **Recommendation**

Must not be disposed of together with household garbage. Do not allow product to reach sewage system.

- **Uncleaned packagings:**

- **Recommendation:**

Packagings that cannot be cleaned are to be disposed of in the same manner as the product.

Disposal must be made according to official regulations.

14 Transport information

- **Land transport ADR/RID (cross-border)**



- **ADR/RID-GGVS/E Class:** 8 Corrosive substances.

- **Kemler Number:** 80

- **UN-Number:** 2735

(Contd. on page 11)

Material Safety Data Sheet

According to 91/155 EC

Printing date 24.04.2003

CP1041 v1.0 RS 492-7145

Reviewed on 24.04.2003

Trade name: SP Handipack Hardener

(Contd. of page 10)

- **Packaging group:** III
- **Label** 8
- **Designation of goods:** 2735 POLYAMINES, LIQUID, CORROSIVE, N.O.S.
(TRIMETHYLHEXAMETHYLENEDIAMINES, m-phenylenebis(methylamine))

- **Maritime transport IMDG:**



- **IMDG Class:** 8
- **UN Number:** 2735
- **Label** 8
- **Packaging group:** III
- **EMS Number:** F-A,S-B
- **Marine pollutant:** No
- **Correct technical name:** POLYAMINES, LIQUID, CORROSIVE, N.O.S.
(TRIMETHYLHEXAMETHYLENEDIAMINES, m-phenylenebis(methylamine))

- **Air transport ICAO-TI and IATA-DGR:**



- **ICAO/IATA Class:** 8
- **UN/ID Number:** 2735
- **Label** 8
- **Packaging group:** III
- **Correct technical name:** POLYAMINES, LIQUID, CORROSIVE, N.O.S.
(TRIMETHYLHEXAMETHYLENEDIAMINES, m-phenylenebis(methylamine))

15 Regulatory information

- **Designation according to EC guidelines:**
The product has been classified and labelled in accordance with EC Directives / Ordinance on Hazardous Materials (GefStoffV)
- **Code letter and hazard designation of product:**
C Corrosive
- **Hazard-determining components of labelling:**
Mannich Base
trimethylhexane-1,6-diamine
2-piperazin-1-ylethylamine
phenol, pure
- **Risk phrases:**
21/22 Harmful in contact with skin and if swallowed.
34 Causes burns.
43 May cause sensitisation by skin contact.
- **Safety phrases:**
20 When using do not eat or drink.
26 In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.
36/37/39 Wear suitable protective clothing, gloves and eye/face protection.
45 In case of accident or if you feel unwell, seek medical advice immediately (show the label where possible).

(Contd. on page 12)

GB

Material Safety Data Sheet

According to 91/155 EC

Printing date 24.04.2003

CP1041 v1.0 RS 492-7145

Reviewed on 24.04.2003

Trade name: SP Handipack Hardener

(Contd. of page 11)

- **National regulations**
- **Technical instructions (air):**

Class	Share in %
I	3.0
II	14.0
III	3.5

- **Water hazard class:** Water hazard class 1 (Self-assessment): slightly hazardous for water.

16 Other information:

These data are based on our present knowledge. However, they shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

- **Relevant R-phrases**
 20/22 Harmful by inhalation and if swallowed.
 21/22 Harmful in contact with skin and if swallowed.
 22 Harmful if swallowed.
 24/25 Toxic in contact with skin and if swallowed.
 34 Causes burns.
 43 May cause sensitisation by skin contact.
 52/53 Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
- **Department issuing data specification sheet:** Environment protection department.
- **Contact:**
 HARALD BEHMER
 NICK PARTINGTON
- *** Data compared to the previous version altered.**

GB