



## Safety Data Sheet according to Regulation (EC) No 1907/2006

Page 1 of 13

LOCTITE 362 99C 5C 0.5MM G known as 99C 362 5C 0.5MM  
0.25KG RLR RS

SDS No. : 221815  
V005.4

Revision: 21.06.2019

printing date: 06.08.2019

Replaces version from: 20.11.2013

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

LOCTITE 362 99C 5C 0.5MM G known as 99C 362 5C 0.5MM 0.25KG RLR RS

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:

Solder Wire

#### 1.3. Details of the supplier of the safety data sheet

Henkel Ltd

Wood Lane End

HP2 4RQ Hemel Hempstead

Great Britain

Phone: +44 1442 278000

Fax-no.: +44 1442 278071

ua-productsafety.uk@henkel.com

#### 1.4. Emergency telephone number

24 Hours Emergency Tel: +44 (0)1442 278497

### SECTION 2: Hazards identification

#### 2.1. Classification of the substance or mixture

##### Classification (CLP):

Skin sensitizer

H317 May cause an allergic skin reaction.

Category 1

#### 2.2. Label elements

##### Label elements (CLP):

##### Hazard pictogram:



Contains

Colophony

Signal word:

Warning

<b>Hazard statement:</b>	H317 May cause an allergic skin reaction.
<b>Precautionary statement: Prevention</b>	P261 Avoid breathing fume. P280 Wear protective gloves.
<b>Precautionary statement: Response</b>	P333+P313 If skin irritation or rash occurs: Get medical advice/attention.

### 2.3. Other hazards

Avoid breathing fumes given out during soldering.

After handling solder wash hands with soap and water before eating, drinking or smoking.

Flux fumes may irritate the nose, throat and lungs and may after prolonged/repeated exposure give an allergic reaction (asthma).

Keep out of reach of children.

Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

## SECTION 3: Composition/information on ingredients

### 3.2. Mixtures

#### Declaration of the ingredients according to CLP (EC) No 1272/2008:

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
Tin 7440-31-5	231-141-8 01-2119486474-28	50- 100 %	
Colophony 8050-09-7	232-475-7 01-2119480418-32	1- < 5 %	Skin Sens. 1 H317

For full text of the H - statements and other abbreviations see section 16 "Other information".

Substances without classification may have community workplace exposure limits available.

## SECTION 4: First aid measures

### 4.1. Description of first aid measures

Inhalation:

Move to fresh air. If symptoms persist, seek medical advice.

Skin contact:

Rinse with running water and soap.

Obtain medical attention if irritation persists.

Eye contact:

Flush eyes with plenty of water for at least 5 minutes. If irritation persists seek medical attention.

Ingestion:

Do not induce vomiting.

Seek medical advice.

### 4.2. Most important symptoms and effects, both acute and delayed

Flux fumes may irritate the nose, throat and lungs and may after prolonged/repeated exposure give an allergic reaction (asthma).

SKIN: Rash, Urticaria.

### 4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

## SECTION 5: Firefighting measures

### 5.1. Extinguishing media

#### Suitable extinguishing media:

Carbon dioxide, foam, powder  
Fine water spray

#### Extinguishing media which must not be used for safety reasons:

Do not use water on fires where molten metal is present.

### 5.2. Special hazards arising from the substance or mixture

High temperatures may produce heavy metal dust, fumes or vapours.  
The flux medium will give rise to irritating fumes.

### 5.3. Advice for firefighters

Wear self-contained breathing apparatus.

## SECTION 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

Wear protective equipment.

### 6.2. Environmental precautions

Do not empty into drains / surface water / ground water.

### 6.3. Methods and material for containment and cleaning up

Scrape up spilled material and place in a closed container for disposal.  
Dispose of contaminated material as waste according to Section 13.

### 6.4. Reference to other sections

See advice in section 8

## SECTION 7: Handling and storage

### 7.1. Precautions for safe handling

Extraction is necessary to remove fumes evolved during reflow.

When using do not eat, drink or smoke.

Wash hands before breaks and immediately after handling the product.

Avoid breathing fumes given out during soldering.

See advice in section 8

Avoid skin and eye contact.

#### Hygiene measures:

Good industrial hygiene practices should be observed.

Do not eat, drink or smoke while working.

After handling solder wash hands with soap and water before eating, drinking or smoking.

### 7.2. Conditions for safe storage, including any incompatibilities

Ensure good ventilation/extraction.

Store in a cool, dry place.

Refer to Technical Data Sheet

### 7.3. Specific end use(s)

Solder Wire

**SECTION 8: Exposure controls/personal protection**

**8.1. Control parameters**

**Occupational Exposure Limits**

Valid for  
Great Britain

Ingredient [Regulated substance]	ppm	mg/m <sup>3</sup>	Value type	Short term exposure limit category / Remarks	Regulatory list
Rosin 8050-09-7 [ROSIN-BASED SOLDER FLUX FUME]		0,05	Time Weighted Average (TWA):		EH40 WEL
Rosin 8050-09-7 [ROSIN-BASED SOLDER FLUX FUME]		0,15	Short Term Exposure Limit (STEL):		EH40 WEL

**Occupational Exposure Limits**

Valid for  
Ireland

Ingredient [Regulated substance]	ppm	mg/m <sup>3</sup>	Value type	Short term exposure limit category / Remarks	Regulatory list
Tin 7440-31-5 [TIN, METAL (AS SN)]		2	Time Weighted Average (TWA):	Indicative OELV	IR_OEL
Tin 7440-31-5 [TIN (INORGANIC COMPOUNDS AS SN)]		2	Time Weighted Average (TWA):	Indicative	ECLTV
Rosin 8050-09-7 [ROSIN CORE SOLDER PYROLYSIS PRODUCTS (AS AIRBORNE TOTAL RESIN ACID)]		0,05	Time Weighted Average (TWA):		IR_OEL
Rosin 8050-09-7 [ROSIN CORE SOLDER PYROLYSIS PRODUCTS (AS AIRBORNE TOTAL RESIN ACID)]		0,15	Short Term Exposure Limit (STEL):	15 minutes	IR_OEL

**Predicted No-Effect Concentration (PNEC):**

Name on list	Environmental Compartment	Exposure period	Value				Remarks
			mg/l	ppm	mg/kg	others	
Tin 7440-31-5	aqua (freshwater)						
Tin 7440-31-5	aqua (marine water)						
Tin 7440-31-5	sewage treatment plant (STP)						
Tin 7440-31-5	sediment (freshwater)						
Tin 7440-31-5	sediment (marine water)						
Tin 7440-31-5	Air						
Tin 7440-31-5	Soil						
Tin 7440-31-5	Predator						
Colophony 8050-09-7	aqua (freshwater)		0,002 mg/l				
Colophony 8050-09-7	aqua (marine water)		0,0002 mg/l				
Colophony 8050-09-7	sediment (freshwater)				0,007 mg/kg		
Colophony 8050-09-7	sediment (marine water)				0,001 mg/kg		
Colophony 8050-09-7	Soil				0 mg/kg		
Colophony 8050-09-7	sewage treatment plant (STP)		1000 mg/l				
Colophony 8050-09-7	aqua (intermittent releases)		0,016 mg/l				

**Derived No-Effect Level (DNEL):**

Name on list	Application Area	Route of Exposure	Health Effect	Exposure Time	Value	Remarks
Tin 7440-31-5	General population	dermal	Long term exposure - systemic effects		80 mg/kg	
Tin 7440-31-5	Workers	inhalation	Long term exposure - systemic effects		71 mg/m3	
Tin 7440-31-5	Workers	dermal	Long term exposure - systemic effects		10 mg/kg	
Tin 7440-31-5	General population	inhalation	Long term exposure - systemic effects		17 mg/m3	
Tin 7440-31-5	General population	oral	Long term exposure - systemic effects		5 mg/kg	
Colophony 8050-09-7	Workers	inhalation	Long term exposure - systemic effects		117 mg/m3	
Colophony 8050-09-7	Workers	dermal	Long term exposure - systemic effects		17 mg/kg	
Colophony 8050-09-7	General population	inhalation	Long term exposure - systemic effects		35 mg/m3	
Colophony 8050-09-7	General population	dermal	Long term exposure - systemic effects		10 mg/kg	
Colophony 8050-09-7	General population	oral	Long term exposure - systemic effects		10 mg/kg	

**Biological Exposure Indices:**

None

**8.2. Exposure controls:**

Engineering controls:

Extraction is necessary to remove fumes evolved during reflow.

Where reasonably practicable this should be achieved by the use of local exhaust ventilation and good general extraction.

Ensure good ventilation/extraction.

Respiratory protection:

In case of aerosol formation, we recommend wearing of appropriate respiratory protection equipment with ABEK P2 filter (EN 14387).

This recommendation should be matched to local conditions.

Ensure adequate ventilation.

An approved mask or respirator fitted with an organic vapour cartridge should be worn if the product is used in a poorly ventilated area

**Hand protection:**

Chemical-resistant protective gloves (EN 374).

Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374):

nitrile rubber (NBR;  $\geq$  0.4 mm thickness)

Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374):

nitrile rubber (NBR;  $\geq$  0.4 mm thickness)

This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

**Eye protection:**

Safety glasses with sideshields or chemical safety goggles should be worn if there is a risk of splashing.

Protective eye equipment should conform to EN166.

**Skin protection:**

Wear suitable protective clothing.

Protective clothing should conform to EN 14605 for liquid splashes or to EN 13982 for dusts.

**Advices to personal protection equipment:**

The information provided on personal protective equipment is for guidance purposes only. A full risk assessment should be conducted prior to using this product to determine the appropriate personal protective equipment to suit local conditions.

Personal protective equipment should conform to the relevant EN standard.

**SECTION 9: Physical and chemical properties****9.1. Information on basic physical and chemical properties**

Appearance	solid
	grey
Odor	None
Odour threshold	No data available / Not applicable
pH	Not applicable
Melting point	227 °C (440.6 °F)
Solidification temperature	No data available / Not applicable
Initial boiling point	No data available / Not applicable
Flash point	None
Evaporation rate	No data available / Not applicable
Flammability	No data available / Not applicable
Explosive limits	No data available / Not applicable
Vapour pressure	Not applicable
Relative vapour density:	No data available / Not applicable
Density (25 °C (77 °F))	7,3 g/cm <sup>3</sup>
Bulk density	No data available / Not applicable
Solubility	No data available / Not applicable
Solubility (qualitative) (Solvent: Water)	Insoluble
Partition coefficient: n-octanol/water	Not applicable
Auto-ignition temperature	No data available / Not applicable
Decomposition temperature	No data available / Not applicable
Viscosity	No data available / Not applicable
Viscosity (kinematic)	No data available / Not applicable
Explosive properties	No data available / Not applicable
Oxidising properties	No data available / Not applicable

**9.2. Other information**

No data available / Not applicable

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

Solder alloy will react with concentrated nitric acid to produce toxic fumes of nitrogen oxides.

### 10.2. Chemical stability

Stable under recommended storage conditions.

### 10.3. Possibility of hazardous reactions

See section reactivity

### 10.4. Conditions to avoid

No decomposition if stored and applied as directed.

### 10.5. Incompatible materials

See section reactivity.

### 10.6. Hazardous decomposition products

Thermal decomposition can lead to release of irritating gases and vapors.

## SECTION 11: Toxicological information

### General toxicological information:

Fumes emitted during soldering may irritate the skin.  
Prolonged or repeated contact may cause skin irritation.  
Prolonged or repeated contact may cause eye irritation.

### 11.1. Information on toxicological effects

#### Acute oral toxicity:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Species	Method
Tin 7440-31-5	LD50	> 2.000 mg/kg	rat	OECD Guideline 423 (Acute Oral toxicity)
Colophony 8050-09-7	LD50	2.800 mg/kg	rat	not specified

#### Acute dermal toxicity:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Species	Method
Tin 7440-31-5	LD50	> 2.000 mg/kg	rat	OECD Guideline 402 (Acute Dermal Toxicity)
Colophony 8050-09-7	LD50	> 2.000 mg/kg	rat	OECD Guideline 402 (Acute Dermal Toxicity)



**Acute inhalative toxicity:**

Inhalation of dust may cause shortness of breath, tightness of the chest, a sore throat and cough

No substance data available.

**Skin corrosion/irritation:**

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Exposure time	Species	Method
Tin 7440-31-5	not irritating		rabbit	OECD Guideline 404 (Acute Dermal Irritation / Corrosion)
Colophony 8050-09-7	not irritating	4 h	rabbit	OECD Guideline 404 (Acute Dermal Irritation / Corrosion)

**Serious eye damage/irritation:**

Fumes emitted during soldering may irritate the eyes.

Hazardous substances CAS-No.	Result	Exposure time	Species	Method
Tin 7440-31-5	not irritating		rabbit	OECD Guideline 405 (Acute Eye Irritation / Corrosion)
Colophony 8050-09-7	not irritating		rabbit	OECD Guideline 405 (Acute Eye Irritation / Corrosion)

**Respiratory or skin sensitization:**

No data available.

**Germ cell mutagenicity:**

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Type of study / Route of administration	Metabolic activation / Exposure time	Species	Method
Tin 7440-31-5	negative	bacterial reverse mutation assay (e.g Ames test)	with and without		OECD Guideline 471 (Bacterial Reverse Mutation Assay)
Tin 7440-31-5	negative	in vitro mammalian chromosome aberration test	with and without		OECD Guideline 473 (In vitro Mammalian Chromosome Aberration Test)
Tin 7440-31-5	negative	mammalian cell gene mutation assay	with and without		OECD Guideline 476 (In vitro Mammalian Cell Gene Mutation Test)
Colophony 8050-09-7	negative	bacterial reverse mutation assay (e.g Ames test)	with and without		OECD Guideline 471 (Bacterial Reverse Mutation Assay)

**Carcinogenicity**

No data available.

**Reproductive toxicity:**

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result / Value	Test type	Route of application	Species	Method
Tin 7440-31-5	NOAEL P > 1.000 mg/kg		oral: gavage	rat	OECD Guideline 421 (Reproduction / Developmental Toxicity Screening Test)

**STOT-single exposure:**

No data available.

**STOT-repeated exposure::**

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result / Value	Route of application	Exposure time / Frequency of treatment	Species	Method
Tin 7440-31-5	NOAEL > 1.000 mg/kg	oral: gavage	28 days daily	rat	OECD Guideline 407 (Repeated Dose 28-Day Oral Toxicity in Rodents)

**Aspiration hazard:**

No data available.

**SECTION 12: Ecological information**

**General ecological information:**

Do not empty into drains / surface water / ground water.

**12.1. Toxicity**

**Toxicity (Fish):**

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Tin 7440-31-5	LC50		96 h	Pimephales promelas	OECD Guideline 203 (Fish, Acute Toxicity Test)
Colophony 8050-09-7	LC50		96 h	Pimephales promelas	OECD Guideline 203 (Fish, Acute Toxicity Test)

**Toxicity (Daphnia):**

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Colophony 8050-09-7	EL50		48 h	Daphnia magna	OECD Guideline 202 (Daphnia sp. Acute Immobilisation Test)

**Chronic toxicity to aquatic invertebrates**

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Tin 7440-31-5	NOEC		7 d	Ceriodaphnia dubia	other guideline:

**Toxicity (Algae):**

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Tin 7440-31-5	EC50		72 h	Pseudokirchneriella subcapitata	OECD Guideline 201 (Alga, Growth Inhibition Test)
Tin 7440-31-5	NOEC		72 h	Pseudokirchneriella subcapitata	OECD Guideline 201 (Alga, Growth Inhibition Test)
Colophony 8050-09-7	EL50		72 h	Pseudokirchneriella subcapitata	OECD Guideline 201 (Alga, Growth Inhibition Test)
Colophony 8050-09-7	NOELR		72 h	Pseudokirchneriella subcapitata	OECD Guideline 201 (Alga, Growth Inhibition Test)

#### Toxicity to microorganisms

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Tin 7440-31-5	EC50		3 h	activated sludge of a predominantly domestic sewage	OECD Guideline 209 (Activated Sludge, Respiration Inhibition Test)
Colophony 8050-09-7	EC20		3 h	activated sludge of a predominantly domestic sewage	OECD Guideline 209 (Activated Sludge, Respiration Inhibition Test)

#### 12.2. Persistence and degradability

The product is not biodegradable.

Hazardous substances CAS-No.	Result	Test type	Degradability	Exposure time	Method
Colophony 8050-09-7	readily biodegradable	aerobic	71 %	28 d	OECD Guideline 301 D (Ready Biodegradability: Closed Bottle Test)

#### 12.3. Bioaccumulative potential

No data available.

No substance data available.

#### 12.4. Mobility in soil

The product is insoluble and sinks in water.

Hazardous substances CAS-No.	LogPow	Temperature	Method
Colophony 8050-09-7	> 3 - 6,2		OECD Guideline 117 (Partition Coefficient (n-octanol / water), HPLC Method)

#### 12.5. Results of PBT and vPvB assessment

Hazardous substances CAS-No.	PBT / vPvB
Tin 7440-31-5	Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.
Colophony 8050-09-7	Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

#### 12.6. Other adverse effects

No data available.

## SECTION 13: Disposal considerations

#### 13.1. Waste treatment methods

**Product disposal:**

Wherever possible unwanted solder alloy should be recycled for recovery of metal.  
Otherwise dispose of in accordance with local and national regulations.

**Disposal of uncleaned packages:**

Dispose of as unused product.

**Waste code**

06 04 05 - wastes containing other heavy metals

The valid EWC waste code numbers are source-related. The manufacturer is therefore unable to specify EWC waste codes for the articles or products used in the various sectors. The EWC codes listed are intended as a recommendation for users. We will be happy to advise you.

## SECTION 14: Transport information

**14.1. UN number**

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

**14.2. UN proper shipping name**

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

**14.3. Transport hazard class(es)**

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

**14.4. Packing group**

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

**14.5. Environmental hazards**

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

**14.6. Special precautions for user**

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

**14.7. Transport in bulk according to Annex II of Marpol and the IBC Code**

not applicable

## SECTION 15: Regulatory information

**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

VOC content < 3 %  
(2010/75/EC)

**15.2. Chemical safety assessment**

A chemical safety assessment has not been carried out.

**National regulations/information (Great Britain):**

Remarks

The Health & Safety at Work Act 1974.  
The Control of Substances Hazardous to Health Regulations. L5:General Approved Code of Practice to the COSHH Regulations. HS(G)97:A Step by Step Guide to the COSHH Regulations. HS(G)193: COSHH essentials: Easy steps to control chemicals.  
IND (G)248L:Solder fume and you. IND(G)249L:Controlling health risks from rosin (colophony) based solder fluxes.  
The Control of Lead at Work Regulations. L132:Control of Lead at Work: Approved Code of Practice and Guidance.  
Employees should be under medical surveillance if the risk assessment made under the Control of Lead at Work Regulations indicates they are likely to be exposed to significant concentrations of lead, or if an Employment Medical Advisor or appointed doctor so certifies.  
A woman employed on work which exposes her to lead should notify her employer as soon as possible if she becomes pregnant. The Employment Medical Advisor / Appointed Doctor should be informed of the pregnancy.  
Under the Management of Health and Safety at Work Regulations, employers are required to assess the particular risks to health at work of pregnant workers and workers who have recently given birth or who are breast feeding.

## SECTION 16: Other information

The labelling of the product is indicated in Section 2. The full text of all abbreviations indicated by codes in this safety data sheet are as follows:  
H317 May cause an allergic skin reaction.

### Further information:

This Safety Data Sheet has been produced for sales from Henkel to parties purchasing from Henkel, is based on Regulation (EC) No 1907/2006 and provides information in accordance with applicable regulations of the European Union only. In that respect, no statement, warranty or representation of any kind is given as to compliance with any statutory laws or regulations of any other jurisdiction or territory other than the European Union. When exporting to territories other than the European Union, please consult with the respective Safety Data Sheet of the concerned territory to ensure compliance or liaise with Henkel's Product Safety and Regulatory Affairs Department (ua-productsafety.de@henkel.com) prior to export to other territories than the European Union.

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

Dear Customer,

Henkel is committed to creating a sustainable future by promoting opportunities along the entire value chain. If you would like to contribute by switching from a paper to the electronic version of SDS, please contact the local Customer Service representative. We recommend to use a non-personal email address (e.g. SDS@your\_company.com).

**Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.**