

IPD H 5P2,5 BK - H distributor

1499531

<https://www.phoenixcontact.com/gb/products/1499531>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

H distributor, product family: IPD, number of positions: 4+PE, 600 V, 17.5 A, black, coding: P



Your advantages

- Easy distribution of power, as components are plugged directly
- Simple, time-saving wiring in the field with Push-Lock connection
- Reliable installation in harsh environments with IP66, IP68, and IP69K throughout the entire system
- Secure, tool-free locking even in particularly difficult installation situations
- Fast commissioning with preassembled cable assemblies

Commercial data

Item number	1499531
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AF6MAA
Product key	AF6MAA
GTIN	4063151955441
Weight per piece (including packing)	214.5 g
Weight per piece (excluding packing)	214 g
Customs tariff number	85366990
Country of origin	DE

IPD H 5P2,5 BK - H distributor

1499531

<https://www.phoenixcontact.com/gb/products/1499531>



Technical data

Notes

Order information:	Mounting material is not supplied as standard.
--------------------	--


Product properties

Product type	Power distributor
Product family	IPD
Type	H-distributor
Number of positions	5
Connection profile	4+PE
Position marking	1, 2, 3, N, PE
Coding	P

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Dimensions

Dimensional drawing	
Width	125 mm
Height	54 mm
Length	63 mm

Electrical properties

Rated surge voltage (III/3)	6 kV
Rated current	17.5 A
Rated voltage (III/3)	600 V
Nominal voltage U_N	600 V AC
	600 V DC
Nominal current I_N	17.5 A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	50 (IP66/IP68/IP69K)
	100 (IP66)

IPD H 5P2,5 BK - H distributor



1499531

<https://www.phoenixcontact.com/gb/products/1499531>

Material specifications

Color (Housing)	black (RAL 9005)
Flammability rating according to UL 94	V0

Cable/line

Position marking	1, 2, 3, N, PE
------------------	----------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66
	IP68 (2 m / 24 h)
	IP69K
	Touch-proof when not plugged in (IP2X)
Impact strength	IK07
Ambient temperature (operation)	-30 °C ... 100 °C
Temperature when conductor connected	-5 °C ... 50 °C
Resistance to UV radiation	yes

IPD H 5P2,5 BK - H distributor



1499531

<https://www.phoenixcontact.com/gb/products/1499531>




Drawings


Dimensional drawing




Dimensional drawing



Screw fixing (mounting material not supplied as standard)




Derating diagram for 1.0 mm²




Derating diagram for 1.5 mm²

Diagram



Derating diagram for 2.5 mm²

Circuit diagram



IPD H 5P2,5 BK - H distributor

1499531

<https://www.phoenixcontact.com/gb/products/1499531>



Approvals

💡 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1499531>



VDE Zeichengenehmigung

Approval ID: 40059408

IPD H 5P2,5 BK - H distributor

1499531

<https://www.phoenixcontact.com/gb/products/1499531>



Classifications

ECLASS

ECLASS-13.0	27440603
-------------	----------

ETIM

ETIM 9.0	EC002567
----------	----------

IPD H 5P2,5 BK - H distributor

1499531

<https://www.phoenixcontact.com/gb/products/1499531>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk