

CP2617 v1.2 RS 136-8537**SAFETY DATA SHEET
RS Pro High Grade Cleaning Fluid**

According to Regulation (EC) No 1907/2006, Annex II, as amended. Commission Regulation (EU) No 2015/830 of 28 May 2015.

SECTION 1: Identification of the substance/mixture and of the company/undertaking**1.1. Product identifier**

Product name	RS Pro High Grade Cleaning Fluid
Product number	136-8537, ZP
UFI	UFI: 9QUC-N0VK-Y00H-JW3H

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses	Cleaning agent.
Uses advised against	No specific uses advised against are identified.

1.3. Details of the supplier of the safety data sheet

Supplier	RS Components Ltd Birchington Road, Corby, Northants NN17 9RS +44 (0) 845 850 9900 RCustomerServicesUK@rs-components.com
-----------------	--

RS Components Ltd
Glenview Industrial Estate
Herberton Road
Rialto
Dublin 12
+353 (0) 1 415 3100
enquiries.ie@rs-components.com

1.4. Emergency telephone number

Emergency telephone	+44 (0)1865 407333 +44 1235 239670
----------------------------	---------------------------------------

SECTION 2: Hazards identification**2.1. Classification of the substance or mixture****Classification (EC 1272/2008)**

Physical hazards	Aerosol 1 - H222, H229
Health hazards	Eye Irrit. 2 - H319 STOT SE 3 - H336 Asp. Tox. 1 - H304
Environmental hazards	Aquatic Chronic 2 - H411

2.2. Label elements**Hazard pictograms**

Signal word

Danger

RS Pro High Grade Cleaning Fluid

Hazard statements	H222 Extremely flammable aerosol. H229 Pressurised container: may burst if heated. H319 Causes serious eye irritation. H336 May cause drowsiness or dizziness. H411 Toxic to aquatic life with long lasting effects.
Precautionary statements	P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. P211 Do not spray on an open flame or other ignition source. P251 Do not pierce or burn, even after use. P261 Avoid breathing spray. P410+P412 Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F. P501 Dispose of contents/ container in accordance with national regulations.
Contains	pentane, Propan-2-ol
Supplementary precautionary statements	P264 Wash contaminated skin thoroughly after handling. P271 Use only outdoors or in a well-ventilated area. P273 Avoid release to the environment. P280 Wear protective gloves/ protective clothing/ eye protection/ face protection. P304+P340 IF INHALED: Remove person to fresh air and keep comfortable for breathing. P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. P312 Call a POISON CENTRE/doctor if you feel unwell. P337+P313 If eye irritation persists: Get medical advice/ attention. P391 Collect spillage. P403+P233 Store in a well-ventilated place. Keep container tightly closed.

2.3. Other hazards

This product does not contain any substances classified as PBT or vPvB.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

pentane		60-100%
CAS number: 109-66-0	EC number: 203-692-4	REACH registration number: 01-2119459286-30-XXXX
Classification		
Flam. Liq. 2 - H225		
STOT SE 3 - H336		
Asp. Tox. 1 - H304		
Aquatic Chronic 2 - H411		
Propan-2-ol		10-30%
CAS number: 67-63-0	EC number: 200-661-7	REACH registration number: 01-2119457558-25-XXXX
Classification		
Flam. Liq. 2 - H225		
Eye Irrit. 2 - H319		
STOT SE 3 - H336		

RS Pro High Grade Cleaning Fluid

Carbon Dioxide	1-5%
CAS number: 124-38-9	
Classification	
Press. Gas (Comp.) - H280	

The full text for all hazard statements is displayed in Section 16.

SECTION 4: First aid measures

4.1. Description of first aid measures

General information	Get medical attention if any discomfort continues. Show this Safety Data Sheet to the medical personnel.
Inhalation	Move affected person to fresh air and keep warm and at rest in a position comfortable for breathing. Maintain an open airway. Loosen tight clothing such as collar, tie or belt. When breathing is difficult, properly trained personnel may assist affected person by administering oxygen. Get medical attention. Place unconscious person on their side in the recovery position and ensure breathing can take place.
Ingestion	Rinse mouth thoroughly with water. Give a few small glasses of water or milk to drink. Stop if the affected person feels sick as vomiting may be dangerous. Never give anything by mouth to an unconscious person. Place unconscious person on their side in the recovery position and ensure breathing can take place. Keep affected person under observation. Get medical attention if symptoms are severe or persist.
Skin contact	Rinse with water.
Eye contact	Rinse with water. Do not rub eye. Remove any contact lenses and open eyelids wide apart. Get medical attention if any discomfort continues.
Protection of first aiders	First aid personnel should wear appropriate protective equipment during any rescue.

4.2. Most important symptoms and effects, both acute and delayed

General information	The severity of the symptoms described will vary dependent on the concentration and the length of exposure.
Inhalation	A single exposure may cause the following adverse effects: Headache. Nausea, vomiting. Central nervous system depression. Drowsiness, dizziness, disorientation, vertigo. Narcotic effect.
Ingestion	Due to the physical nature of this product, it is unlikely that ingestion will occur. Aspiration hazard if swallowed. Entry into the lungs following ingestion or vomiting may cause chemical pneumonitis.
Skin contact	Repeated exposure may cause skin dryness or cracking.
Eye contact	Irritating to eyes.

4.3. Indication of any immediate medical attention and special treatment needed

Notes for the doctor	Treat symptomatically.
-----------------------------	------------------------

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media	The product is flammable. Extinguish with alcohol-resistant foam, carbon dioxide, dry powder or water fog. Use fire-extinguishing media suitable for the surrounding fire.
Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire.

RS Pro High Grade Cleaning Fluid

5.2. Special hazards arising from the substance or mixture

Specific hazards Containers can burst violently or explode when heated, due to excessive pressure build-up. Bursting aerosol containers may be propelled from a fire at high speed. If aerosol cans are ruptured, care should be taken due to the rapid escape of the pressurised contents and propellant. Vapours may form explosive mixtures with air.

Hazardous combustion products Thermal decomposition or combustion products may include the following substances: Harmful gases or vapours.

5.3. Advice for firefighters

Protective actions during firefighting Avoid breathing fire gases or vapours. Evacuate area. Keep upwind to avoid inhalation of gases, vapours, fumes and smoke. Ventilate closed spaces before entering them. Cool containers exposed to heat with water spray and remove them from the fire area if it can be done without risk. Cool containers exposed to flames with water until well after the fire is out. If a leak or spill has not ignited, use water spray to disperse vapours and protect men stopping the leak. Avoid discharge to the aquatic environment. Control run-off water by containing and keeping it out of sewers and watercourses. If risk of water pollution occurs, notify appropriate authorities.

Special protective equipment for firefighters Wear positive-pressure self-contained breathing apparatus (SCBA) and appropriate protective clothing. Firefighter's clothing conforming to European standard EN469 (including helmets, protective boots and gloves) will provide a basic level of protection for chemical incidents.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions Wear protective clothing as described in Section 8 of this safety data sheet. No action shall be taken without appropriate training or involving any personal risk. Do not touch or walk into spilled material. Evacuate area. Risk of explosion. Provide adequate ventilation. No smoking, sparks, flames or other sources of ignition near spillage. Promptly remove any clothing that becomes contaminated.

6.2. Environmental precautions

Environmental precautions Avoid discharge into drains or watercourses or onto the ground. Avoid discharge to the aquatic environment.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up Wear protective clothing as described in Section 8 of this safety data sheet. Clear up spills immediately and dispose of waste safely. Eliminate all ignition sources if safe to do so. No smoking, sparks, flames or other sources of ignition near spillage. Under normal conditions of handling and storage, spillages from aerosol containers are unlikely. If aerosol cans are ruptured, care should be taken due to the rapid escape of the pressurised contents and propellant. Small Spillages: Wipe up with an absorbent cloth and dispose of waste safely. Large Spillages: If the product is soluble in water, dilute the spillage with water and mop it up. Alternatively, or if it is not water-soluble, absorb the spillage with an inert, dry material and place it in a suitable waste disposal container. Flush contaminated area with plenty of water. Wash thoroughly after dealing with a spillage. Dangerous for the environment. Do not empty into drains. For waste disposal, see Section 13.

6.4. Reference to other sections

Reference to other sections For personal protection, see Section 8. See Section 11 for additional information on health hazards. See Section 12 for additional information on ecological hazards. For waste disposal, see Section 13.

SECTION 7: Handling and storage

RS Pro High Grade Cleaning Fluid

7.1. Precautions for safe handling

Usage precautions

Read and follow manufacturer's recommendations. Wear protective clothing as described in Section 8 of this safety data sheet. Keep away from food, drink and animal feeding stuffs. Avoid exposing aerosol containers to high temperatures or direct sunlight. The product is flammable. Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. Do not handle until all safety precautions have been read and understood. Do not handle broken packages without protective equipment. Do not reuse empty containers. Do not spray on an open flame or other ignition source. Do not pierce or burn, even after use. Spray will evaporate and cool rapidly and may cause frostbite or cold burns if in contact with skin. Avoid contact with eyes. Avoid inhalation of vapours and spray/mists.

Advice on general occupational hygiene

Wash promptly if skin becomes contaminated. Take off contaminated clothing. Wash contaminated clothing before reuse.

7.2. Conditions for safe storage, including any incompatibilities

Storage precautions

Store away from incompatible materials (see Section 10). Keep away from oxidising materials, heat and flames. Keep only in the original container. Keep container tightly closed, in a cool, well ventilated place. Keep containers upright. Protect containers from damage. Protect from sunlight. Do not store near heat sources or expose to high temperatures. Do not expose to temperatures exceeding 50°C/122°F.

Storage class

Miscellaneous hazardous material storage.

7.3. Specific end use(s)

Specific end use(s)

The identified uses for this product are detailed in Section 1.2.

SECTION 8: Exposure controls/Personal protection

8.1. Control parameters

Occupational exposure limits

pentane

Long-term exposure limit (8-hour TWA): WEL 600 ppm 1800 mg/m³

Propan-2-ol

Long-term exposure limit (8-hour TWA): WEL 400 ppm 999 mg/m³

Short-term exposure limit (15-minute): WEL 500 ppm 1250 mg/m³

Carbon Dioxide

Long-term exposure limit (8-hour TWA): WEL 5000 ppm 9150 mg/m³

Short-term exposure limit (15-minute): WEL 15000 ppm 27400 mg/m³

WEL = Workplace Exposure Limit

8.2. Exposure controls

Protective equipment



Appropriate engineering controls

Provide adequate general and local exhaust ventilation. Ensure the ventilation system is regularly maintained and tested. Good general ventilation should be adequate to control worker exposure to airborne contaminants. Observe any occupational exposure limits for the product or ingredients.

Eye/face protection

Wear tight-fitting, chemical splash goggles or face shield. If inhalation hazards exist, a full-face respirator may be required instead.

RS Pro High Grade Cleaning Fluid

Hand protection	No specific hand protection recommended. Avoid contact with skin.
Other skin and body protection	Wear appropriate clothing to prevent repeated or prolonged skin contact.
Hygiene measures	Wash after use and before eating, smoking and using the toilet. Do not eat, drink or smoke when using this product.
Respiratory protection	Ensure all respiratory protective equipment is suitable for its intended use and is 'CE'-marked. Check that the respirator fits tightly and the filter is changed regularly. Gas and combination filter cartridges should comply with European Standard EN14387. Full face mask respirators with replaceable filter cartridges should comply with European Standard EN136. Half mask and quarter mask respirators with replaceable filter cartridges should comply with European Standard EN140.
Environmental exposure controls	Keep container tightly sealed when not in use. Emissions from ventilation or work process equipment should be checked to ensure they comply with the requirements of environmental protection legislation. In some cases, fume scrubbers, filters or engineering modifications to the process equipment will be necessary to reduce emissions to acceptable levels.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance	Liquid.
Colour	Colourless.
Odour	Characteristic.
pH	Not available.
Melting point	Not available.
Initial boiling point and range	Not available.
Flash point	< -45°C/-49°F
Evaporation rate	Not available.
Flammability (solid, gas)	Not available.
Upper/lower flammability or explosive limits	Not available.
Vapour pressure	Not available.
Vapour density	Not available.
Bulk density	0.63 kg/l
Solubility(ies)	Not available.
Partition coefficient	Not available.
Auto-ignition temperature	Not available.
Decomposition Temperature	Not available.
Viscosity	Not available.
Explosive properties	Not considered to be explosive.
Oxidising properties	Does not meet the criteria for classification as oxidising.

9.2. Other information

RS Pro High Grade Cleaning Fluid

SECTION 10: Stability and reactivity

10.1. Reactivity

Reactivity See the other subsections of this section for further details.

10.2. Chemical stability

Stability Stable at normal ambient temperatures and when used as recommended. Stable under the prescribed storage conditions.

10.3. Possibility of hazardous reactions

Possibility of hazardous reactions The following materials may react strongly with the product: Oxidising agents.

10.4. Conditions to avoid

Conditions to avoid Avoid exposing aerosol containers to high temperatures or direct sunlight. Pressurised container: may burst if heated

10.5. Incompatible materials

Materials to avoid No specific material or group of materials is likely to react with the product to produce a hazardous situation.

10.6. Hazardous decomposition products

Hazardous decomposition products Does not decompose when used and stored as recommended. Thermal decomposition or combustion products may include the following substances: Harmful gases or vapours.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity - oral

Notes (oral LD₅₀) Based on available data the classification criteria are not met.

Acute toxicity - dermal

Notes (dermal LD₅₀) Based on available data the classification criteria are not met.

Acute toxicity - inhalation

Notes (inhalation LC₅₀) Based on available data the classification criteria are not met.

Skin corrosion/irritation

Animal data Based on available data the classification criteria are not met.

Serious eye damage/irritation

Serious eye damage/irritation Causes serious eye irritation.

Respiratory sensitisation

Respiratory sensitisation Based on available data the classification criteria are not met.

Skin sensitisation

Skin sensitisation Based on available data the classification criteria are not met.

Germ cell mutagenicity

Genotoxicity - in vitro Based on available data the classification criteria are not met.

Carcinogenicity

Carcinogenicity Based on available data the classification criteria are not met.

IARC carcinogenicity

None of the ingredients are listed or exempt.

Reproductive toxicity

RS Pro High Grade Cleaning Fluid

Reproductive toxicity - fertility Based on available data the classification criteria are not met.

Reproductive toxicity - development Based on available data the classification criteria are not met.

Specific target organ toxicity - single exposure

STOT - single exposure STOT SE 3 - H336 May cause drowsiness or dizziness.

Target organs Central nervous system

Specific target organ toxicity - repeated exposure

STOT - repeated exposure Not classified as a specific target organ toxicant after repeated exposure.

Aspiration hazard

Aspiration hazard Asp. Tox. 1 - H304 May be fatal if swallowed and enters airways. Pneumonia may be the result if vomited material containing solvents reaches the lungs.

General information

The severity of the symptoms described will vary dependent on the concentration and the length of exposure.

Inhalation

A single exposure may cause the following adverse effects: Headache. Nausea, vomiting. Central nervous system depression. Drowsiness, dizziness, disorientation, vertigo. Narcotic effect.

Ingestion

Due to the physical nature of this product, it is unlikely that ingestion will occur. Aspiration hazard if swallowed. Entry into the lungs following ingestion or vomiting may cause chemical pneumonitis.

Skin contact

Repeated exposure may cause skin dryness or cracking.

Eye contact

Irritating to eyes.

Route of exposure

Ingestion Inhalation Skin and/or eye contact

Target organs

Central nervous system

SECTION 12: Ecological information

12.1. Toxicity

Toxicity Aquatic Chronic 2 - H411 Toxic to aquatic life with long lasting effects.

12.2. Persistence and degradability

Persistence and degradability The degradability of the product is not known.

12.3. Bioaccumulative potential

Bioaccumulative potential No data available on bioaccumulation.

Partition coefficient

Not available.

12.4. Mobility in soil

Mobility

The product contains volatile organic compounds (VOCs) which will evaporate easily from all surfaces.

12.5. Results of PBT and vPvB assessment

12.6. Other adverse effects

Other adverse effects None known.

SECTION 13: Disposal considerations

RS Pro High Grade Cleaning Fluid

13.1. Waste treatment methods

General information	The generation of waste should be minimised or avoided wherever possible. Reuse or recycle products wherever possible. This material and its container must be disposed of in a safe way. When handling waste, the safety precautions applying to handling of the product should be considered. Care should be taken when handling emptied containers that have not been thoroughly cleaned or rinsed out. Empty containers or liners may retain some product residues and hence be potentially hazardous.
Disposal methods	Do not empty into drains. Empty containers must not be punctured or incinerated because of the risk of an explosion. Dispose of surplus products and those that cannot be recycled via a licensed waste disposal contractor. Waste, residues, empty containers, discarded work clothes and contaminated cleaning materials should be collected in designated containers, labelled with their contents.

SECTION 14: Transport information

General	For limited quantity packaging/limited load information, consult the relevant modal documentation using the data shown in this section.
----------------	---

14.1. UN number

UN No. (ADR/RID)	1950
UN No. (IMDG)	1950
UN No. (ICAO)	1950
UN No. (ADN)	1950

14.2. UN proper shipping name

Proper shipping name (ADR/RID)	AEROSOLS
Proper shipping name (IMDG)	AEROSOLS (CONTAINS pentane)
Proper shipping name (ICAO)	AEROSOLS
Proper shipping name (ADN)	AEROSOLS

14.3. Transport hazard class(es)

ADR/RID class	2.1
ADR/RID classification code	5F
ADR/RID label	2.1
IMDG class	2.1
ICAO class/division	2.1
ADN class	2.1

Transport labels



14.4. Packing group

ADR/RID packing group	None
IMDG packing group	None

RS Pro High Grade Cleaning Fluid

ICAO packing group None

ADN packing group None

14.5. Environmental hazards

Environmentally hazardous substance/marine pollutant



14.6. Special precautions for user

Always transport in closed containers that are upright and secure. Ensure that persons transporting the product know what to do in the event of an accident or spillage.

EmS F-D, S-U

ADR transport category 2

Tunnel restriction code (D)

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Transport in bulk according to Not applicable.

Annex II of MARPOL 73/78
and the IBC Code

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

National regulations Health and Safety at Work etc. Act 1974 (as amended).
The Carriage of Dangerous Goods and Use of Transportable Pressure Equipment Regulations 2009 (SI 2009 No. 1348) (as amended) ["CDG 2009"].
EH40/2005 Workplace exposure limits.
The Aerosol Dispensers Regulations 2009 (SI 2009 No. 2824).

EU legislation Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH) (as amended).
Commission Regulation (EU) No 2015/830 of 28 May 2015.
Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures (as amended).
Council Directive of 20 May 1975 on the approximation of the laws of the Member States relating to aerosol dispensers (75/324/EEC) (as amended).

15.2. Chemical safety assessment

No chemical safety assessment has been carried out.

Inventories

EU - EINECS/ELINCS

None of the ingredients are listed or exempt.

SECTION 16: Other information

RS Pro High Grade Cleaning Fluid

Abbreviations and acronyms used in the safety data sheet	<p>ADR: European Agreement concerning the International Carriage of Dangerous Goods by Road.</p> <p>ADN: European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways.</p> <p>RID: European Agreement concerning the International Carriage of Dangerous Goods by Rail.</p> <p>IATA: International Air Transport Association.</p> <p>ICAO: Technical Instructions for the Safe Transport of Dangerous Goods by Air.</p> <p>IMDG: International Maritime Dangerous Goods.</p> <p>CAS: Chemical Abstracts Service.</p> <p>ATE: Acute Toxicity Estimate.</p> <p>LC₅₀: Lethal Concentration to 50 % of a test population.</p> <p>LD₅₀: Lethal Dose to 50% of a test population (Median Lethal Dose).</p> <p>EC₅₀: 50% of maximal Effective Concentration.</p> <p>PBT: Persistent, Bioaccumulative and Toxic substance.</p> <p>vPvB: Very Persistent and Very Bioaccumulative.</p>
Classification abbreviations and acronyms	<p>Aerosol = Aerosol</p> <p>Eye Irrit. = Eye irritation</p> <p>STOT SE = Specific target organ toxicity-single exposure</p> <p>Aquatic Chronic = Hazardous to the aquatic environment (chronic)</p>
Classification procedures according to Regulation (EC) 1272/2008	<p>Asp. Tox. 1 - H304: STOT SE 3 - H336: Eye Irrit. 2 - H319: : Calculation method. Aquatic Chronic 2 - H411: : Calculation method. Aerosol 1 - H222, H229: : Expert judgement.</p>
Training advice	<p>Only trained personnel should use this material.</p>
Issued by	<p>Emily Kirk</p>
Revision date	<p>15/11/2019</p>
Revision	<p>0.2</p>
SDS number	<p>1441</p>
Hazard statements in full	<p>H222 Extremely flammable aerosol.</p> <p>H225 Highly flammable liquid and vapour.</p> <p>H229 Pressurised container: may burst if heated.</p> <p>H280 Contains gas under pressure; may explode if heated.</p> <p>H304 May be fatal if swallowed and enters airways.</p> <p>H319 Causes serious eye irritation.</p> <p>H336 May cause drowsiness or dizziness.</p> <p>H411 Toxic to aquatic life with long lasting effects.</p>

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty, guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.