


| SPECIFICATIONS                    |                                  |
|-----------------------------------|----------------------------------|
| CONTACT CARRIER MATERIAL          | NYLON OR TPU                     |
| MOLDED HEAD MATERIAL/COLOR        | TPU/YELLOW                       |
| CONTACT MATERIAL/PLATING          | BRASS/GOLD                       |
| LOCKING SLEEVE/COLOR              | POM, SNAP LOCK/BLACK (J1)        |
| RATED CURRENT [A]                 | 2.0 A                            |
| RATED VOLTAGE [V]                 | 125 VAC/VDC                      |
| OUTER CABLE JACKET MATERIAL/COLOR | TPU/BLACK                        |
| CONDUCTOR INSULATION MATERIAL     | PVC                              |
| NUMBER OF CONDUCTORS [AWG]        | 4x26 AWG                         |
| TEMPERATURE RANGE                 | -40°C to +90°C (-40°F to +194°F) |
| PROTECTION CLASS                  | MEETS NEMA 1,3,4,6P AND IEC IP67 |



| CABLE LENGTH | TOLERANCE   |
|--------------|---|
| ALL LENGTHS  | + 4% (OR 50mm) OF LENGTH<br>- 0% (OR 0mm) OF LENGTH<br>WHICHEVER IS GREATER |
| STRIP LENGTH | TOLERANCE   |
| 0-7mm        | ±0.5mm  |
| 8-29mm       | ±1.0mm  |
| 30-49mm      | ±2.0mm  |
| 50-69mm      | ±3.0mm  |
| 70-100mm     | ±4.0mm  |
| OVER 100mm   | ±5.0mm  |

NOTES:

1. "\*" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.

2. "/S90" DESIGNATES THERMOPLASTIC POLYURETHANE (TPU) CABLE JACKET.

SOURCE DRAWING - FOR REFERENCE ONLY

|   |   |  |                  |   |                                     |
|---|---|--|------------------|---|-------------------------------------|
| RELATED DOCUMENTS<br>1.<br>2.<br>3.<br>4. | 3RD ANGLE PROJECTION<br>  | THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED. |                  | <b>TURCK INC</b><br><i>High Technology Sensors and Automation Controls</i><br>3000 CAMPUS DRIVE<br>MINNEAPOLIS, MN 55441<br>1-800-544-7769<br>(763) 553-7300<br>(763) 553-0708 fax<br>turck.com |                                     |
|   |   | MATERIAL   | DRFT RWC<br>APVD | DATE 02/26/10<br>SCALE 1=1.0  | DESCRIPTION<br>PKG 4Z--*--PSG 4/S90 |
| FINISH                                    | ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY<br><br>CONTACT TURCK FOR MORE INFORMATION | UNIT OF MEASUREMENT<br><b>MILLIMETER [ INCH ]</b>  |                  | IDENTIFICATION NO.  | REV<br>D                            |
| DO NOT SCALE THIS DRAWING                 |   | FILE: 777008283  |                  | SHEET 1 OF 1  |                                     |

|     |                       |     |          |         |
|-----|-----------------------|-----|----------|---------|
| D   | UPDATE CABLE DIAMETER | KMY | 02/01/12 | 36086   |
| REV | DESCRIPTION           | BY  | DATE     | ECO NO. |