



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Pb (.6% in 74020097) <b>Article Safe Usage Statements:</b> Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1059412-1  
[4504 7985 00](#)

Customers Also Bought



TE Part #1-1623782-1  
[SQM5 33K 5% \(METAL FILM\)](#)



TE Part #1742428-1  
[110 FASTON,TAB,PCB,TPBR](#)




TE Part #2-604771-0  
[CABLE TIE, BLACK, 4" \(1000\)](#)



TE Part #3-641213-3  
[03P MTA100 HDR ASSY PO/ST LF](#)



TE Part #1586512-2  
[02P CMNL HDR ASSY PC NATL LF](#)



TE Part #3-1393159-6  
[20C250=SPRING,HOLD-DOWN,R10,.0](#)




TE Part #350211-1  
[04P CMNL HDR ASSY PC](#)



TE Part #3-643817-5  
[05P MTA156 CONN ASSY 18AWG  
ORA](#)



TE Part #350541-1  
[03P CMNL HDR ASSY SHORT NATL](#)



TE Part #3-1393143-6  
[27E342=SOCKET,R10,2POLE,PCB,.180](#)

Documents

Product Drawings

[4503 5022 00](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

[OSP Bulkhead Feedthrough Cable Plug Rear Mount Direct Solder Attachment 1059386-1 and 1059384-1](#)

English

