



Brand of NTN corporation

Technical data

UCPE215

Bearing units




Grey cast housing, radial insert ball bearing with socket set screws, seal with slinger

KIT CONTENT

UC215G2, PE215

VISUAL (S)



PRODUCT DEFINITION

Brand	SNR
A - Housing width	66 mm
A1 - Housing top width	48 mm
B - Width of Inner Ring	77,8 mm
d - Shaft diameter	75 mm
G - Grease fitting	R1/8"



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
 S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
 SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

PRODUCT DEFINITION

H - Distance mounting base to centerline spheric. seating diam.	82,5 mm
H1 - Housing foot height	27,5 mm
H2 - Housing height	164 mm
J - Mounting holes distance	210 mm
L - Housing length	265 mm
L1 - Housing foot length	78 mm
N - Mounting hole dimension	22 mm
N1 - Mounting hole length	30 mm
S - Distance front side/bearing centre	33,3 mm

PRODUCT PERFORMANCE

C - Dynamic load rating	66000000 mN
C0 - Static load rating	49500000 mN
Operating temperature min.	253,15 °K
Operating temperature max.	373,15 °K

OTHER FEATURES

Mass	6,91 kg
Recommended tightening torque for set screw	33 N-m

