

Product Data Sheet

T 12/1 eco!efficiency

A powerful, whisper quiet dry vacuum cleaner.

Kärcher's T 12/1 is a supremely robust, functional and powerful dry vacuum cleaner for professional users. With excellent ergonomic properties and compact design this high capacity vacuum was developed for the specific needs of hotels, shops and contract cleaning. The T 12/1 is a lightweight unit fitted with a 12m power cord enabling a large cleaning radius. It is also equipped with a large foot operated on/off switch, accessory storage on the back of the machine and integrated power cord storage around the turbine head. The chassis is fitted with an all round bumper, to protect the machine, furniture and other obstacles. With the option of the ESB 28 power brush the T 12/1 converts into a brush type vacuum perfect for cleaning in areas where stricter hygiene standards are paramount.



High performance,
40% less energy use*



Features and Benefits:

- 40% less energy consumption and perfect daily cleaning performance
- Thanks to optimised air stream technology, the T 12/1 eco!efficiency offers nearly the same cleaning performance as the standard T 12/1, but with 40% less energy consumption and a noise level of only 56 dB(A)
- The 750 W motor combined with modified flow channels generates around 98% of the cleaning performance of the standard T 12/1 – but costs 40% less to run



Range Comparison

Kärcher tub vacuum cleaners



Accessories

Standard accessories



Suction hose with bend
(2.5 m)
4.440-774



Metal suction tubes
(2 x 0.5m)
6.900-618



Carpet/floor tool
(dry)
6.906-696



Washable permanent nylon
filter basket
5.731-619

Optional accessories



Crevice & upholstery tool
suction brush
2.860-143



HEPA filter
(standard on T 12/1 HEPA)
6.414-801



ESB power brush
2.640-875



Power brush
(160mm)
2.860-113



Pack of paper bags
(pk 10)
9.533-211

Technical Specification

	T 12/1	T 12/1 HEPA
Power supply (Ph/V/Hz)	1/240/50	1/240/50
Max. Power Rating (w)	1300	1300
Air Flow Rate (l/s)	61	61
Vacuum Pressure (mbar/KPa)	244/24.4	244/24.4
Container Capacity (l)	12	12
Cable Length (m)	12	12
Suction Hose Length (m)	2.5	2.5
Operating Noise (dB(A))	61	61
Weight (kg)	6.6	6.6
Standard Inside Diameter (mm)	32	32
Dimensions (L x W x H) (mm)	340 x 315 x 410	340 x 315 x 410
Part Number	9.621-248	9.533-160

KARCHER®

makes a difference

Tel: 01295 752 082

Kärcher (UK) Ltd, Beaumont Road, Banbury, Oxon OX16 1TB
info@karcher.co.uk www.karcher.co.uk