Unigloves Product specification sheet Revision 4 | 17 October 2017

1.	Product code	GS002*					
2.	Product description	Unicare Soft Latex powdered					
3.	Material	Latex					
4.	Inspection parameters	Criteria		Inspection leve	el AC	QL QL	Standard
		Dimensions		S-2		4 EN455-2	
		Physical properties		S-2		4 EN455-2	
		Water tight test (1,000ml) Visual defects		G-1 1.		.5 EN455-1	
				G-1	2.	5 In-house	
5.	Glove dimensions			Size (mm)			
٥.		Dimensions	XS	S	М	L	XL
		Product code	GS0021	GS0022	GS0023	GS0024	GS0025
		Palm width	75 ± 5	80 ± 10	95 ± 10	110 ± 10	≥ 110
		Length	≥ 240	≥ 240	≥ 240	≥ 240	≥ 240
6.	Glove thickness	Point of thickness measurement Nominal single v					
		Cuff (at beaded end)				0.08	
		Palm (at centre of palm)				0.10	
		Fingertip (at fingertip) 0.12					
7.	Physical properties	Parameters Median force at break (N) Tensile strength (MPa)		Before aging		After aging	
				N/A		N/A	
				Min 18.0		Min 14.0	
		Ultimate elongation	Min 6	Min 650		Min 500	
8.	Proteins	> 50 μg/g extractable latex proteins					
9.	Powder residue	Maximum 10.0 mg / glove					
10.	Cuff type	Beaded					
11.	Design	Ambidextrous					
12.	Surface	Microroughened					
13.	Colour	Natural					
14.	Quality assurance	Manufactured under ISO 9001 and 13485					
15.	Weight (based on size medium)	5g					

The above data represents the product norm, which may be changed without notice and is intended as a guide only.