

Vacuum Cleaner LXT®

DCL180

18V • 42 mbar • 0.65 L

High-suction vacuum cleaner

This silent vacuum cleaner with high suction power is ideal for removing dirt and dust from the floor, staircases, jobsite or vehicle.



LXT

Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Air volume	1,4 m³/min
Max. sealed suction	42 mbar
Continuous Use 18V / 5.0 Ah Battery	33 min
Continuous Use 18V / 6.0 Ah Battery	39 min
Tank Capacity for Dust	0,65 L
Sound Pressure Level (L _{pA})	71 dB(A)
Vibration Level (3 axes)	≤ 2,5 m/s²
Tool weight with battery	1,2 - 1,5 kg
Product Dimensions (L x W x H):	999 x 114 x 152 mm
Continuous Use 18V / 3.0 Ah Battery	20 min
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Suction power	30 W
Product net weight	0,9 kg

User benefits

- Low noise level for pleasant work.
- Battery protection circuit protects against overloading, over-discharging and over-heating
- Ideal for upholstered furniture and stairs or workshop use
- Ergonomic soft grip handle provides increased comfort
- Increased storage capacity for longer time between waste disposal

Link to product - www.makitaauk.com



Related products

Optional AC

1910D3-4

Cyclone Pre-separator, White



1910D4-2

Cyclone Pre-separator



1910D5-0

Cyclone Pre-separator



1911L1-0

Vacuum Cleaner Stand Set



Other

User manual

Parts drawing